



Cross Reference to Rockwell
Part Number PN-128480



Relay, Time Delay

Time Delay Relay, Coil Voltage 120 VAC, Contact Form DPDT, Contact Current Rating 10 Amps, Power Rating @ 120 VAC 1/3 HP, Power Rating @ 240 VAC 1/2 HP, Maximum Time Range 999 Minutes, Minimum Time Range 0.05 Second, Number of Pins 8, On Delay

Brand	DAYTON
Mfr. Model #	6A854
Ship Qty.	1
Ship Weight (lbs.)	0.25

Additional Info

Time-Delay Relays

Tech Specs

Item: Time Delay Relay

Type: Plug-In

Contact Form: DPDT

Pins: 8

Base Type: Octal

Socket: 5X852, 1EGP3, 1EGP5

Function: On Delay

Contact Amp Rating (Resistive): 10

HP @ 120V: 1/3

HP @ 240V: 1/2

Coil Volts: 120VAC

Min. Time Setting: 0.05 sec.

Max. Time Setting: 999 min.

Notes & Restrictions

There are currently no notes or restrictions for this item.

MSDS

This item does not require a **Material Safety Data Sheet (MSDS)**.

Required Accessories

Socket, 8 Pins, 300V



Item #: 5X852

Brand: DAYTON