

Product Selection

Table 12-186. Types KD, HKD and KDC Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40°C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac		High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac		Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac		Thermal-Magnetic Trip Unit Only ①		Standard Terminals Only	
	Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ①		Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ①		Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ①		For Use with Standard or High or Ultra High Interrupting Frames		See Page 12-113 for Optional Terminals	
	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$

2-Pole

100	KD2100		HKD2100		KDC2100		KT2100T		TA300K ②	
125	KD2125		HKD2125		KDC2125		KT2125T		TA300K ②	
150	KD2150		HKD2150		KDC2150		KT2150T		TA300K ②	
175	KD2175		HKD2175		KDC2175		KT2175T		TA300K ②	
200	KD2200		HKD2200		KDC2200		KT2200T		TA300K ②	
225	KD2225		HKD2225		KDC2225		KT2225T		TA300K ②	
250	KD2250		HKD2250		KDC2250		KT2250T		TA350K ②	
300	KD2300		HKD2300		KDC2300		KT2300T		TA350K ②	
350	KD2350		HKD2350		KDC2350		KT2350T		TA350K ②	
400	KD2400		HKD2400		KDC2400		KT2400T		2TA400K ③	

3-Pole

100	KD3100		HKD3100		KDC3100		KT3100T		TA300K ②	
125	KD3125		HKD3125		KDC3125		KT3125T		TA300K ②	
150	KD3150		HKD3150		KDC3150		KT3150T		TA300K ②	
175	KD3175		HKD3175		KDC3175		KT3175T		TA300K ②	
200	KD3200		HKD3200		KDC3200		KT3200T		TA300K ②	
225	KD3225		HKD3225		KDC3225		KT3225T		TA300K ②	
250	KD3250		HKD3250		KDC3250		KT3250T		TA350K ②	
300	KD3300		HKD3300		KDC3300		KT3300T		TA350K ②	
350	KD3350		HKD3350		KDC3350		KT3350T		TA350K ②	
400	KD3400		HKD3400		KDC3400		KT3400T		3TA400K ③	



12

4-Pole

100	KD4100		HKD4100		KDC4100		KT3100T		TA300K ②	
125	KD4125		HKD4125		KDC4125		KT3125T		TA300K ②	
150	KD4150		HKD4150		KDC4150		KT3150T		TA300K ②	
175	KD4175		HKD4175		KDC4175		KT3175T		TA300K ②	
200	KD4200		HKD4200		KDC4200		KT3200T		TA300K ②	
225	KD4225		HKD4225		KDC4225		KT3225T		TA300K ②	
250	KD4250		HKD4250		KDC4250		KT3250T		TA350K ②	
300	KD4300		HKD4300		KDC4300		KT3300T		TA350K ②	
350	KD4350		HKD4350		KDC4350		KT3350T		TA350K ②	
400	KD4400		HKD4400		KDC4400		KT3400T		4TA400K ③	

① Magnetic trip adjustable 5 – 10 times continuous ampere rating.

② Individually packed.

③ 2TA400K, 3TA400K and 4TA400K terminal kits contain one terminal for each pole and one terminal cover.

Table 12-187. Types KD, HKD and KDC Thermal-Magnetic Circuit Breakers — Frame Only

Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac		High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac		Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac	
Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$

2-Pole

KD2400F		HKD2400F		KDC2400F	
---------	--	----------	--	----------	--

3-Pole

KD3400F		HKD3400F		KDC3400F	
---------	--	----------	--	----------	--

4-Pole

KD4400F		HKD4400F		KDC4400F	
---------	--	----------	--	----------	--