


STATE MOTOR & CONTROL SOLUTIONS  Cross Reference RA Part 25105-007-02

Product FINDER

PART #
product search 

Advanced Search



NEED HELP?
Call us for assistance
1.866.354.0063

Trusted PRODUCTS

- Custom Control Panels
- ABB
- Baldor Motors
- Bodine Electric Authorized Distributor
- Browning
- Emerson Power Transmission
- Furnas
- Hammond Transformers
- KB Electronics Controls
- Leeson Electric Motors
- Nord Gearing
- Sealmaster Bearings
- SEW Eurodrive
- Siemens
- Stearns Brakes
- US Motors
- WEG Electric
- Yaskawa
- Motor Repair / Rewind
- Engineering Data

view all manufacturers



Home / Hammond Transformer, NMF050LE, 50 kVA, 240 X 480 Pri Voltage, 120/240 Sec Voltage, 1PH, Nema 3R



Hammond Transformer, **NMF050LE**, 50 kVA, 240 X 480 Pri Voltage, 120/240 Sec Voltage, 1PH, Nema 3R

Part No: NMF050LE

\$1,533.60

Call for Freight Quote

Details

Specifications

kVA	50
Phase	1PH
Pri Voltage	240 X 480
Sec Voltage	120/240
Enclosure	Nema 3R
Winding Material	Aluminum
K-Factor	
Phase Shift	
Dimensions (WxDxH)	26.00 x 25.00 x 38.00
Weight	370
Mtg. Type	F or W *
Case Style	NH3
Wiring Diagram	SCD 17

Documents

- [Data Page](#)
- [Wiring Diagram](#)
- [Case Style](#)

- Electrical and Control
- AC Motors
- DC Motors
- DC Variable Speed Drives
- Clutches and Brakes
- Electrical Enclosures
- Fuses
- Motor Controls
- Reduced Voltage Starters
- Relays and Timers
- Transformers
- Line Reactors

- Power and transmission
- Bearings
- Couplings
- Gear Boxes/Gear Motors
- Sheaves and Belting
- Sprockets

- Other solutions
- Lubrication Systems
- Motor Bases
- Phase Converters
- Raceway Systems
- Terminal Blocks

