



## ORDERING INFORMATION

## STYLE A PLUG-IN

MODEL NUMBER	OPERATING VOLTAGE	TYPE OF ADJUSTMENT	DROP-OUT VOLTAGE		AGENCY APPROVAL	OUTPUT RATINGS
			1 Ø LOW	3 Ø LOW		
<b>SLA-120-ALA</b>	95-130 Adj.	Lock Shaft	79-108	85-117	—	DPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 2
<b>SLA-120-ASA</b>		Screwdriver				SPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 1
<b>SLA-120-ASB</b>						SPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 3
<b>SLA-230-ALA</b>	190-270 Adj.	Lock Shaft	158-224	171-243		DPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 2
<b>SLA-230-ASA</b>		Screwdriver				SPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 1
<b>SLA-230-ASB</b>						SPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 3
<b>SLA-380-ASA</b>	350-440 Adj.	Screwdriver	290-365	315-396	—	SPDT, 360 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 1
<b>SLA-440-ASA</b>	430-480 Adj.		357-398	387-432		
<b>SUA-120-ALA</b>	95-130 Adj.	Lock Shaft	79-108	85-117		SPDT, 345 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 1
<b>SUA-120-ALAU*</b>						
<b>SUA-230-ALA</b>	190-270 Adj.	Screwdriver	158-224	171-243		
<b>SUA-230-ALAU*</b>						
<b>SUA-380-ASA</b>	350-440 Adj.	Screwdriver	290-365	315-396		SPDT, 360 VA Inductive; 10 Amps Resistive @ 240 VAC, Figure 1
<b>SUA-440-ASA</b>	430-480 Adj.		357-398	387-432		

\*UL Listed only when used with RB-08 relay socket; 5 Amps Resistive @ 240 VAC. All voltages referenced on this page are phase-to-phase. Models also available with fixed operating voltages. Consult factory.

## STYLE E SURFACE MOUNTED ENCLOSURE

MODEL NUMBER	OPERATING VOLTAGE	DROP-OUT VOLTAGE		RESET	AGENCY APPROVAL	OUTPUT RATINGS
		1 Ø LOW	3 Ø LOW			
<b>SLA-120-ALE</b>	95-130 Adj.	79-108	85-117	Automatic		DPDT, 211 VA Inductive; 10 Amps Resistive @ 120 VAC, Figure 4
<b>SLA-120-ALER</b>				Manual		DPDT, 211 VA Inductive; 10 Amps Resistive @ 120 VAC, Figure 4
<b>SLA-230-ALE</b>	190-270 Adj.	158-224	171-243	Automatic		DPDT, 345 VA Inductive; 5 Amps Resistive @ 240 VAC, Figure 4
<b>SLA-230-ALER</b>				Manual		DPDT, 345 VA Inductive; 5 Amps Resistive @ 240 VAC, Figure 4
<b>SLA-380-ALE</b>	350-440 Adj.	290-365	315-396	Automatic		DPDT, 360 VA Inductive; 3 Amps Resistive @ 600 VAC, Figure 4
<b>SLA-380-ALER</b>				Manual		SPDT, 360 VA Inductive; 3 Amps Resistive @ 600 VAC, Figure 5
<b>SLA-440-ALE</b>	430-480 Adj.	357-398	387-432	Automatic		DPDT, 360 VA Inductive; 3 Amps Resistive @ 600 VAC, Figure 4
<b>SLA-440-ALER</b>				Manual		SPDT, 360 VA Inductive; 3 Amps Resistive @ 600 VAC, Figure 5
<b>SLA-575-ALE</b>	525-625 Adj.	436-519	473-563	Automatic		DPDT, 360 VA Inductive; 3 Amps Resistive @ 600 VAC, Figure 4

All voltage referenced are phase-to-phase.—Models also available with fixed operating voltages. Consult factory.

## STYLE N EPOXY ENCAPSULATED

MODEL NUMBER	OPERATING VOLTAGE	TYPE OF OPERATION	DROP-OUT VOLTAGE		AGENCY APPROVAL
			1 Ø LOW	3 Ø LOW	
<b>SLA-120-AFN</b>	120	Fixed	100	108	
<b>SLA-208-AFN</b>	208	Fixed	173	187	
<b>SLA-220-AFN</b>	220	Fixed	183	198	
<b>SLA-240-AFN</b>	240	Fixed	199	216	

All voltage referenced are phase-to-phase.