

**CROSS REFERENCE TO ROCKWELL
PART NUMBER PP7811**

Flexcore Split Core CT

- Seven Opening Sizes
- 1 or 5 Amp Secondaries
- 0.333V or 1.0V Secondaries
- Indoor or Outdoor Use



Flexible split-core opens with a twisting motion. Silicone rubber encapsulation protects against moisture, dirt, oil and corona. Remains flexible from -45° to +200°C.

FC ▲

SPECIFICATIONS

Insulation Level:	0.6kV, BIL 10kV Full Wave
Frequency:	50-400Hz
Thermal factor:	1.25 at 30°C, 1.0 at 55°C
Accuracy:	
200:5 thru 300:5	4%
400:5 thru 500:5	3%
600:5 thru 800:5	2%
1000:5 thru 6000:5	1%
Leads:	12 feet long with spade connectors, Black wire = X1, White wire = X2

ORDERING INFORMATION

To Order—Insert Number Code for Each Letter to Select Catalog Number.
Order Example: FC-1000/5-8

A - B - C

A	Model	
FC	Split core CT	
FCL	UL Listed (Indoor use only)	File E186575
B	Ratio	
	See chart for available sizes	
C	Inside Diameter (inches)	
	4, 6, 8, 11, 14, R , R411	
	(R= 2-3/4 x 6-5/8, R411= 4 x 11)	

AVAILABLE SIZES

Ratio	4"	6"	8"	11"	18"	R	R411	Burden
200/5	X	-	-	-	-	-	-	2VA
250/5	X	-	-	-	-	-	-	2VA
300/5	X	X	-	-	-	-	-	2VA
400/5	X	X	-	-	-	X	-	2VA
500/5	X	X	-	-	-	X	-	3VA
600/5	X	X	-	-	-	X	-	5VA
800/5	X	X	-	-	-	X	-	5VA
1000/5	X	X	X	-	-	X	-	5VA
1200/5	X	X	X	-	-	X	-	5VA
1500/5	X	X	X	X	-	X	X	15VA
1600/5	X	X	X	X	-	X	X	15VA
2000/5	X	X	X	X	X	X	X	25VA
2400/5	-	X	X	X	X	X	X	30VA
2500/5	-	X	X	X	X	X	X	35VA
3000/5	-	X	X	X	X	X	X	45VA
3500/5	-	X	X	X	X	X	X	45VA
4000/5	-	X	X	X	X	X	X	45VA
5000/5	-	X	X	X	X	X	X	45VA
6000/5	-	X	X	X	X	X	X	45VA