

**YA282N : 4/0 CU 2-HOLE LONG 1/2**



[www.fci.com](http://www.fci.com)

**BURNDY® PRODUCTS**

**Specifications**

<b>Dimensional</b>	
<b>Length (Barrel)</b>	Long Barrel
<b>Size (Wire)</b>	4/0 AWG
<b>Stud Hole (Size)</b>	1/2 in.
<b>Stud Hole (Spacing)</b>	1-3/4 in.
<b>Tongue Angle</b>	Straight
<b>Tongue Width (in)</b>	1.02 in.
<b>Wire Type</b>	Commercial Stranded Copper
<b>Strip Length (in)</b>	1-11/16 in.
<b>Physical</b>	
<b>Element A Index</b>	15
<b>Approvals / Certifications</b>	
<b>UL Listed</b>	Yes
<b>CSA Certified</b>	Yes
<b>Other Features</b>	
<b>UPC</b>	78181050365
<b>Keyword</b>	ya