

Product Details and Certifications

Cross Reference RA Part Number: PN-D12950

➔ Product: **140G-K-EXT3**

Description: Frame-K, Extend Terminal, 3 Pole, Qty 3



Representative Photo Only (actual product may vary based on configuration selections)


CIRCUIT BREAKER DATA

Bulletin Number	Bulletin 140G/140MG
Frame Size	K frame
Rated Current(A)	400 A
Number of Poles	3 Poles




ACCESSORY ITEMS

Extended Terminals	Frame-K, Extend Terminal, 3 Pole, Qty 3
--------------------	---


Extended Terminals

 Representative Photo	Description	Frame Size	3-Pole Cat. No. (Pkg. Qty. 3)	4-Pole Cat. No. (Pkg. Qty. 4)
	Extended Terminals for busbar or ring type connection <ul style="list-style-type: none"> G- & I-frame supplied with 100 mm phase barrier H- & J-frame supplied with insulator, 100 mm phase barrier, and terminal cover K- & N-/NS-frame supplied with insulator and 100 mm phase barrier M-frame terminals only 	G	140G-G-EXT3	140G-G-EXT4
		H	140G-H-EXT3	140G-H-EXT4
		I	140G-I-EXT3	140G-I-EXT4
		J	140G-J-EXT3	140G-J-EXT4
		K	140G-K-EXT3	140G-K-EXT4
		M	140G-M-EXT3	140G-M-EXT4
		N, NS	140G-N-EXT3	140G-N-EXT4

Spreader Terminals

 Representative Photo	Description	Frame Size	3-Pole Cat. No. (Pkg. Qty. 3)	4-Pole Cat. No. (Pkg. Qty. 4)
	Spreader Terminals for busbar or ring type connection <ul style="list-style-type: none"> G- & I-frame supplied with 200 mm phase barrier H- & J-frame supplied with insulator, 100 mm phase barrier, and terminal cover K- & N-/NS-frame supplied with insulator and 100 mm phase barrier M- & R-frame terminals only 	G	140G-G-EXS3	140G-G-EXS4
H		140G-H-EXS3	140G-H-EXS4	
I		140G-I-EXS3	140G-I-EXS4	
J		140G-J-EXS3	140G-J-EXS4	
K		140G-K-EXS3	140G-K-EXS4	
M		—	140G-M-EXS4	
N, NS		—	140G-N-EXS4	
 Representative Photo	Top Spreader Terminals for busbar or ring type connection <ul style="list-style-type: none"> M-frame terminals only 	M	140G-M-EXSLI3	—
		N, NS	140G-N-EXSLI3	—
 Representative Photo	Bottom Spreader Terminals for busbar or ring type connection <ul style="list-style-type: none"> N-/NS-frame supplied with insulator and 100 mm phase barrier 	M	140G-M-EXSLO3	—
		N, NS	140G-N-EXSLO3	—

Rear Terminals

 Representative Photo	Description	Frame Size	3-Pole Cat. No. (Pkg. Qty. 3)	4-Pole Cat. No. (Pkg. Qty. 4)
	Rear flat horizontal terminals	Rear flat horizontal terminals	N, NS	140G-N-TLH3
N, NS			140G-N-TLV3	140G-N-TLV4
R ★			140G-R-TLV3	140G-R-TLV4

★ 2000 A and 2500 A MCCBs only.