

Product Details and Certifications

Cross Reference RA Part Number: 1609-NMC A



Product: **1609-NMC**

Description: 1609- Network Management Card



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1609 Power Supplies
Accessory Selection	Individual Accessory Selection

SELECTION

1609 Accessories	(1) Network Management Card
------------------	-----------------------------

Industrial Uninterruptible Power Supply

Catalog Number Explanation/Product Selection/Accessories



Bulletin 1609-P Series — Industrial Uninterruptible Power Supply

- Rugged industrial design
- Tower/rack compatible
- Extended runtime
- Battery management system
- Hot-swappable batteries
- Comprehensive network management
- Remote monitoring/configuration
- Double conversion online
- Pure sine wave output
- Frequency and voltage regulation
- Automatic internal bypass

Certifications

UL Listed (File No. E190749, Guide YEDU)
 CSA Certified (File LR1234)

Standards Compliance

UL 1778
 CE
 CSA C22.2, No. 107
 FCC

Table of Contents

Overview this page
 Cat. No. Explanation this page
 Product Selection this page
 Accessories..... this page
 Specifications..... 8-33
 Approx. Dimensions . 8-34

The Bulletin 1609-P has multiple options for remote management. Please see page 8-28 for details.

Catalog Number Explanation

1609 – P 3000 N
 a b c

a

Power Supply Type	
Code	Description
P	Double Conversion Online Uninterruptible Power Supply

b

Rated Output Power	
Code	Description
3000	3000VA (2100 W)
5000	5000VA (3500 W)
8000	8000VA (6400 W)
10000	10000VA (8000 W)

c

Input/Output Voltage	
Code	Description
N	120V AC
E	208/230V AC
A	230V AC

Product Selection

Output Power	Input Voltage	Cat. No.
3000VA (2100 W)	120V AC	1609-P3000N
3000VA (2100 W)	230V AC	1609-P3000A
5000VA (3500 W)	208/230V AC	1609-P5000E
8000VA (6400 W)	208/230V AC	1609-P8000E
10000VA (8000 W)	208/230V AC	1609-P10000E

Accessories

Description	Cat. No.
Network management card (Standard on units 5 kVA and larger)	1609-NMC
Remote start cable	1609-RSC
Replacement battery	1609-PBAT
External battery pack	1609-PXBP
5000VA CCT (120V step down transformer)	1609-5000CCT
Rail kit	1609-PRK1
Hardwire kit (for 3 and 5 kVA units)	1609-HDK1
Service bypass switch (16 kVA)	1609-PSB1

