


# Product Details and Certifications

## Cross Reference RA Part Number: 193-BC8 A

 **Product: 193-BC8**

Description: Current Adjustment Shield (Pkg. Qty. 10) (for all 193-ED, 193-EE, 592-EE)



Representative Photo Only (actual product may vary based on configuration sections)

### ***OVERLOAD DATA***

---

Bulletin Number	193-IEC Overload Relay Accessories
Accessory Selection	Individual Accessory Selection











### ***SELECTION***

---

193 E1 Plus Accessories

## E1 Plus Electronic Overload Relays

## Accessories

	Description	For Use With	Pkg. Quantity	Cat. No.
	<b>DIN Rail/Panel Adapter</b> For separate mounting – can be mounted to top-hat rail EN 50 022-35	193-ED1_B, 193-EE_B, 193S-EE_B, 193-EE_Z, 592-EE_T	1	<b>193-EPB</b>
		193-ED1_D, 193-EE_D, 193S-EE_D		<b>193-EPD</b>
		193-EE_E, 193S-EE_E		<b>193-EPE</b>
	<b>Current Adjustment Shield</b> Prevents inadvertent adjustment of the current setting. Must be ordered in multiples of package quantities.	193-ED (all) 193-EE (all) 592-EE (all)	<b>10</b>	<b>193-BC8</b> 
	<b>External Reset Adapter</b> For enclosed, through-the-door reset applications. Use with external reset button.	193-ED (all) 193-EE_B, 193-EE_D, 193-EE_E 193-EE_Z	1	<b>193-ERA</b>
	<b>External Reset Button for Enclosed Devices</b>	193-E all	1	<b>800FM-R611</b> (Button)
				<b>800F-ATR08</b> (Rod)
	<b>Terminal Lugs</b> • Set of two • Protection class IP2X per IEC 60529 and DIN 40 050	100-D115, 100-D140, 100-D180, 100-D115E...D180E, 193-EC_F, 193-EE_F	2	<b>100-DTB180</b>
		100-D210...100-D420, 193-EC_G, 193-EF2C, 193-EE_G	2	<b>100-DTB420</b>
	<b>Terminal Lugs, Copper Frame</b> Set of three	100-D115E, 193-EC_F, 193-EE_F	3	<b>100-DLE110</b>
		100-D210...100-D420, 193-EC_G, 193-EE_G	3	<b>100-DL180</b>
		100-D210...100-D420, 193-EC_G, 193-EE_G	3	<b>100-DL420</b>
		100-D630, 100-D860, 193-EC_H, 193-EE_H	3	<b>100-DL630</b>
		100-D630, 100-D860, 193-EC_H, 193-EE_H	3	<b>100-DL860</b>
	<b>Terminal Covers</b> • Protection class IP20 per IEC 60529 and DIN 40 050 • For direct-on-line, reversing, two-speed, and wye-delta/star-delta assemblies	100-D115...100-D180, 193-EC_F, 193-EE_F	1	<b>100-DTC180</b>
		100-D210...100-D420, 193-EC_G, 193-EE_G	1	<b>100-DTC420</b>
		100-D630...100-D860, 193-EC_H, 193-EE_H	1	<b>100-DTC860</b>
	<b>DeviceNet Configuration Terminal</b> Used to interface with objects on a DeviceNet network. Includes 1 m communications cable (193-CB1).	193-EDN, 193-EC (all), 592-EC (all); 280/281/283/284 ArmorStart, 825-P	1	<b>193-DNCT</b>
	<b>1 meter communication cable, color-coded bare leads</b>	193-DNCT	1	193-CB1
	<b>1 meter communication cable, microconnector (male)</b>	193-DNCT	1	<b>193-CM1</b>
	<b>Panel Mount Adapter/Door Mount Bezel Kit</b>	193-DNCT	1	<b>193-DNCT-BZ1</b>

2