

Product Details and Certifications

Cross Reference RA Part Number: PN-100429



Product: **20-750-BNETIP**

Description: PF750-Series BACnet/IP Option



Representative Photo Only (actual product may vary based on configuration sections)

OPTION INFORMATION

Communication Kits

PowerFlex 750-Series AC Drives

Accessory Selection

Individual Accessory Selection

SELECTION

Communications Kits

Communication Option Kits and Accessories



Description	Cat. No.	Used with PowerFlex Common Bus Drive	
		753/755	755TM
BACnet/IP Option Module	20-750-BNETIP	✓	—
Coaxial ControlNet™ Option Module	20-750-CNETC	✓	✓
ControlNet™ Communication Adapter (Coax)	20-COMM-C	✓ ⁽¹⁾	—
DeviceNet™ Option Module	20-750-DNET	✓	✓
DeviceNet™ Communication Adapter	20-COMM-D	✓ ⁽¹⁾	—
Dual-port EtherNet/IP Option Module	20-750-ENETR	✓	✓
EtherNet/IP™ Communication Adapter	20-COMM-E	✓ ⁽¹⁾	—
HVAC Communication Adapter	20-COMM-H	✓ ⁽¹⁾	—
CANopen® Communication Adapter	20-COMM-K	✓ ⁽¹⁾	—
LonWorks® Communication Adapter	20-COMM-L	✓ ⁽¹⁾	—
Modbus/TCP Communication Adapter	20-COMM-M	✓ ⁽¹⁾	—
Profibus DPV1 Option Module	20-750-PBUS	✓	✓
Single-port Profinet I/O Option Module	20-750-PNET	✓	✓
Dual-port Profinet I/O Option Module	20-750-PNET2P	✓	✓
PROFIBUS™ DP Communication Adapter	20-COMM-P	✓ ⁽¹⁾	—
ControlNet™ Communication Adapter (Fiber)	20-COMM-Q	✓ ⁽¹⁾	—
RS485 DF1 Communication Adapter	20-COMM-S	✓ ⁽¹⁾	—
External Communications Kit Power Supply	20-XCOMM-AC-PS1	✓	—
DPI External Communications Kit	20-XCOMM-DC-BASE	✓	—
External DPI I/O Option Board ⁽²⁾	20-XCOMM-IO-OPT1	✓	—
Compact I/O™ Module (3 Channel)	1769-SM1	✓	—
Serial Null Modem Adapter	1203-SNM	✓	✓
Universal Serial Bus Converter ⁽³⁾	1203-USB	✓	✓
ControlNet T-tap Straight	1786-TPS	✓	✓

(1) Requires a Communication Carrier Card (20-750-20COMM or 20-750-20COMM-F1). Refer to the Communication Accessories table on page 62 for details.

(2) For use only with DPI External Communications Kits 20-XCOMM-DC-BASE.

(3) Includes 2 m USB, 20-HIM-H10 & 22-HIM-H10 cables.