

Product Details and Certifications

Cross Reference RA Part Number: PN-37835

 **Product: 20-HIM-A3**

Description: PowerFlex Architecture Class HIM, LCD Display, Full Numeric Keypad



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	20-HIM LCD Display HIM
Accessory Selection	Individual Accessory Selection

SELECTION

PowerFlex Loose Human Interface Modules and Kits

PowerFlex 7-Class Options

Human Interface Modules



Blank Plate



20-HIM-A3



20-HIM-A5



20-HIM-A6



20-HIM-C3S



20-HIM-C5S



20-HIM-C6S

Description	Cat. No.	Used with PowerFlex Drive					
		70	700	700H	700S	700L	753/755
No HIM (Blank Plate), Handheld/Local (Drive Mount)	20-HIM-A0	✓	✓	✓	✓	✓	✓
LCD Display, Full Numeric Keypad, Handheld/Local (Drive Mount)	20-HIM-A3	✓	✓	✓	✓	✓	
LCD Display, Programmer Only, Handheld/Local (Drive Mount)	20-HIM-A5	✓	✓	✓	✓	✓	
Enhanced, LCD, Full Numeric Keypad, Handheld/Local (Drive Mount)	20-HIM-A6	✓	✓	✓	✓	✓	✓
Remote (Panel Mount) LCD Display, Full Numeric Keypad★‡	20-HIM-C3S	✓	✓	✓	✓	✓	
Remote (Panel Mount) LCD Display, Programmer Only★‡	20-HIM-C5S	✓	✓	✓	✓	✓	
Enhanced, LCD, Full Numeric Keypad★‡	20-HIM-C6S	✓	✓	✓	✓	✓	✓

★ IP66, NEMA Type 4X/12—for indoor use only.

‡ Includes a 1202-C30 interface cable (3 m/9.8 ft) for connection to drive.

Human Interface Module (HIM) Accessories

Description	Cat. No.	Used with PowerFlex Drive					
		70	700	700H	700S	700L	753/755
Bezel Kit for LCD HIMs, NEMA Type 1‡	20-HIM-B1	✓	✓	✓	✓	✓	✓
PowerFlex HIM Interface Cable, 1 m (3.3 ft) ♣	20-HIM-H10	✓	✓	✓	✓	✓	✓
Comm Option Cable Kit (Male-Male)							
0.33 m (1.1 ft)	1202-C03	✓	✓	✓	✓	✓	✓
1 m (3.3 ft)	1202-C10	✓	✓	✓	✓	✓	✓
3 m (9.8 ft)	1202-C30	✓	✓	✓	✓	✓	✓
9 m (29.5 ft)	1202-C90	✓	✓	✓	✓	✓	✓
Cable Kit (Male-Female) △							
0.33 m (1.1 ft)	1202-H03	✓	✓	✓	✓	✓	✓
1 m (3.3 ft)	1202-H10	✓	✓	✓	✓	✓	✓
3 m (9.8 ft)	1202-H30	✓	✓	✓	✓	✓	✓
9 m (29.5 ft)	1202-H90	✓	✓	✓	✓	✓	✓
DPI™ Cable Kit with Connectors, Tools and 100 m (328 ft) Cable	1202-CBL-KIT-100M	✓	✓	✓	✓	✓	✓
DPI Cable Connector Kit	1202-TB-KIT-SET	✓	✓	✓	✓	✓	✓
DPI/SCANport™ One to Two Port Splitter Cable	1203-S03	✓	✓	✓	✓	✓	✓

‡ Includes a 1202-C30 interface cable (3 m/9.8 ft) for connection to drive.

♣ Required only when HIM is used as handheld or remote.

△ Required in addition to 20-HIM-H10 for distances up to a total maximum of 10 m (32.8 ft).