


V1k dv/dt Filters

Part Number	NEC Motor HP			Rated Current	Watts Loss	Dimensions (in.) Height x Width x Depth	Open		EX Model Part Number	EX Model List Price
	480V	600V	240V				Weight	List Price		
V1K2A00	0.75	1	-	2	75	9.00 x 5.50 x 7.25	8	\$ 448.00	V1K2A00EX	\$ 515.00
V1K3A00	1 - 1.5	2	0.5	3	75	9.00 x 5.50 x 7.25	8	\$ 457.00	V1K3A00EX	\$ 527.00
V1K4A00	2	3	0.75	4	75	9.00 x 5.50 x 7.25	8	\$ 468.00	V1K4A00EX	\$ 538.00
V1K6A00	3	-	1 - 1.5	6	80	9.00 x 5.50 x 7.25	8	\$ 480.00	V1K6A00EX	\$ 551.00
V1K8A00	5	5	2	8	90	9.00 x 5.50 x 7.25	8	\$ 488.00	V1K8A00EX	\$ 561.00
V1K12A00	7.5	10	3	12	95	9.00 x 5.50 x 7.25	8	\$ 507.00	V1K12A00EX	\$ 584.00
V1K16A00	10	-	5	16	95	9.00 x 5.50 x 8.25	12	\$ 513.00	V1K16A00EX	\$ 589.00
V1K18A00	10	15	-	18	110	9.00 x 5.50 x 8.25	12	\$ 566.00	V1K18A00EX	\$ 651.00
V1K21A00	15	-	-	21	110	9.00 x 5.50 x 8.25	12	\$ 640.00	V1K21A00EX	\$ 738.00
V1K25A00	15	20	7.5	25	110	9.00 x 5.50 x 8.25	12	\$ 684.00	V1K25A00EX	\$ 786.00
V1K27A00	20	25	-	27	110	9.00 x 5.50 x 8.25	14	\$ 711.00	V1K27A00EX	\$ 818.00
V1K35A00	25	30	10	35	130	12.00 x 8.00 x 9.00	17	\$ 741.00	V1K35A00EX	\$ 852.00
V1K45A00	30	40	15	45	135	12.00 x 8.00 x 9.00	17	\$ 770.00	V1K45A00EX	\$ 886.00
V1K55A00	40	50	20	55	145	12.00 x 8.00 x 9.00	23	\$ 795.00	V1K55A00EX	\$ 914.00
V1K80A00	50 - 60	75	25 - 30	80	255	12.00 x 8.00 x 9.00	23	\$ 1,121.00	V1K80A00EX	\$ 1,289.00
V1K110A00	75	100	40	110	245	12.00 x 8.00 x 10.25	40	\$ 1,317.00	V1K110A00EX	\$ 1,515.00
V1K130A00	100	125	50	130	270	8.50 x 11.00 x 9.50	55	\$ 1,540.00	V1K130A00EX	\$ 1,771.00
V1K160A00	125	150	60	160	260	8.50 x 11.00 x 10.50	60	\$ 1,698.00	V1K160A00EX	\$ 1,952.00
V1K200A00	150	200	75	200	265	8.50 x 11.00 x 10.25	60	\$ 1,850.00	V1K200A00EX	\$ 2,128.00
V1K250A00	200	250	100	250	290	8.50 x 11.00 x 10.25	65	\$ 1,901.00	V1K250A00EX	\$ 2,186.00
V1K305A00	250	300	-	305	325	8.75 x 11.00 x 12.25	80	\$ 2,067.00	V1K305A00EX	\$ 2,377.00
V1K362A00	300	350	150	362	300	8.50 x 11.75 x 12.00	80	\$ 2,366.00	V1K362A00EX	\$ 2,720.00
V1K420A00	350	450	-	420	450	10.00 x 11.75 x 13.75	95	\$ 2,741.00	V1K420A00EX	\$ 3,152.00
V1K480A00	400	500	200	480	475	10.00 x 11.75 x 13.75	100	\$ 2,926.00	V1K480A00EX	\$ 3,365.00
V1K600A00	500	600	-	600	515	12.75 x 15.00 x 13.75	130	\$ 3,064.00	V1K600A00EX	\$ 3,524.00
V1K750A00	600	700	-	750	770	12.75 x 15.00 x 14.75	135	\$ 5,002.00	V1K750A00EX	\$ 5,752.00

V1k Open Filter



*The V1k SCCR version is also available. For information, please contact the Technical Support.