

CROSS TO PN-61471

Product Details and Certifications

Product: 20F11ND027AA0NNNNN

Description: PowerFlex 753 AC Drive, with Embedded I/O, Air Cooled, AC Input with DC Terminals, Open Type, 27 Amps, 20HP ND, 15HP HD, 480 VAC, 3 PH, Frame 3, Filtered, CM Jumper Removed, DB Transistor, Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 753 AC Drive, with Embedded I/O
Voltage Class	480 VAC, 3 PH
Current / Power Rating	27 Amps, 20HP ND, 15HP HD
Enclosure Type	Open Type
Input Type	AC Input with DC Terminals
Frame Size	Frame 3
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	DB Transistor

Recommended Spare Parts

20-750-2262C-2R	1	PF750-24V I/O Module-2AI,2AO,6DI,2RO
20-750-2262D-2R	1	PF750-115V I/O Module-2AI,2AO,6DI,2RO
20-750-2263C-1R2T	1	PF750-24V I/O Module-2AI,2AO,6DI,1RO,2TO
20-750-ENC-1	1	PF750 Incremental Encoder Module
20-750-DENC-1	1	PF750 Dual Incremental Encoder Module
20-750-UFB-1	1	PF750 Universal Feedback Module
20-750-APS	1	PF750 24V Aux Power Supply Module
20-750-S	1	PF750 Safe Torque Off Module
20-750-S1	1	PF750 Safe Speed Monitor Module
20-750-FLNG1-F3	1	PF750 Flange Adapter, Type 1, Frame 3
20-750-EMC1-F3	1	PF750 EMC Plate & Cores, Frame 3
20-750-EMC2-F3	1	PF750 EMC Cores, Frame 3
20-750-NEMA1-F3	1	PF750 NEMA 1 Kit, Frame 3
20-750-CNETC	1	PF750-Series ControlNet Coax
20-750-DNET	1	PowerFlex 750-Series DeviceNet Option Card
20-750-20COMM	1	PowerFlex 750-Series 20-COMM-* Adapter Card
20-HIM-A6	1	PowerFlex Architecture Class Enhanced HIM, NEMA 1
20-HIM-C6S	1	PowerFlex Architecture Class Remote Enhanced HIM, IP66 (NEMA 4X/12) Indoor Use Only
SK-R1-MCB1-PF753	1	PF753 Main Control Board

SK-R1-TB-PF753	1	PF753 Main Control Board Terminal Blocks
SK-R1-POD1	1	PF750 Control Pod, Frames 2-7
SK-R1-BP1	1	PF750 Backplane Interface
SK-R1-CR1	1	PF750 Pod HIM Cradle
SK-R1-PC1	1	PF750 Power Interface Cable
SK-R1-PJ1-F25	1	PF750 Power Jumper Screws, Frames 2 - 5
SK-R1-TB-2262	1	PF750 2262 I/O Terminal Blocks
SK-R1-TB-APS	1	PF750 APS Terminal Block
SK-R1-TB-S	1	PF750 Safe Torque Off Terminal Block
SK-R1-TB-S1	1	PF750 Safe Speed Monitor Terminal Blocks
SK-R1-TB-ENC-1	1	PF750 Single Encoder Terminal Block
SK-R1-TB-DENC-1	1	PF750 Dual Encoder Terminal Block
SK-R1-CVR1-F3	1	PF750 Open / NEMA 1 Cover, Fr 3
SK-R9-CHSS1-F3	1	PF750 Open / NEMA 1 Chassis, Fr 3
SK-R9-FAN11-F3	1	PF750 Open/NEMA 1 Heatsink Fan Kit, Fr 3
SK-R9-FAN2-F23	1	PF750 Internal Fan Kit, Frames 2 and 3