

Product Details and Certifications

Product: 20F1AND186AN0NNNNN

Description: PowerFlex 753 AC Drive, with Embedded I/O, Air Cooled, AC Input with Precharge, no DC Terminals, Open Type, 186 Amps, 150HP ND, 125HP HD, 480 VAC, 3 PH, Frame 6, Filtered, CM Jumper Removed, None, Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 753 AC Drive, with Embedded I/O
Voltage Class	480 VAC, 3 PH
Current / Power Rating	186 Amps, 150HP ND, 125HP HD
Enclosure Type	Open Type
Input Type	AC Input with Precharge, no DC Terminals
Frame Size	Frame 6
Filtering & CMCap Config	Filtered, CM Jumper Removed
Dynamic Braking	None

Recommended Spare Parts

20-750-2262C-2R	1	PF750-24V I/O Module-2AI,2AO,6DI,2RO
20-750-2262D-2R	1	PF750-115V I/O Module-2AI,2AO,6DI,2RO
20-750-2263C-1R2T	1	PF750-24V I/O Module-2AI,2AO,6DI,1RO,2TO
20-750-ENC-1	1	PF750 Incremental Encoder Module
20-750-DENC-1	1	PF750 Dual Incremental Encoder Module
20-750-UFB-1	1	PF750 Universal Feedback Module
20-750-APS	1	PF750 24V Aux Power Supply Module
20-750-S	1	PF750 Safe Torque Off Module
20-750-S1	1	PF750 Safe Speed Monitor Module
20-750-FLNG4-F6	1	PF750 Flange Adapter, Type 4X, Frame 6
20-750-NEMA1-F6	1	PF750 NEMA 1 Kit, Frame 6
20-750-DCBB1-F6	1	PF750 DC bus bars, Frame 6
20-750-CNETC	1	PF750-Series ControlNet Coax
SK-R9-FAN11-F6	1	PF750 Series, Type 1 Heatsink Fan Kit, Frame 6
20-750-DNET	1	PowerFlex 750-Series DeviceNet Option Card
20-750-20COMM	1	PowerFlex 750-Series 20-COMM-* Adapter Card
20-HIM-A6	1	PowerFlex Architecture Class Enhanced HIM, NEMA 1
20-HIM-C6S	1	PowerFlex Architecture Class Remote Enhanced HIM, IP66 (NEMA 4X/12) Indoor Use Only
SK-R1-MCB1-PF753	1	PF753 Main Control Board

SK-R1-TB-PF753	1	PF753 Main Control Board Terminal Blocks
SK-R1-POD1	1	PF750 Control Pod, Frames 2-7
SK-R1-BP1	1	PF750 Backplane Interface
SK-R1-CR1	1	PF750 Pod HIM Cradle
SK-R1-PC1	1	PF750 Power Interface Cable
SK-R1-TB-2262	1	PF750 2262 I/O Terminal Blocks
SK-R1-TB-APS	1	PF750 APS Terminal Block
SK-R1-TB-S	1	PF750 Safe Torque Off Terminal Block
SK-R1-TB-S1	1	PF750 Safe Speed Monitor Terminal Blocks
SK-R1-TB-ENC-1	1	PF750 Single Encoder Terminal Block
SK-R1-TB-DENC-1	1	PF750 Dual Encoder Terminal Block
SK-R1-CVR1-F6	1	PF750 Open /NEMA 1 Cover, Fr 6
SK-R1-AD1-F67	1	PF750 Access Door, Frs 6 & 7
SK-R9-LEG1-F6	1	PF750 Leg, Frame 6
SK-R9-FAN2-F6	1	PF750 Internal Fan Kit, Frame 6
SK-R9-PCG1-DF6	1	PF750 Precharge Kit, Frame 6
SK-R9-FAN11-F6	1	PF750 Series, Type 1 Heatsink Fan Kit, Frame 6
20-750-AC TE1-F6	1	PF750, AC Pwr Term Extension, Fr 6
20-750-PTG1-F6	1	PF750, Pwr Term Guard, Fr 6