

2.3

Molded Case Circuit Breakers

Series C



Cross Reference RA Part PN-54773

2

Types KD, HKD and KDC Electronic Circuit Breakers with Interchangeable Trip Units—Four-Pole ^{①②}

Max. Cont. Ampere Rating at 40°C ^③	Circuit Breaker Frame Only			Digitrip RMS 310 Trip Unit Only ^④				Digitrip 310 Rating Plug Only			Standard Terminals Only See Page V4-T2-188 for Optional Terminals	
	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac	Standard Adjustable Short Time Pickup with I ² t Short Delay Ramp	Options Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I ² t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Ampere Rating	Fixed Rating Plug Catalog Number	Adjustable Rating Plug Ampere Rating		
												Catalog Number
125	KD4400F	HKD4400F	KDC4400F	KES4125LS	KES4125LSI	—	—	70	1KES070T	70/90/100/125 A1KES125T1	TA300K ^⑤	
								90	1KES090T		TA300K ^⑤	
								100	1KES100T		TA300K ^⑤	
								110	1KES110T		TA300K ^⑤	
								125	1KES125T		TA300K ^⑤	
250	KD4400F	HKD4400F	KDC4400F	KES4250LS	KES4250LSI	—	—	70	2KES070T	125/150/200/250 A2KES250T1	TA300K ^⑤	
								100	2KES100T		TA300K ^⑤	
								125	2KES125T		TA300K ^⑤	
								150	2KES150T		TA300K ^⑤	
								160	2KES160T		TA300K ^⑤	
								175	2KES175T		TA300K ^⑤	
								200	2KES200T		TA300K ^⑤	
								225	2KES225T		TA300K ^⑤	
400	KD4400F	HKD4400F	KDC4400F	KES4400LS	KES4400LSI	—	—	200	4KES200T	200/250/300/400 A4KES400T1	TA300K ^⑤	
								225	4KES225T		TA300K ^⑤	
								250	4KES250T		200/240/260/280 A4KES200T5	TA350K ^⑤
								300	4KES300T		TA350K ^⑤	
								350	4KES350T		320/340/360/380 A4KES300T5	TA350K ^⑤
								400	4KES400T		TA350K ^⑤	



Notes

- ① Trip unit includes protected neutral pole. Use corresponding three-pole trip unit if protected neutral pole is not required.
- ② Fully rated neutral pole protection is standard. For 50% rated protection on neutral pole, add Suffix E to four-pole trip unit catalog number.
- ③ Ampere rating is established by rating plug.
- ④ For AC use only.
- ⑤ Individually packed.
- ⑥ 3TA400K and 4TA400K terminal kits contain one terminal for each pole and one terminal cover.