

**QUICKLAG Industrial Circuit Breakers Accessories**

Cross-reference to Rockwell  
Part # PP1748

Accessory Type <sup>①</sup>	Catalog Number	Description	Order in Multiples of
Handle Locks: Non-padlockable	<b>QL1NPL</b>	QUICKLAG Type P, B, C – 1 Pole	10
	<b>QL23NPL</b>	QUICKLAG Type P, B, C – 2, 3 Poles	10
Handle Locks: Padlockable	<b>QL1PL</b>	QUICKLAG Type P, B, C – 1 Pole	10
	<b>QLPB123PL</b>	QUICKLAG Type P, B – 1, 2, 3 Poles	10
	<b>QC123PL</b>	QUICKLAG Type C – 1, 2, 3 Poles	10
	<b>QLGF12PL</b>	Ground Fault Padlock Device Type P, B – 1, 2 Poles	10
Handle Tie	<b>QL1HT</b>	QUICKLAG Handle Tie - 1 Pole	100
Mounting Hardware	<b>QCFLIP</b>	QUICKLAG Type C Face Mounting Clip	24
	<b>QC1FP</b>	QUICKLAG Type C Face Mounting Plate – 1 Pole	10
	<b>QC2FP</b>	QUICKLAG Type C Face Mounting Plate – 2 Poles	10
	<b>QC3FP</b>	QUICKLAG Type C Face Mounting Plate – 3 Poles	10
	<b>QC1FPLOFF</b>	QUICKLAG Type C Face Mounting Plate and Lock-off (Off Only) – 1 Pole	10
	<b>QC2FPLOFF</b>	QUICKLAG Type C Face Mounting Plate and Lock-off (Off Only) – 2 Pole	10
	<b>QC3FPLOFF</b>	QUICKLAG Type C Face Mounting Plate and Lock-off (Off Only) – 3 Poles	10
	<b>QCBCLIP</b>	QUICKLAG Type C Base Mounting Clamp	100
	<b>QC6BP</b>	QUICKLAG Base Mounting Plate – 6 Poles Total	10
	<b>QC4CONB</b>	QUICKLAG Type C Single Point Connector	10
	<b>QCDINADAPT</b>	QUICKLAG Type C DIN Rail Adapter	6
Dummy Breakers	<b>HQP1000</b>	QUICKLAG Type P	1
	<b>BAB1000</b>	QUICKLAG Type B	1
	<b>QC1000</b>	QUICKLAG Type C	1
	<b>QC30SAMPLE</b>	QUICKLAG Type C Clear Choice Breaker	4



**QL1NPL**



**QL23NPL**



**QL1PL**



**QLPB123PL**



**QC123PL**



**QL1HT**



**QCFLIP**



**QC1FP**



**QC2FP**



**QC3FP**



**QCBCLIP**



**QC6BP**



**QC4CONB**



**QCDINADAPT**

① See pages 7 and 8 for QCR and QCF accessories.