



PART NO.	CHG. LTR.	K.V.A.	PRIM. SEC.		HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	NAME PLATE	CAT. NO. REF.	REMARKS
			VOLTAGES	VOLTAGES								
X-231398	D	.750	220	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231399	D	.750	440	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231400	G	.750	600 550	120 110	60 50/60	7-1/8		6-1/8	4-3/8	45010-334-24	1497-N35	
X-231401	D	.350	220	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	
X-231402	D	.350	440	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	OBSELETE
X-231403	D	.350	550	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	
X-231404	D	.750	380	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231405	D	.550	160	110	42	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231406	D	.750	400	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231407	D	.750	550	220	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231408	D	.750	500	220	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231409	D	.750	500	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231410	D	.750	440	220	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231411	D	.750	480	220	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231412	D	.750	110	24	60	6-3/4		5-3/4	4	H-18969	NONE	NOTE 1- 10-32 UNF-2B
X-231413	E	.750	208	120	60	6-3/4		5-3/4	4	45010-334-22	1497-N33	
X-231414	E	.750	240	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231415	E	.750	480	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231416	F	.750	600	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231417	H	.750	380	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231418	J	.750	415	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231419	K	.750	480	240	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231420	E	.750	480	120	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231421	E	.750	240	24	60	6-3/4		5-3/4	4	H-18969	NONE	NOTE 1- 10-32 UNF-2B
X-231422	E	.750	120	120	60	6-3/4		5-3/4	4	H-18969	NONE	

PARTIALLY DISCONTINUED		
DISCONTINUED DATE: 1-83		
P.O.N.	ECN	NO.
75-37	7723-76	12
PARTS: X-231402		

REFERENCE REVISION AUTHORIZATION 17 2075-96 DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED XX: ± XXX: ± ANGLES: ±		CONT. XFMR. 0.750 KVA FRAME SIZE EQUIVALENT TO HEVI-DUTY SZ0 CONTROL TRANSFORMER DESIGN 		MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC. LOCATION: MILWAUKEE, WISCONSIN U.S.A. DR. D. EVANS DATE 7-8-96 DWG SIZE SHEET 1 OF 1 CHKD. <i>H. Mykelsen</i> DATE 3-27-97 APPD. <i>Joe Logigian</i> DATE 3-31-97 B X-231398-422	
--	--	--	--	--	--