



PART NO.	CHG. LTR.	K.V.A.	VOLTAGES		HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	NAME PLATE	CAT. NO. REF.	REMARKS
			PRIM.	SEC.								
X-231478	D	1.0	220	110	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231479	D	1.0	440	110	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231480	D	1.0	550	110	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231481	D	.500	220	110	25	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231482	D	.500	440	110	25	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231483	D	.500	550	110	25	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231484	E	1.0	380	110	50	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231485	D	1.0	440	220	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231486	D	1.0	400	110	50	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231487	D	1.0	380	220	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231488	D	1.0	550	220	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231489	E	1.0	500	110	50	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231490	D	1.0	440	24	60	6	1/2	5	3-1/4	H-18969	NONE	NOTE 1: 0.265 DIA. HOLE
X-231491	D	1.0	415	110	50	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231492	D	1.0	200	110	50/60	6-3/8	9/16	5-3/8	3-5/8	H-18969	NONE	
X-231493	D	1.0	208	110	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231494	D	1.0	208	120	60	6	1/2	5	3-1/4	45010-334-25	1497-N36	
X-231495	E	1.0	120	24	60	6	1/2	5	3-1/4	H-18969	NONE	NOTE 1: 0.265 DIA. HOLE
X-231496	G	1.0	208	120	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231497	G	1.0	240	120	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231498	G	1.0	480	120	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231499	G	1.0	600	120	60	6	1/2	5	3-1/4	45010-334-27	1497-N38	
X-231500	E	1.0	450	120	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231501	E	1.0	480	240	60	6	1/2	5	3-1/4	H-18969	NONE	
X-231502	E	1.0	550	120	60	6	1/2	5	3-1/4	H-18969	NONE	

REFERENCE		CONT. XFMR. 1.0 KVA FRAME SIZE EQUIVALENT TO HEVI-DUTY SZ0 CONTROL TRANSFORMER DESIGN				MAC DOCUMENT	
REVISION AUTHORIZATION 13 2075-96						THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX ± .XXX ± ANGLES: ±				LOCATION: MILWAUKEE, WISCONSIN U.S.A.			
		DR. D. EVANS	DATE 7-8-96	DWG. SIZE			
		CHKD. <i>M.A. J...</i>	DATE 8/29/96	SHEET 1 OF 1			
		APPD. <i>Joe Hajishawli</i>	DATE 3-31-97	B X-231478-502			