

Product Details and Certifications

Cross Reference RA Part Number: PN-23317

Product: **100S-D630ED22C**

Description: 100S-D Safety Contactor, IEC 630A, 110-130V AC/DC, 50/60Hz
Electronic Coil with Electronic Interface, 2 N.O. - 2 N.C.



Representative Photo Only (actual product may vary based on configuration sections)

CONTACTOR DATA

Bulletin Number	100S-D IEC Safety Contactor
Current Rating	630A
Coil Voltage	110-130V AC/DC 50Hz/60Hz
Number of Poles	3 Poles
Coil Type	Electronic Coil with Electronic Interface
Auxiliary Contact Configuration	2 N.O. - 2 N.C.

CERTIFICATIONS AND APPROVALS

UL
CSA
IEC
CE
For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

Safety Contactors



Bulletin	100S-C/104S-C	100S-D
Screw Terminals	✓	Thru-hole Threaded (630...860 A)
Max. Current I_e	97 A	860 A
Current Rating	9...97 A	115...860 A
Features	<ul style="list-style-type: none"> Positively guided/mechanically linked auxiliary contacts Front-mounted auxiliary contacts: <ul style="list-style-type: none"> Permanently fixed Protective cover to prevent manual operation Red contact housing for easy identification Incorporates IEC 947-5-1 "Mechanically Linked" symbol Optional gold-plated bifurcated versions AC and DC operating coils SUVA third-party certification 	<ul style="list-style-type: none"> Mirror contact performance on auxiliary contacts, which are required in feedback circuit for modern safety applications. The N.C. auxiliary contacts will not change state when a power contact welds. SUVA third-party certification AC and DC operating coils "Mirror Contact" symbol
Contacts	3 main poles with N.C. mechanically linked feedback contacts	3 main poles with N.C. mechanically linked feedback contacts
Coil Voltages	AC = 12...600V, 50/60Hz DC = 12...250V	<p>Conventional Coils Cat. Nos. 100S-D115...D180 AC: 24...550V, 50 Hz; 24...600V, 60Hz; 100...277V, 50/60Hz DC: 24...250V</p> <p>Electronic Coils Cat. Nos. 100S-D115...D300 AC: 24...500V, 50/60 Hz DC: 24...255V</p> <p>Cat. Nos. 100S-D420 AC: 42...500V 50/60 Hz DC: 48...255V</p> <p>Cat. Nos. 100S-D630...D860 AC: 100...600V, 50/60 Hz DC: 110...255V</p>
Optional Accessories	<ul style="list-style-type: none"> Side-mount auxiliary contacts Surge suppressors Electronic timers Mechanical interlocks 	<ul style="list-style-type: none"> Side-mount auxiliary contacts Surge suppressors IP20 terminal blocks Terminal shields Terminal covers Connecting components Terminal lugs Mechanical/electrical interlocks
Standards Compliance	EN/IEC 60947-4 IEC 60947-5-1 Annex L — Mechanically Linked Contacts IEC 60947-4-1 Annex H — Mirror Contacts UL 508 CSA C22.2 No. 14 EN50205	EN/IEC 60947-4 IEC 60947-4-1, Annex H — Mirror Contacts IEC 60947-4-1/A1: 2002-09, Annex F UL 508 CSA C22.2, No. 14
Certifications	<ul style="list-style-type: none"> cULus Listed (File No. E3125; Guide NLDX, NLDX7) SUVA Third-Party Certified CE Marked 	<ul style="list-style-type: none"> cULus Listed (File No. E3125; Guide No. NLDX, NLDX7) SUVA Third-Party Certified CE Marked CCC (115...180 A - conventional coil; 140...420 A - electronic coil)
Product Selection	Page 2-134	Page 2-151



Bulletin 100S-D — Safety Contactors

- 63...500 kW @ 400V
- 75...600 Hp @ 460V
- 100...700 Hp @ 575V
- Electronic and conventional coils
 - AC & DC
 - Integrated PLC interface
 - Low power pick-up & hold-in
 - Wide voltage ranges
- Complete range of accessories
- Environmentally friendly
- Compact dimensions

Bulletin 100S-D safety contactors were designed to address the needs of modern safety applications requiring feedback and monitoring of the energy isolating switchgear used in hazardous motion loads. The

100S-D meets these needs through its "mirror contact" design. If a power contact welds, the N.C. auxiliary contacts will not change state. This feature provides reliable indication about the open/closed status of the main power poles. In addition, the gold-plated bifurcated auxiliary contacts are ideally suited for low-energy applications or feedback control circuits with multiple series-connected N.C. auxiliary contacts.

Table of Contents

- Product Selection this page
- Accessories..... 2-153
- Approximate Dimensions..... 2-198

Standards Compliance

- IEC 60947-4-1
- IEC 60947-4 Annex F
- IEC 60947 Type "2"
- Coordination
- CSA C22.2 No. 14
- UL 508

Certifications

- CE Marked
- cULus Listed (File No. E 41850, Guide NLDX, NLDX7)
- SUVA Certified
- CCC (115...180 conventional coil; 140...420 electronic coil)

Your order must include: cat. no. of the contactor specified with coil voltage code and, if required, cat. no. of any accessories and/or replacement coils.

Product Selection
3-Pole AC-Operated Contactors

I_e [A]		Switching of 3-phase motors AC-2, AC-3										Auxiliary contacts		Cat. No. ➤
60 °C	40 °C	kW (50 Hz)*						Hp (60 Hz)				N.O.	N.C.⊗	
AC-3	AC-1	230V	400V	415V	500V	690V	1000V	200V	230V	460V	575V			
115	250	37	63	66/75	80	111	63	40	40	75	100	2	2	100S-D115⊗22BC
140	250	45	78	82/90	80/100‡	110/132‡	75	40	50	100	125	2	2	100S-D140⊗22BC
180	250	55	101	100	90/125‡	132/160‡	90	50	60	150	150	2	2	100S-D180⊗22BC
210	350	63	118	110	205	200	110	60	75	150	200	2	2	100S-D210⊗22BC
250	350	80	140	150	250	250	133	75	100	200	250	2	2	100S-D250⊗22BC
300	450	90	170	160	290	300	160	100	125	250	300	2	2	100S-D300⊗22BC
420	540	132	238	250	420	425	220	150	175	350	400	2	2	100S-D420⊗22BC
630	800	200	355	355	500	500	—	200	250	500	600	2	2	100S-D630⊗22BC
860	1000	250	500	500	500	600	—	250	300	600	700	2	2	100S-D860⊗22BC

* Preferred values according to IEC 60072-1.

⊗ The N.C. contacts meet IEC 60947-4 Annex F requirements for mirror contact performance. The N.C. mirror contacts are wired in series or parallel and must be used as monitoring contacts with feedback to the safety circuit.

‡ Higher kW rating only applies to contactors with electronic coil.

➤ If standard cross-stamped auxiliary contacts are required, remove the letter "B" before the letter "C" in the cat. no. Example: Cat. No. **100S-D115⊗22BC** becomes Cat. No. **100S-D115⊗22C**.

⊗Coil voltage code—see page 2-152



Bulletin 100S-D
IEC Contactors
 Product Selection



⊗ **Coil Voltage Codes for AC Control**

Conventional Coil	[V]	24	48	100	110	120	200	208	220 ...230	230	240	277	380 ...400	415	440	480	500	550	600
100S-D115...100S-D180	AC, 50 Hz	K	Y	—	D	—	—	—	A	—	T	—	N	B	G	—	M	C	—
	AC, 60 Hz	J	X	—	—	D	—	H	—	—	A	T	—	—	N	B	—	—	C
100S-D115	AC, 50/60 Hz	—	—	KP	KN	—	KG	—	KL	KF	KA	KT	—	—	—	—	—	—	—

Electronic Coil w/ PLC Interface§	[V]	24	42...64	100	110... 130	200	208... 277	200... 220	230... 250	277	380... 415	380... 440	440... 480	380... 500	500
100S-D95...100S-D300	AC, 50/60 Hz	EJ♣	EY	EP	ED	EG	EA	—	—	—	—	VN	—	EN	—
100S-D420	AC, 50/60 Hz	—	—	EP	ED	EG	EA	—	—	—	—	—	—	EN	—
100S-D630...100S-D860	AC, 50/60 Hz	—	—	EP	ED	—	—	EG	EA	ET	EN	—	EB	—	EM

2



§ Signal voltage of the Cat. No. 100S-D... electronic interface U_g : 24V DC/ I_g : 15 mA

Pick-up voltage: 13.0V DC...30.2V DC
 Drop-out voltage: -3.0V DC...+5.0V DC

♣ Not available with 100S-D300.

3-Pole DC-Operated Contactors

I_e [A]		Switching of 3-phase motors AC-2, AC-3										Auxiliary contacts		Conventional Coil Cat. No.	Electronic Coil Cat. No. >		
60 °C	40 °C	kW (50 Hz) *						Hp (60 Hz)				N.O.	N.C. * *				
		230V	400V	415V	500V	690V	1000V	200V	230V	460V	575V						
AC-3	AC-1																
115	250	37	63	66/75	80	111	63	40	40	75	100	2	2	100S-D115⊗33LC‡	100S-D115⊗22BC		
140	250	45	78	75	80/100§	110/132§	75	40	50	100	125	3	2/1L	100S-D140⊗33LC‡	100S-D140⊗22BC		
180	250	55	101	100	90/125§	132/160§	90	50	60	150	150	3	2/1L	100S-D180⊗33LC‡	100S-D180⊗22BC		
210	350	63	118	110	205	200	110	60	75	150	200	2	2	—	100S-D210⊗22BC		
250	350	80	140	150	250	250	133	75	100	200	250	2	2	—	100S-D250⊗22BC		
300	450	90	170	160	290	300	160	100	125	250	300	2	2	—	100S-D300⊗22BC		
420	540	132	238	250	420	425	220	150	175	350	400	2	2	—	100S-D420⊗22BC		
630	800	200	355	355	500	500	—	200	250	500	600	2	2	—	100S-D630⊗22BC		
860	1000	250	500	500	500	600	—	250	300	600	700	2	2	—	100S-D860⊗22BC		

* Preferred values according to IEC 60072-1.

⊗ The N.C. contacts meet IEC 60947-4 Annex F requirements for mirror contact performance. The N.C. mirror contacts are wired in series or parallel and must be used as monitoring contacts with feedback to the safety circuit.

‡ For conventional DC coil only. The pickup winding must be interconnected with the N.C. late-breaking auxiliary contacts.

§ Higher kW rating only applies to contactors with electronic coil.

> If standard cross-stamped front-mount auxiliary contacts are required, remove the letter "B" before the letter "C" in the Cat. No. Example: Cat. No. **100S-D115⊗22BC** becomes Cat. No. **100S-D115⊗22C**.



⊗ **Coil Voltage Codes for DC Control**

Conventional Coil	[V]	24	48	110	125	220	250
100S-D115...100S-D180	DC	ZJ	ZY	ZD	ZS	ZA	ZT

Electronic Coil w/ EI Interface ♣	[V]	24	48...72	110...130	200...255
100S-D115...100S-D300	DC	EZJ	EZY	EZD	EZA
100S-D420	DC	—	—	EZD	EZA
100S-D630...860	DC	—	—	ED	EA



♣ Signal voltage of the cat. no. 100S-S... electronic interface U_g : 24V DC/ I_g : 15 mA

Pick-up voltage: 13.0V DC...30.2V DC
 Drop-out voltage: -3.0V DC...+5.0V DC

