

Product Details and Certifications

Product: 140U-I6C3-D10

Description: 100A Molded Case Circuit Breaker, 3-Pole, Frame Size I, Medium Breaking Capacity

SYSTEM VOLTAGE DATA

| | |
|---------------------------------|----------------------------------|
| Supply Voltage, Maximum | 600V 60Hz |
| Maximum Available Fault Current | 100kA@240V, 65kA@480V, 25kA@600V |

CIRCUIT BREAKER

| | |
|-------------------------------|---|
| Circuit Breaker Type | Molded Case Circuit Breaker |
| Application | Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Fixed Magnetic) |
| Rated Operational Current (A) | 100A |
| Frame Size | Frame Size I |
| Magnetic Trip Current (A) | 700A Min - 1400A Max Fixed |
| Breaking Capacity | Medium Breaking Capacity |
| Certifications | UL 489, CSA 22.2 No. 5 |

FACTORY OPTIONS

| | |
|--|------|
| Factory Modifications - Left Front Mounting | None |
| Factory Modifications - Right Front Mounting | None |

TERMINAL LUG DATA

| | |
|------------------------|--------------------------|
| Important Information! | #14AWG - #1/0 AWG, Cu/Al |
|------------------------|--------------------------|

Dimensions and Weight

| | |
|-------------------|------------|
| Weight (kg / lbs) | 2.04 / 4.5 |
|-------------------|------------|
