

# Product Details and Certifications

Cross Reference RA Part Number: 1492-CE9 B

 **Product: 1492-CE9**

Description: CE9 White, No Bulk Pack ( Single Block)



Representative Photo Only (actual product may vary based on configuration sections)

## **BASE DATA**

---

Bulletin Number	1492 Terminal Block
Electrical Standards	UL
Type of Device	NEMA/EEMAC Terminal Block
Base Block Type	Single Circuit Insolation Switch Block

## **DETAIL DATA**

---

Screw Type	Knife Disconnect Isolating
Wire Range	#22 - #10 AWG
Voltage Rating	600V AC/DC
Color	White
Bulk Pack	No Bulk Pack ( Single Block)

## **CERTIFICATIONS AND APPROVALS**

---

UR

CSA

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/IFRAME/index.htm>

# NEMA/EEMAC Terminal Blocks

## Isolation Switch Blocks

	1492-CE9		1492-H7	
<p>Dimensions are not intended to be used for manufacturing purposes.  <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.</p>				
<b>Specifications</b>	<i>Knife disconnect isolating terminal block with screw terminal and wire clamp.</i>		<i>High-density isolating terminal block with finger-safe terminals.</i>	
Approvals	UL/CSA		UL/CSA/CE	
Voltage Rating	600V AC/DC		300V AC/DC	
Maximum Current	10 A		15 A	
Wire Range (Rated Cross Section)	#22...#10 AWG (0.5...6 mm <sup>2</sup> )		#30...#12 AWG (0.05...4 mm <sup>2</sup> )	
Wire Strip Length	0.38 in. (9.7 mm)		0.38 in. (9.7 mm)	
Recommended Tightening Torque	10...16 lb-in. (1.1...1.8 N•m)		3...7 lb-in. (0.3...0.8 N•m)	
Fuse Size (Not Supplied)	—		1/4 in. x 1-1/4 in. Dummy Fuse (Supplied)	
Density	16 pcs./ft (52/m)		33 pcs./ft (108/m)	
Insulation Temperature Range	-40...+221 °F (-40...+105 °C)		-40...+221 °F (-40...+105 °C)	
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pcs./Pkg.</b>	<b>Cat. No.</b>	<b>Pcs./Pkg.</b>
Terminal Block	1492-CE9	10	1492-H7	25
<b>Accessories (Accessories)</b>	<b>Cat. No.</b>	<b>Pcs./Pkg.</b>	<b>Cat. No.</b>	<b>Pcs./Pkg.</b>
Mounting Rails:				
A-B Rail	1492-N1	20	1492-N1	20
3 ft Rigid A-B Rail	1492-N22	20	1492-N22	20
3 ft High-Rise A-B Rail	1492-N44	2	1492-N44	2
Standoff Brackets (use every 12 in.)	1492-N25	2	1492-N25	2
1 m Symmetrical DIN	—	—	199-DR1	10
1 m Symmetrical DIN (Aluminum)	—	—	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)	—	—	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)	—	—	1492-DR7	2
End Barrier	1492-N17	50	1492-N37	50
End Anchors:				
A-B Rail	1492-N23	10	1492-N23	10
A-B Rail — Normal Duty	1492-N47	50	1492-N47	50
DIN Rail — Normal Duty	—	—	1492-EA35	50
DIN Rail — Heavy Duty	—	—	1492-EAH35	10
Side Jumpers:				
Side Jumper — 10-pole Uninsulated	—	—	1492-N49	10
	—	—	—	—
Fanning Strip (12-pole can cut to desired length)	—	—	1492-SJS	10
Marking Systems	—	—	1492-MS8X12 (56/sheet)	5