

Product Details and Certifications

Product: 140U-JD3D3-D12

Description: 125A Molded Case Circuit Breaker, 3-Pole, Frame Size JD, Standard Breaking Capacity

SYSTEM VOLTAGE DATA

| | |
|---------------------------------|---------------------------------|
| Supply Voltage, Maximum | 600V 60Hz |
| Maximum Available Fault Current | 65kA@240V, 35kA@480V, 18kA@600V |

CIRCUIT BREAKER

| | |
|-------------------------------|--|
| Circuit Breaker Type | Molded Case Circuit Breaker |
| Application | Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Adj. Magnetic) |
| Rated Operational Current (A) | 125A |
| Frame Size | Frame Size JD |
| Magnetic Trip Current (A) | 625A - 1250A Adjustable |
| Breaking Capacity | Standard Breaking Capacity |
| Certifications | UL 489, CSA 22.2 No. 5 |

FACTORY OPTIONS

| | |
|--|------|
| Factory Modifications - Left Front Mounting | None |
| Factory Modifications - Right Front Mounting | None |

TERMINAL LUG DATA

| | |
|------------------------|--------------------------------|
| Important Information! | Terminal Lugs are Not Provided |
|------------------------|--------------------------------|

Dimensions and Weight

| | |
|-------------------|-------------|
| Weight (kg / lbs) | 4.55 / 10.0 |
|-------------------|-------------|
