

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBLD4 A**

 **Product: 1492-EBLD4**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 20



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory

# Spring-Clamp Connection Terminal Blocks

## Multi-Circuit Feed-Through Blocks

	1492-LD4			1492-LTF3		
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.						
<b>Specifications</b>	Two-circuit feed-through terminal block			Three-circuit feed-through terminal block with multiple cross connection points		
Certifications		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>
Voltage Rating	600V AC/DC		800V AC/DC	300V AC/DC		500V AC/DC
Maximum Current	25 A	30 A	32 A	15 A	20 A	
Wire Range (Rated Cross Section)	#26...10 AWG		4 mm <sup>2</sup>	#26...12 AWG	2.5 mm <sup>2</sup>	
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)		
Density	49 pcs/ft (163 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Color	Grey	<b>1492-LD4</b>	20	<b>1492-LTF3</b>	25	
	Red	1492-LD4-RE	20	—	—	
	Blue	<b>1492-LD4-B</b>	20	—	—	
	Black	1492-LD4-BL	20	—	—	
	Green	1492-LD4-G	20	—	—	
	Yellow	<b>1492-LD4-Y</b>	20	—	—	
	Orange	<b>1492-LD4-OR</b>	20	—	—	
	Brown	1492-LD4-BR	20	—	—	
	White	<b>1492-LD4-W</b>	20	—	—	
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Mounting Rails						
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10		<b>199-DR1</b>	10	
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10		<b>1492-DR5</b>	10	
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2		<b>1492-DR6</b>	2	
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2		<b>1492-DR7</b>	2	
<b>End Barriers</b>	Grey	<b>1492-EBLD4</b>	20	<b>1492-EBLTF3</b>	20	
	Blue	1492-EBLD4-B	20	—	—	
	Yellow	1492-EBLD4-Y	20	—	—	
End Anchors and Retainers						
Screwless End Retainer	<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20	
DIN Rail — Normal Duty	<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100	
DIN Rail — Heavy Duty	<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50	
Jumpers						
Plug-in Center Jumper — 50-Pole	—	—		<b>1492-CJK5-50</b>	10	
Plug-in Center Jumper — 10-Pole	<b>1492-CJK6-10</b>	20		<b>1492-CJK5-10</b>	20	
Plug-in Center Jumper — 9-Pole	1492-CJK6-9	20		<b>1492-CJK5-9</b>	20	
Plug-in Center Jumper — 8-Pole	<b>1492-CJK6-8</b>	20		<b>1492-CJK5-8</b>	20	
Plug-in Center Jumper — 7-Pole	1492-CJK6-7	20		<b>1492-CJK5-7</b>	20	
Plug-in Center Jumper — 6-Pole	<b>1492-CJK6-6</b>	20		<b>1492-CJK5-6</b>	20	
Plug-in Center Jumper — 5-Pole	<b>1492-CJK6-5</b>	20		<b>1492-CJK5-5</b>	20	
Plug-in Center Jumper — 4-Pole	<b>1492-CJK6-4</b>	60		<b>1492-CJK5-4</b>	60	
Plug-in Center Jumper — 3-Pole	<b>1492-CJK6-3</b>	60		<b>1492-CJK5-3</b>	60	
Plug-in Center Jumper — 2-Pole	<b>1492-CJK6-2</b>	60		<b>1492-CJK5-2</b>	60	
Vertical Cross Connector*	—	—		<b>1492-CJL5D</b>	20	
Other Accessories						
Reducing Sleeves 26...24 AWG (0.13...0.2 mm <sup>2</sup> )	—	—		1492-PSLTF3-2	100	
Reducing Sleeves 22...20 AWG (0.25...0.5 mm <sup>2</sup> )	—	—		1492-PSLTF3-5	100	
Test Plug	<b>1492-TP23</b>	20		—	—	
Electrical Warning Plate	1492-EWPL6	20		—	—	
Marking Systems						
Snap-In Marker Cards	<b>1492-M6X10</b> (120/card)	5		<b>1492-SM5X10</b> (144/card)	5	
Snap-In Marker Cards	<b>1492-M6X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5	

\* Used to electrically connect 2 levels of 1492-LTF3