

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBTF3 B**

 **Product: 1492-EBTF3**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 50



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory



# Screw Connection Terminal Blocks

## Sensor Blocks

1492-WTF3...

1492-WTS3...

Dimensions are not intended to be used for manufacturing purposes.  
**Note:** Height dimension is measured from top of rail to top of terminal block.



Specifications	Three-circuit terminal block.			Three-level sensor block.		
Certifications		CSA	IEC		CSA	IEC
Voltage Rating	300V AC/DC		250V AC/DC	300V AC/DC		250V AC/DC
Maximum Current	10 A		24 A	10 A		24 A
Wire Range (Rated Cross Section)	#26...14 AWG		0.5...2.5mm <sup>2</sup>	#26...14 AWG		0.5...2.5mm <sup>2</sup>
Recommended Tightening Torque	4.2...4.6 lb•in (0.5 N•m)			4.2...4.6 lb•in (0.5 N•m)		
Density	60 pcs/ft (197 pcs/m)			60 pcs/ft (197 pcs/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)			-40...+195 °F (-40...+90 °C)		
Indicator Type WTF3/WTS3	No indicator			No indicator		
WTF3LP/WTS3LP	Red LED for PNP devices (10...50V)			Red LED for PNP devices (10...50V)		
WTF3LN/WTS3LN	Red LED for NPN devices (10...50V)			Red LED for NPN devices (10...50V)		
Leakage Current WTF3/WTS3	—			—		
WTF3LP/WTS3LP	2.69 mA @ 50V			2.69 mA @ 50V		
WTF3LN/WTS3LN	2.69 mA @ 50V			2.69 mA @ 50V		
Wire Strip Length	0.31 in. (8 mm)			0.31 in. (8 mm)		
Short-Circuit Current Rating	See page 12-42					

Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color: Grey	<b>1492-WTF3</b>	50	<b>1492-WTS3</b>	50
Blue	—	—	<b>1492-WTS3-B</b>	50
Grey for PNP devices	<b>1492-WTF3LP</b>	50	<b>1492-WTS3LP</b>	50
Grey for NPN devices	1492-WTF3LN	50	<b>1492-WTS3LN</b>	50
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails:				
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10	<b>199-DR1</b>	10
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2
<b>End Barrier</b>	<b>1492-EBTF3</b>	50	<b>1492-EBTS3</b>	50
End Anchors and Retainers:				
Screwless End Retainer	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20
DIN Rail — Normal Duty	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100
DIN Rail — Heavy Duty	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50
Jumpers:				
Center Jumper — 50-pole	<b>1492-CJT5-50</b>	5	<b>1492-CJT5-50</b>	5
Center Jumper — 10-pole	<b>1492-CJT5-10</b>	10	<b>1492-CJT5-10</b>	10
Center Jumper — 3-pole	1492-CJT5-3	10	1492-CJT5-3	10
Center Jumper — 2-pole	<b>1492-CJT5-2</b>	10	<b>1492-CJT5-2</b>	10
Center Jumper Link	<b>1492-CJL5</b>	10	<b>1492-CJL5</b>	10
Center Jumper Cover — Red	<b>1492-CJCR5</b>	10	<b>1492-CJCR5</b>	10
Center Jumper Cover — Blue	<b>1492-CJCB5</b>	10	<b>1492-CJCB5</b>	10
Side — 20-pole Insulated Red	<b>1492-SJT5-20-R</b>	10	<b>1492-SJT5-20-R</b>	10
Side — 20-pole Insulated Blue	<b>1492-SJT5-20-B</b>	10	<b>1492-SJT5-20-B</b>	10
Other Accessories:				
Partition Plate	<b>1492-PPTS3</b>	50	<b>1492-PPTS3</b>	50
Test Plug Adapter	<b>1492-TA285</b>	10	<b>1492-TA285</b>	10
Electrical Warning Plate				
4-Pole	1492-EWP5-4	10	1492-EWP5-4	10
1-Pole	1492-EWP5	10	1492-EWP5	10
Marking Systems:				
Snap-in Marker Card	<b>1492-MS5X9 (80/card)</b>	5	<b>1492-MS5X9 (80/card)</b>	5

