


Product Details and Certifications

Cross Reference RA Part Number: 1492-CE6 B



Product: **1492-CE6**

Description: CE6 White, No Bulk Pack (Single Block)



Representative Photo Only (actual product may vary based on configuration sections)

BASE DATA

Bulletin Number	1492 Terminal Block
Electrical Standards	UL
Type of Device	NEMA/EEMAC Terminal Block
Base Block Type	Single Circuit Open Construction Block

DETAIL DATA

Screw Type	Screw Terminal w/ Wire Clamp
Features	Fuse Block
Wire Range	#22 - #10 AWG
Voltage Rating	600V AC/DC
Color	White
Bulk Pack	No Bulk Pack (Single Block)

CERTIFICATIONS AND APPROVALS

UR

CSA

For UL Certifications Directory:



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>



1492-CE6

1492-UF3

Dimensions are not intended to be used for manufacturing purposes.
Note: Height dimension is measured from top of rail to top of terminal block.



Specifications	13/32" x 1-1/2" fuse block with screw terminals and wire clamp.		GMT-style fuse block with blown fuse alarm circuit, finger-safe.	
Approvals	UL/CSA		UL/CE	
Voltage Rating	600V AC/DC		125V AC, 60V DC	
Maximum Current	10 A		4 A	
Wire Range (Rated Cross Section)	#22...#10 AWG (0.5...6 mm ²)		#30...#12 AWG (0.05...4 mm ²)	
Wire Strip Length	0.38 in. (9.7 mm)		0.38 in. (9.7 mm)	
Recommended Tightening Torque	10...16 lb-in. (1.1...1.8 N•m)		3...7 lb-in. (0.3...0.8 N•m)	
Fuse Size (Not Supplied)	13/32 in. x 1-1/2 in. Fuse		Bussmann GMT-Type Alarm Fuse	
Leakage Current (Indicator Circuit)	-		-	
Density	16 pcs./ft (52/m)		40 pcs./ft (131/m)	
Insulation Temperature Range	-40...+221 °F (-40...+105 °C)		-40...+221 °F (-40...+105 °C)	
Terminal Blocks	Cat. No.	Pcs./ Pkg.	Cat. No.	Pcs./ Pkg.
Terminal Block	1492-CE6	10	1492-UF3	40
Terminal Block: Two 3' Rails White	1492-CE695	1	-	-
Accessories (Accessories)	Cat. No.	Pcs./ Pkg.	Cat. No.	Pcs./ Pkg.
Mounting Rails:				
A-B Rail	1492-N1	20	1492-N1	20
3 ft Rigid A-B Rail	1492-N22	20	1492-N22	20
3 ft High-Rise A-B Rail	1492-N44	2	1492-N44	2
Standoff Brackets (use every 12 in.)	1492-N25	2	1492-N25	2
1 m Symmetrical DIN	-	-	199-DR1	10
1 m Symmetrical DIN (Aluminum)	-	-	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)	-	-	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)	-	-	1492-DR7	2
End Barrier	1492-N17	50	Not Required	-
End Anchors:				
A-B Rail	1492-N23	10	1492-N23	10
A-B Rail – Normal Duty	1492-N47	50	1492-N47	50
DIN Rail – Normal Duty	-	-	1492-EA35	50
DIN Rail – Heavy Duty	-	-	1492-EAH35	10
Side Jumpers:				
Side Jumper – 10-pole Uninsulated	-	-	1492-N46	10
Fuse Puller	1492-N12	50	-	-
Marking Systems	-	-	1492-MN81	5

