

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-FPK2120 A**



**Product: 1492-FPK2120**

Description: 1492 Terminal Block, Fuse Plug with Blown Fuse Indication (60 - 150 V), Black



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory

# Screw Connection Terminal Blocks

## Plug-In Style Terminal Blocks

	1492-J3P			1492-J3PTP			1492-JD3P		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
<b>Specifications</b>	Selectable component plug-in terminal block			Selectable component plug-in terminal block with test plug socket			Two Circuit selectable component plug-in terminal block		
<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>
<b>Voltage Rating</b>	600V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC		500V AC/DC	300V AC/DC		500V AC/DC
<b>Maximum Current</b>	20 A	10 A	24 A	20 A	10 A	24 A	20 A		24 A
<b>Wire Range (Rated Cross Section)</b>	#30...12 AWG		2.5 mm <sup>2</sup>	#30...12 AWG		2.5 mm <sup>2</sup>	#24...12 AWG	#30...12 AWG	2.5 mm <sup>2</sup>
<b>Wire Strip Length</b>	0.39 in. (10 mm)			0.39 in. (10 mm)			0.31 in. (8 mm)		
<b>Recommended Tightening Torque</b>	4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)		
<b>Density</b>	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Short-Circuit Current Rating</b>	See page 12-42								
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Color:</b>	Grey	<b>1492-J3P</b>	100		<b>1492-J3PTP</b>	100		<b>1492-JD3P</b>	50
	Red	1492-J3P-RE	100		—	—		—	—
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Mounting Rails:</b>									
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>	10		<b>199-DR1</b>	10		<b>199-DR1</b>	10
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10
1 m Hi-Rise Sym. DIN (Aluminum)		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2
<b>End Barriers</b>		<b>1492-EBJ3</b>	50		<b>1492-EBJ3</b>	50		<b>1492-EBJD3P</b>	20
<b>End Anchors and Retainers:</b>		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20
<b>Screwless End Retainer</b>									
DIN Rail — Normal Duty		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100
DIN Rail — Heavy Duty		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50
<b>Jumpers* †:</b>		<b>1492-CJLJ5-50</b>	10		<b>1492-CJLJ5-50</b>	10		—	—
Center Jumper — 50-Pole									
Center Jumper — 10-Pole		<b>1492-CJLJ5-10</b>	20		<b>1492-CJLJ5-10</b>	20		<b>1492-CJJ5-10</b>	20
Center Jumper — 9-Pole		1492-CJLJ5-9	20		1492-CJLJ5-9	20		—	—
Center Jumper — 8-Pole		<b>1492-CJLJ5-8</b>	20		<b>1492-CJLJ5-8</b>	20		—	—
Center Jumper — 7-Pole		<b>1492-CJLJ5-7</b>	20		<b>1492-CJLJ5-7</b>	20		—	—
Center Jumper — 6-Pole		<b>1492-CJLJ5-6</b>	20		<b>1492-CJLJ5-6</b>	20		—	—
Center Jumper — 5-Pole		<b>1492-CJLJ5-5</b>	20		<b>1492-CJLJ5-5</b>	20		—	—
Center Jumper — 4-Pole		<b>1492-CJLJ5-4</b>	60		<b>1492-CJLJ5-4</b>	60		<b>1492-CJJ5-4</b>	50
Center Jumper — 3-Pole		<b>1492-CJLJ5-3</b>	60		<b>1492-CJLJ5-3</b>	60		<b>1492-CJJ5-3</b>	50
Center Jumper — 2-Pole		<b>1492-CJLJ5-2</b>	60		<b>1492-CJLJ5-2</b>	60		<b>1492-CJJ5-2</b>	50
<b>Screw Type Jumper Notching Tool</b>		—	—		—	—		<b>1492-T1</b>	1
<b>Other Accessories:</b>		<b>1492-EBJ16</b>	20		<b>1492-EBJ16</b>	20		<b>1492-PPJD3P</b>	20
<b>Partition Plate</b>									
Test Plug		—	—		<b>1492-TP23</b>	20		—	—
Disconnect Plug		<b>1492-DPL</b>	50		<b>1492-DPL</b>	50		<b>1492-DPL</b>	50
Component Plug		<b>1492-CPL</b>	50		<b>1492-CPL</b>	50		<b>1492-CPL</b>	50
<b>Fuse Plug</b>		<b>1492-FPK2</b>	20		<b>1492-FPK2</b>	20		<b>1492-FPK2</b>	20
Without Blown Fuse Indicator									
10...36V Blown Fuse Indicator		<b>1492-FPK224</b>	20		<b>1492-FPK224</b>	20		<b>1492-FPK224</b>	20
35...70V Blown Fuse Indicator		1492-FPK248	20		1492-FPK248	20		1492-FPK248	20
<b>60...150V Blown Fuse Indicator</b>		<b>1492-FPK2120</b>	20		<b>1492-FPK2120</b>	20		<b>1492-FPK2120</b>	20
140...250V Blown Fuse Indicator		<b>1492-FPK2250</b>	20		<b>1492-FPK2250</b>	20		<b>1492-FPK2250</b>	20
<b>Marking Systems:</b>		<b>1492-M5X12</b> (144/card)	5		<b>1492-M5X12</b> (144/card)	5		<b>1492-SM5X10</b> (144/card)	5
Snap-in marker cards									
Snap-in marker cards		<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5



\* Cat. nos. 1492-J3P and J3PTP use screwless center jumpers. Cat. No. 1492-JD3P uses a screw-type center jumper.

† Use of Center Jumpers may affect spacings, requiring derating of terminal blocks. See the Terminal Block selection guide, pub. no. 1492-SG008\*.

