

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-CJL12-2 A**

 **Product: 1492-CJL12-2**

Description: Plug-In Center Jumper, 12 mm Center to Center,  
2 Poles, Gray



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 IEC Terminal Block Accessories
Accessory Selection	Individual Accessory Selection




## ***SELECTION***

---

Screw Type Center Jumpers

# Spring-Clamp Connection Terminal Blocks

## Standard Feed-Through Blocks

	1492-L16			1492-L16D*			1492-L35					
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.												
<b>Specifications</b>	Feed-through terminal block			Power distribution block with center jumper connection/feed			Feed-through terminal block					
<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>	
<b>Voltage Rating</b>	600V AC/DC			800V AC/DC	550V AC/DC	600V AC/DC			800V AC/DC	690V AC/DC		
<b>Maximum Current</b>	65 A			76 A	66 A	65 A			76 A	120 A	125 A	109 A
<b>Wire Range (Rated Cross Section)</b>	#14...4 AWG			16 mm <sup>2</sup>	16 mm <sup>2</sup> (16...6 AWG)	#14...4 AWG			16 mm <sup>2</sup>	#12...2 AWG	35 mm <sup>2</sup>	35 mm <sup>2</sup> (14...2 AWG)
<b>Wire Strip Length</b>	0.70 in. (18 mm)			0.70 in. (18 mm)			0.98 in. (25 mm)					
<b>Density</b>	25 pcs/ft (82 pcs/m)			20 pcs/ft (66 pcs/m)			18 pcs/ft (62 pcs/m)					
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)					
<b>Short-Circuit Current Rating</b>	See page 12-78											
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Color</b>	Grey	<b>1492-L16</b>	25		<b>1492-L16D*</b>	20		<b>1492-L35</b>	10			
	Red	1492-L16-RE	25		—	—		1492-L35-RE	10			
	Blue	1492-L16-B	25		—	—		1492-L35-B	10			
	Black	1492-L16-BL	25		—	—		1492-L35-BL	10			
	Green	1492-L16-G	25		—	—		1492-L35-G	10			
	Yellow	1492-L16-Y	25		—	—		1492-L35-Y	10			
	Orange	1492-L16-OR	25		—	—		1492-L35-OR	10			
	Brown	1492-L16-BR	25		—	—		1492-L35-BR	10			
	White	1492-L16-W	25		—	—		1492-L35-W	10			
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Mounting Rails</b>												
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>	10		<b>199-DR1</b>	10		<b>199-DR1</b>	10			
1 m Symmetrical Heavy Duty DIN (Steel, Unslotted)		<b>199-DR4</b>	5		<b>199-DR4</b>	5		<b>199-DR4</b>	5			
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10			
1 m Hi-Rise Symmetrical DIN (Aluminum)		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2			
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2			
1 m Symmetrical Heavy Duty DIN (Copper, Unslotted)		1492-DR8	5		1492-DR8	5		1492-DR8	5			
1 m Symmetrical Heavy Duty DIN (Steel Slotted)		<b>1492-DR9</b>	5		<b>1492-DR9</b>	5		<b>1492-DR9</b>	5			
<b>End Barriers</b>	Grey	<b>1492-EBL16</b>	20		Integrated to Block	—		Integrated to Block	—			
	Blue	1492-EBL16-B	20		—	—		—	—			
	Yellow	<b>1492-EBL16-Y</b>	20		—	—		—	—			
<b>End Anchors and Retainers</b>												
Screwless End Retainer		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20			
DIN Rail — Normal Duty		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100			
DIN Rail — Heavy Duty		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50			
<b>Jumpers</b>												
Plug-in Center Jumper — 2-Pole		<b>1492-CJL12-2</b>	25		*	—		<b>1492-CJL16-2</b>	10			
<b>Other Accessories</b>												
Test Plug		<b>1492-TP23</b>	20		<b>1492-TP23</b>	20		<b>1492-TP23</b>	20			
Test Adapter		—	—		—	—		—	—			
Electrical Warning Plate		1492-EWPL12	20		1492-EWPL12	20		1492-EWPL16	20			
<b>Marking Systems</b>												
Snap-In Marker Cards‡		<b>1492-M7X12</b> (108/card)	5		<b>1492-M7X12</b> (108/card)	5		<b>1492-M7X12</b> (108/card)	5			
Snap-In Marker Cards		<b>1492-M8X5</b> (160/card)	5		<b>1492-M8X5</b> (160/card)	5		<b>1492-M8X5</b> (160/card)	5			
Hinged Marker Cards		<b>1492-MH5X15</b> (96/card)	5		<b>1492-MH5X15</b> (96/card)	5		<b>1492-MH5X15</b> (96/card)	5			

\* Can be electrically connected through center jumper for power distribution to 1492 - L3, L3Q, L4, L4T, L4Q, L6, and L6T terminal blocks. See page 12-55 for distribution guidelines.

\* Use defined center jumper for standard terminal blocks when connecting for power distribution.

‡ May only be mounted in terminal block corner marking positions.

