


Product Details and Certifications

Cross Reference RA Part Number: 1492-CJL16-2 A

 **Product: 1492-CJL16-2**

Description: Plug-in Center Jumper, 16 mm Center to Center,
2 Poles, Gray



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 IEC Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

Screw Type Center Jumpers

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L16			1492-L16D*			1492-L35					
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
	Specifications Feed-through terminal block			Power distribution block with center jumper connection/feed			Feed-through terminal block					
Certifications												
Voltage Rating	600V AC/DC			600V AC/DC			600V AC/DC			600V AC/DC		
Maximum Current	65 A			65 A			120 A			125 A		
Wire Range (Rated Cross Section)	#14...4 AWG			#14...4 AWG			#12...2 AWG			35 mm ²		
Wire Strip Length	0.70 in. (18 mm)			0.70 in. (18 mm)			0.98 in. (25 mm)			0.98 in. (25 mm)		
Density	25 pcs/ft (82 pcs/m)			20 pcs/ft (66 pcs/m)			18 pcs/ft (62 pcs/m)			18 pcs/ft (62 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-78											
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-L16	25		1492-L16D*	20		1492-L35	10		1492-L35	10
	Red	1492-L16-RE	25		—	—		1492-L35-RE	10		1492-L35-RE	10
	Blue	1492-L16-B	25		—	—		1492-L35-B	10		1492-L35-B	10
	Black	1492-L16-BL	25		—	—		1492-L35-BL	10		1492-L35-BL	10
	Green	1492-L16-G	25		—	—		1492-L35-G	10		1492-L35-G	10
	Yellow	1492-L16-Y	25		—	—		1492-L35-Y	10		1492-L35-Y	10
	Orange	1492-L16-OR	25		—	—		1492-L35-OR	10		1492-L35-OR	10
	Brown	1492-L16-BR	25		—	—		1492-L35-BR	10		1492-L35-BR	10
	White	1492-L16-W	25		—	—		1492-L35-W	10		1492-L35-W	10
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10		199-DR1	10
1 m Symmetrical Heavy Duty DIN (Steel, Unslotted)		199-DR4	5		199-DR4	5		199-DR4	5		199-DR4	5
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10		1492-DR5	10
1 m Hi-Rise Symmetrical DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2		1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2		1492-DR7	2
1 m Symmetrical Heavy Duty DIN (Copper, Unslotted)		1492-DR8	5		1492-DR8	5		1492-DR8	5		1492-DR8	5
1 m Symmetrical Heavy Duty DIN (Steel Slotted)		1492-DR9	5		1492-DR9	5		1492-DR9	5		1492-DR9	5
End Barriers	Grey	1492-EBL16	20		Integrated to Block	—		Integrated to Block	—		Integrated to Block	—
	Blue	1492-EBL16-B	20		—	—		—	—		—	—
	Yellow	1492-EBL16-Y	20		—	—		—	—		—	—
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50
Jumpers												
Plug-in Center Jumper — 2-Pole		1492-CJL12-2	25		*	—		1492-CJL16-2	10		1492-CJL16-2	10
Other Accessories												
Test Plug		1492-TP23	20		1492-TP23	20		1492-TP23	20		1492-TP23	20
Test Adapter		—	—		—	—		—	—		—	—
Electrical Warning Plate		1492-EWPL12	20		1492-EWPL12	20		1492-EWPL16	20		1492-EWPL16	20
Marking Systems												
Snap-In Marker Cards‡		1492-M7X12 (108/card)	5		1492-M7X12 (108/card)	5		1492-M7X12 (108/card)	5		1492-M7X12 (108/card)	5
Snap-In Marker Cards		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5
Hinged Marker Cards		1492-MH5X15 (96/card)	5		1492-MH5X15 (96/card)	5		1492-MH5X15 (96/card)	5		1492-MH5X15 (96/card)	5

* Can be electrically connected through center jumper for power distribution to 1492 - L3, L3Q, L4, L4T, L4Q, L6, and L6T terminal blocks. See page 12-55 for distribution guidelines.

* Use defined center jumper for standard terminal blocks when connecting for power distribution.

‡ May only be mounted in terminal block corner marking positions.

