

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBL2 A**

 **Product: 1492-EBL2**

Description: 1492 Terminal Block, End Barrier, Gray ( Standard), Qty.50



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection




## ***SELECTION***

---

1492 Accessory

# Spring-Clamp Connection Terminal Blocks

## Standard Feed-Through Blocks

	1492-L2				1492-L2T				1492-L2Q			
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.												
<b>Specifications</b>	<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 2 connection points on one side</i>				<i>Feed-through terminal block with 2 connection points per side</i>			
<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>
<b>Voltage Rating</b>	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC
<b>Maximum Current</b>	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A
<b>Wire Range (Rated Cross Section)</b>	#26...14 AWG		1.5 mm <sup>2</sup>	1.5 mm <sup>2</sup>	#26...14 AWG		1.5 mm <sup>2</sup>	1.5 mm <sup>2</sup>	#26...14 AWG		1.5 mm <sup>2</sup>	1.5 mm <sup>2</sup>
<b>Wire Strip Length</b>	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
<b>Density</b>	87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)			
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
<b>Terminal Blocks</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>
<b>Color</b>	Grey	<b>1492-L2</b>		50		<b>1492-L2T</b>		50		<b>1492-L2Q</b>		50
	Red	<b>1492-L2-RE</b>		50		<b>1492-L2T-RE</b>		50		<b>1492-L2Q-RE</b>		50
	Blue	<b>1492-L2-B</b>		50		<b>1492-L2T-B</b>		50		<b>1492-L2Q-B</b>		50
	Black	<b>1492-L2-BL</b>		50		<b>1492-L2T-BL</b>		50		<b>1492-L2Q-BL</b>		50
	Green	<b>1492-L2-G</b>		50		<b>1492-L2T-G</b>		50		<b>1492-L2Q-G</b>		50
	Yellow	<b>1492-L2-Y</b>		50		<b>1492-L2T-Y</b>		50		<b>1492-L2Q-Y</b>		50
	Orange	<b>1492-L2-OR</b>		50		<b>1492-L2T-OR</b>		50		<b>1492-L2Q-OR</b>		50
	Brown	<b>1492-L2-BR</b>		50		<b>1492-L2T-BR</b>		50		<b>1492-L2Q-BR</b>		50
	White	<b>1492-L2-W</b>		50		<b>1492-L2T-W</b>		50		<b>1492-L2Q-W</b>		50
<b>Accessories</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>		<b>Cat. No.</b>		<b>Pkg Qty.</b>
<b>Mounting Rails</b>												
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>		10		<b>199-DR1</b>		10		<b>199-DR1</b>		10
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>		10		<b>1492-DR5</b>		10		<b>1492-DR5</b>		10
1 m Hi-Rise Sym. DIN (Aluminum)		<b>1492-DR6</b>		2		<b>1492-DR6</b>		2		<b>1492-DR6</b>		2
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>		2		<b>1492-DR7</b>		2		<b>1492-DR7</b>		2
<b>End Barriers</b>	Grey	<b>1492-EBL2</b>		50		<b>1492-EBL2T</b>		50		<b>1492-EBL2Q</b>		50
	Blue	<b>1492-EBL2-B</b>		50		<b>1492-EBL2T-B</b>		50		<b>1492-EBL2Q-B</b>		50
	Yellow	<b>1492-EBL2-Y</b>		50		<b>1492-EBL2T-Y</b>		50		<b>1492-EBL2Q-Y</b>		50
<b>End Anchors and Retainers</b>												
Screwless End Retainer		<b>1492-ERL35</b>		20		<b>1492-ERL35</b>		20		<b>1492-ERL35</b>		20
DIN Rail — Normal Duty		<b>1492-EAJ35</b>		100		<b>1492-EAJ35</b>		100		<b>1492-EAJ35</b>		100
DIN Rail — Heavy Duty		<b>1492-EAHJ35</b>		50		<b>1492-EAHJ35</b>		50		<b>1492-EAHJ35</b>		50
<b>Jumpers</b>												
Plug-in Center Jumper — 10-Pole		<b>1492-CJL4-10</b>		20		<b>1492-CJL4-10</b>		20		<b>1492-CJL4-10</b>		20
Plug-in Center Jumper — 5-Pole		<b>1492-CJL4-5</b>		60		<b>1492-CJL4-5</b>		60		<b>1492-CJL4-5</b>		60
Plug-in Center Jumper — 4-Pole		<b>1492-CJL4-4</b>		60		<b>1492-CJL4-4</b>		60		<b>1492-CJL4-4</b>		60
Plug-in Center Jumper — 3-Pole		<b>1492-CJL4-3</b>		60		<b>1492-CJL4-3</b>		60		<b>1492-CJL4-3</b>		60
Plug-in Center Jumper — 2-Pole		<b>1492-CJL4-2</b>		60		<b>1492-CJL4-2</b>		60		<b>1492-CJL4-2</b>		60
<b>Other Accessories</b>												
Reducing Sleeves #28...#24 AWG (0.13...0.2 mm <sup>2</sup> ) White		<b>1492-PSL2-2</b>		100		<b>1492-PSL2-2</b>		100		<b>1492-PSL2-2</b>		100
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm <sup>2</sup> ) Grey		<b>1492-PSL2-5</b>		100		<b>1492-PSL2-5</b>		100		<b>1492-PSL2-5</b>		100
Test Plug (Stackable)		<b>1492-TPL4</b>		25		<b>1492-TPL4</b>		25		<b>1492-TPL4</b>		25
Electrical Warning Plate		<b>1492-EWPL4</b>		20		<b>1492-EWPL4</b>		20		<b>1492-EWPL4</b>		20
<b>Marking Systems</b>												
Snap-In Marker Cards		<b>1492-M3X12</b> (120/card)		5		<b>1492-M3X12</b> (120/card)		5		<b>1492-M3X12</b> (120/card)		5
Snap-In Marker Cards		<b>1492-M3X5</b> (100/card)		5		<b>1492-M3X5</b> (100/card)		5		<b>1492-M3X5</b> (100/card)		5

