


Product Details and Certifications

Cross Reference RA Part Number: 1492-L2T A

 **Product: 1492-L2T**

Description: 1492-L Spring Clamp Terminal Block, One-Circuit Feed-Through Block, 1.5 mm²
(# 26 AWG - # 14 AWG), 2 Connection points on one side, Gray (Standard)



Representative Photo Only (actual product may vary based on configuration sections)

BLOCK STYLE

Bulletin Number	1492 Terminal Block Accessories
Base Block Style	Standard Feed-Through Blocks

BASE DATA

Base Block Type	One-Circuit Feed-Through Block
-----------------	--------------------------------

DETAIL DATA

Features	2 Connection points on one side
Maximum Wire Size & Rating	UL: 26-14 AWG (15A @300V AC/DC)\nCSA: 26-14 AWG (20A @300VAC/DC)\nIEC: 1.5mm ² (17.5A @500V AC/DC)\nEEx e II: 1.5mm ² (15A @550V AC/DC)
Color	Gray (Standard)

CERTIFICATIONS AND APPROVALS

UR	UL 486E, UL 1059; Reference File: E40735, E187022
CSA	CSA C22.2 No. 65, No. 158; On Website, Name: Rockwell, Keyword Search: 1492
IEC	EN 60947-1, EN 60947-7-1(Feed-Through), -2(Ground), -3(Fuse)
ATEX	http://www.rockwellautomation.com/products/certification/ex/excert.html
Short Circuit Current Rating	This terminal block carries a minimum of 10kA SCCR rating for all protection methods. Please see the table for other possible elevated ratings.
For CSA Certifications:	http://directories.csa-international.org/directorymain.asp
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks



Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.	1492-L2 				1492-L2T 				1492-L2Q 			
	Feed-through terminal block				Feed-through terminal block with 2 connection points on one side				Feed-through terminal block with 2 connection points per side			
Specifications	Feed-through terminal block				Feed-through terminal block with 2 connection points on one side				Feed-through terminal block with 2 connection points per side			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC
Maximum Current	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A
Wire Range (Rated Cross Section)	#26...14 AWG		1.5 mm ²	1.5 mm ²	#26...14 AWG		1.5 mm ²	1.5 mm ²	#26...14 AWG		1.5 mm ²	1.5 mm ²
Wire Strip Length	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			

Terminal Blocks		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color	Grey	1492-L2	50	1492-L2T	50	1492-L2Q	50
	Red	1492-L2-RE	50	1492-L2T-RE	50	1492-L2Q-RE	50
	Blue	1492-L2-B	50	1492-L2T-B	50	1492-L2Q-B	50
	Black	1492-L2-BL	50	1492-L2T-BL	50	1492-L2Q-BL	50
	Green	1492-L2-G	50	1492-L2T-G	50	1492-L2Q-G	50
	Yellow	1492-L2-Y	50	1492-L2T-Y	50	1492-L2Q-Y	50
	Orange	1492-L2-OR	50	1492-L2T-OR	50	1492-L2Q-OR	50
	Brown	1492-L2-BR	50	1492-L2T-BR	50	1492-L2Q-BR	50
	White	1492-L2-W	50	1492-L2T-W	50	1492-L2Q-W	50
Accessories		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails							
1 m Symmetrical DIN (Steel)		199-DR1	10	199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10	1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2	1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2	1492-DR7	2	1492-DR7	2
End Barriers	Grey	1492-EBL2	50	1492-EBL2T	50	1492-EBL2Q	50
	Blue	1492-EBL2-B	50	1492-EBL2T-B	50	1492-EBL2Q-B	50
	Yellow	1492-EBL2-Y	50	1492-EBL2T-Y	50	1492-EBL2Q-Y	50
End Anchors and Retainers							
Screwless End Retainer		1492-ERL35	20	1492-ERL35	20	1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50
Jumpers							
Plug-in Center Jumper — 10-Pole		1492-CJL4-10	20	1492-CJL4-10	20	1492-CJL4-10	20
Plug-in Center Jumper — 5-Pole		1492-CJL4-5	60	1492-CJL4-5	60	1492-CJL4-5	60
Plug-in Center Jumper — 4-Pole		1492-CJL4-4	60	1492-CJL4-4	60	1492-CJL4-4	60
Plug-in Center Jumper — 3-Pole		1492-CJL4-3	60	1492-CJL4-3	60	1492-CJL4-3	60
Plug-in Center Jumper — 2-Pole		1492-CJL4-2	60	1492-CJL4-2	60	1492-CJL4-2	60
Other Accessories							
Reducing Sleeves #28...#24 AWG (0.13...0.2 mm ²) White		1492-PSL2-2	100	1492-PSL2-2	100	1492-PSL2-2	100
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm ²) Grey		1492-PSL2-5	100	1492-PSL2-5	100	1492-PSL2-5	100
Test Plug (Stackable)		1492-TPL4	25	1492-TPL4	25	1492-TPL4	25
Electrical Warning Plate		1492-EWPL4	20	1492-EWPL4	20	1492-EWPL4	20
Marking Systems							
Snap-In Marker Cards		1492-M3X12 (120/card)	5	1492-M3X12 (120/card)	5	1492-M3X12 (120/card)	5
Snap-In Marker Cards		1492-M3X5 (100/card)	5	1492-M3X5 (100/card)	5	1492-M3X5 (100/card)	5