


Product Details and Certifications

Cross Reference RA Part Number: 1492-L3Q-B A

Product: **1492-L3Q-B**

Description: 1492-L Spring Clamp Terminal Block, One-Circuit Feed-Through Block, 2.5 mm²
(# 30 AWG - # 12 AWG), 2 Connection points on each side, Blue



Representative Photo Only (actual product may vary based on configuration sections)

BLOCK STYLE

Bulletin Number	1492 Terminal Block Accessories
Base Block Style	Standard Feed-Through Blocks

BASE DATA

Base Block Type	One-Circuit Feed-Through Block
-----------------	--------------------------------

DETAIL DATA

Features	2 Connection points on each side
Maximum Wire Size & Rating	UL: 30-12 AWG (25A @600V AC/DC)\nCSA: 26-12 AWG (27A @600V AC/DC)\nIEC: 2.5mm ² (24A @800V AC/DC)\nEEx e II: 2.5mm ² /20-12 AWG (21A @550V AC/DC)
Color	Blue

CERTIFICATIONS AND APPROVALS

UR	UL 486E, UL 1059; Reference File: E40735, E187022
CSA	CSA C22.2 No. 65, No. 158; On Website, Name: Rockwell, Keyword Search: 1492
IEC	EN 60947-1, EN 60947-7-1(Feed-Through), -2(Ground), -3(Fuse)
ATEX	http://www.rockwellautomation.com/products/certification/ex/excert.html
Short Circuit Current Rating	This terminal block carries a minimum of 10kA SCCR rating for all protection methods. Please see the table for other possible elevated ratings.
For CSA Certifications:	http://directories.csa-international.org/directorymain.asp
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks



1492-L3

1492-L3T

1492-L3Q

Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.			
	Feed-through terminal block	Feed-through terminal block with 3 connection points, 2 on one side	Feed-through terminal block with 2 points on each side

Specifications	1492-L3				1492-L3T				1492-L3Q			
Certifications												
Voltage Rating	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC
Maximum Current	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A
Wire Range (Rated Cross Section)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)
Wire Strip Length	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating (SCCR)	See page 12-78											

Terminal Blocks		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color	Grey	1492-L3	100	1492-L3T	100	1492-L3Q	100
	Red	1492-L3-RE	100	1492-L3T-RE	100	1492-L3Q-RE	100
	Blue	1492-L3-B	100	1492-L3T-B	100	1492-L3Q-B	100
	Black	1492-L3-BL	100	1492-L3T-BL	100	1492-L3Q-BL	100
	Green	1492-L3-G	100	1492-L3T-G	100	1492-L3Q-G	100
	Yellow	1492-L3-Y	100	1492-L3T-Y	100	1492-L3Q-Y	100
	Orange	1492-L3-OR	100	1492-L3T-OR	100	1492-L3Q-OR	100
	Brown	1492-L3-BR	100	1492-L3T-BR	100	1492-L3Q-BR	100
	White	1492-L3-W	100	1492-L3T-W	100	1492-L3Q-W	100

Accessories		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails							
	1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10
	1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10
	1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2
	1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2
End Barriers	Grey	1492-EBL3	50	1492-EBL3T	50	1492-EBL3Q	50
	Blue	1492-EBL3-B	50	1492-EBL3T-B	50	1492-EBL3Q-B	50
	Yellow	1492-EBL3-Y	50	1492-EBL3T-Y	50	1492-EBL3Q-Y	50
End Anchors and Retainers	Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20
	DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100
	DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50
Jumpers	Plug-in Center Jumper — 50-Pole	1492-CJK5-50	10	1492-CJK5-50	10	1492-CJK5-50	10
	Plug-in Center Jumper — 10-Pole	1492-CJK5-10	20	1492-CJK5-10	20	1492-CJK5-10	20
	Plug-in Center Jumper — 9-Pole	1492-CJK5-9	20	1492-CJK5-9	20	1492-CJK5-9	20
	Plug-in Center Jumper — 8-Pole	1492-CJK5-8	20	1492-CJK5-8	20	1492-CJK5-8	20
	Plug-in Center Jumper — 7-Pole	1492-CJK5-7	20	1492-CJK5-7	20	1492-CJK5-7	20
	Plug-in Center Jumper — 6-Pole	1492-CJK5-6	20	1492-CJK5-6	20	1492-CJK5-6	20
	Plug-in Center Jumper — 5-Pole	1492-CJK5-5	20	1492-CJK5-5	20	1492-CJK5-5	20
	Plug-in Center Jumper — 4-Pole	1492-CJK5-4	60	1492-CJK5-4	60	1492-CJK5-4	60
	Plug-in Center Jumper — 3-Pole	1492-CJK5-3	60	1492-CJK5-3	60	1492-CJK5-3	60
	Plug-in Center Jumper — 2-Pole	1492-CJK5-2	60	1492-CJK5-2	60	1492-CJK5-2	60
Other Accessories	Reducing Sleeves #30...#24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2	100	1492-PSL3-2	100	1492-PSL3-2	100
	Reducing Sleeves #22...#20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5	100	1492-PSL3-5	100	1492-PSL3-5	100
	Reducing Sleeves #18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10	100	1492-PSL3-10	100	1492-PSL3-10	100
	Test Plug	1492-TP23	20	1492-TP23	20	1492-TP23	20
	Test Plug (Stackable)	1492-TPL5	25	1492-TPL5	25	1492-TPL5	25
	Electrical Warning Plate	1492-EWPL5	20	1492-EWPL5	20	1492-EWPL5	20
Marking Systems	Snap-In Marker Cards	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5
	Snap-In Marker Cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5
	Hinged Marker Cards	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5
	Hinged Marker Cards	1492-MH5X15 (96/card)	5	1492-MH5X15 (96/card)	5	1492-MH5X15 (96/card)	5