

Product Details and Certifications

Cross Reference RA Part Number: 1492-LD3-OR A

 **Product: 1492-LD3-OR**

Description: 1492-L Spring Clamp Terminal Block, Two-Circuit Feed-Through Block, 2.5 mm²
(# 22 AWG - # 14 AWG), Standard Feedthrough, Orange



Representative Photo Only (actual product may vary based on configuration sections)

BLOCK STYLE

Bulletin Number	1492 Terminal Block Accessories
Base Block Style	Multi-Circuit Feed-Through Blocks

BASE DATA

Base Block Type	Two-Circuit Feed-Through Block
-----------------	--------------------------------

DETAIL DATA

Features	Standard Feedthrough
Maximum Wire Size & Rating	UL: 30-12 AWG (20A @600V AC/DC)\nCSA: 30-12 AWG (25A @600V AC/DC)\nIEC: 2.5mm ² (24A @800V AC/DC)
Color	Orange

CERTIFICATIONS AND APPROVALS

UR	UL 486E, UL 1059; Reference File: E40735, E187022
CSA	CSA C22.2 No. 65, No. 158; On Website, Name: Rockwell, Keyword Search: 1492
IEC	EN 60947-1, EN 60947-7-1(Feed-Through), -2(Ground), -3(Fuse)
ATEX	http://www.rockwellautomation.com/products/certification/ex/excert.html
Short Circuit Current Rating	This terminal block carries a minimum of 10kA SCCR rating for all protection methods. Please see the table for other possible elevated ratings.
For CSA Certifications:	http://directories.csa-international.org/directorymain.asp
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

Spring-Clamp Connection Terminal Blocks

Multi-Circuit Feed-Through Blocks

	1492-LD2			1492-LD3				1492-L3QS			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
Specifications	Two-circuit feed-through terminal block			Two-circuit feed-through terminal block				Side-by-side two circuit terminal block			
Certifications		CSA	IEC		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	300V AC/DC	600V AC/DC	500V AC/DC	600V AC/DC	25 A	800V AC/DC	550V AC/DC	600V AC/DC	27 A	800V AC/DC	550V AC/DC
Maximum Current	10 A		17.5 A	20 A	25 A	24 A	20 A	25 A	27 A	24 A	21 A
Wire Range (Rated Cross Section)	#28... 16 AWG		1.5 mm ²	#30... 12 AWG		2.5 mm ²	0.5...2.5 mm ² (#20...14 AWG)	#26... 12 AWG		2.5 mm ²	2.5 mm ² (20... 12 AWG)
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	87 pcs/ft (285 pcs/m)			59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Terminal Blocks		Cat. No.	Pkg Qty.	Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.	
Color	Grey	1492-LD2	50	1492-LD3		25		1492-L3QS		50	
	Red	1492-LD2-RE	50	1492-LD3-RE		25		1492-L3QS-RE		50	
	Blue	1492-LD2-B	50	1492-LD3-B		25		1492-L3QS-B		50	
	Black	1492-LD2-BL	50	1492-LD3-BL		25		1492-L3QS-BL		50	
	Green	1492-LD2-G	50	1492-LD3-G		25		1492-L3QS-G		50	
	Yellow	1492-LD2-Y	50	1492-LD3-Y		25		1492-L3QS-Y		50	
	Orange	1492-LD2-OR	50	1492-LD3-OR		25		1492-L3QS-OR		50	
	Brown	1492-LD2-BR	50	1492-LD3-BR		25		1492-L3QS-BR		50	
	White	1492-LD2-W	50	1492-LD3-W		25		1492-L3QS-W		50	
Accessories		Cat. No.	Pkg Qty.	Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.	
Mounting Rails											
1 m Symmetrical DIN (Steel)		199-DR1	10	199-DR1		10		199-DR1		10	
1 m Symmetrical DIN (Aluminum)		1492-DR5	10	1492-DR5		10		1492-DR5		10	
1 m Hi-Rise Symmetrical DIN (Aluminum)		1492-DR6	2	1492-DR6		2		1492-DR6		2	
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2	1492-DR7		2		1492-DR7		2	
End Barriers	Grey	1492-EBLD2	50	1492-EBLD3		20		1492-EBL3Q		50	
	Blue	1492-EBLD2-B	20	1492-EBLD3-B		20		1492-EBL3Q-B		50	
	Yellow	1492-EBLD2-Y	20	1492-EBLD3-Y		20		1492-EBL3Q-Y		50	
End Anchors and Retainers											
Screwless End Retainer		1492-ERL35	20	1492-ERL35		20		1492-ERL35		20	
DIN Rail — Normal Duty		1492-EAJ35	100	1492-EAJ35		100		1492-EAJ35		100	
DIN Rail — Heavy Duty		1492-EAHJ35	50	1492-EAHJ35		50		1492-EAHJ35		50	
Jumpers											
Plug-in Center Jumper — 50-Pole		—	—	1492-CJK5-50		10		—		—	
Plug-in Center Jumper — 10-Pole		1492-CJL4-10	20	1492-CJK5-10		20		—		—	
Plug-in Center Jumper — 9-Pole		—	—	1492-CJK5-9		20		—		—	
Plug-in Center Jumper — 8-Pole		—	—	1492-CJK5-8		20		—		—	
Plug-in Center Jumper — 7-Pole		—	—	1492-CJK5-7		20		—		—	
Plug-in Center Jumper — 6-Pole		—	—	1492-CJK5-6		20		—		—	
Plug-in Center Jumper — 5-Pole		1492-CJL4-5	60	1492-CJK5-5		20		—		—	
Plug-in Center Jumper — 4-Pole		1492-CJL4-4	60	1492-CJK5-4		60		—		—	
Plug-in Center Jumper — 3-Pole		1492-CJL4-3	60	1492-CJK5-3		60		—		—	
Plug-in Center Jumper — 2-Pole		1492-CJL4-2	60	1492-CJK5-2		60		—		—	
Other Accessories											
Reducing Sleeves #28...24 AWG (0.13...0.2 mm ²)		1492-PSL2-2	100	1492-PSLS2-2		100		1492-PSL3-2		100	
Reducing Sleeves #22...20 AWG (0.25...0.5 mm ²)		1492-PSL2-5	100	1492-PSLS2-5		100		1492-PSL3-5		100	
Reducing Sleeves #18 AWG (0.75...1.0 mm ²)		—	—	—		—		1492-PSL3-10		100	
Test Plug		1492-TPL4	25	—		—		1492-TP23		20	
		—	—	—		—		1492-TPL5		25	
Electrical Warning Plate		1492-EWPL4	20	—		—		1492-EWPL5		20	
		1492-M3X12 (120/card)*	5	1492-M5X10 (144/card)		5		1492-M5X10 (144/card)		5	
Marking Systems											
Snap-In Marker Cards		1492-M3X5 (100/card)	5	1492-M5X5 (200/card)		5		1492-M5X5 (200/card)		5	
Hinged Marker Cards		—	—	—		—		1492-MH5X10 (96/card)		5	

* May only be mounted in terminal block corner marking positions.

