


Product Details and Certifications

Cross Reference RA Part Number: 1492-N37 B

 **Product: 1492-N37**

Description: 1492 Terminal Block Accessories, End Barrier, Gray (Standard)



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Terminal Blocks and Wiring System



Screw Connection Terminal Blocks

Fuse Blocks

1492-H...

1492-WFB4...

Dimensions are not intended to be used for manufacturing purposes.
Note: Height dimension is measured from top of rail to top of terminal block.



Specifications

Single-circuit fusible terminal block with or without fuse indication.

Single-circuit fuse block with or without fuse indication.

Certifications	UL		CSA	IEC	UL		CSA	IEC
	H6/WFB4	H5/WFB424	H4/WFB4250	300V AC/DC	10...57V AC/DC	100...300V AC	300V AC/DC	500V AC/DC
Voltage Rating				10...57V AC/DC		10...57V AC/DC		
Maximum Current	15 A			15 A		15 A *		
Wire Range (Rated Cross Section)	#30...12 AWG		0.5...4 mm ²	#30...12 AWG		0.5...4 mm ²		
Wire Strip Length	0.38 in. (9.7 mm)			0.31 in. (8 mm)				
Recommended Tightening Torque	7.1 lb•in (0.8 N•m)			2.65...5.3 lb•in (0.3...0.6 N•m)				
Density	33 pcs/ft (109pcs /m)			38 pcs/ft (125 pcs/m)				
Housing Temperature Range	-40...+195 °F (-40...+90 °C)			-40...+195 °F (-40...+90 °C)				
Indicator Type								
H6/WFB4	Non-Indicating			Non-Indicating				
H5/WFB424	Red LED			Red LED				
H4/WFB4250	Neon			Neon				
Leakage Current								
H6/WFB4	—			—				
H5/WFB424	2 mA @ 24V			2 mA @ 24V				
H4/WFB4250	2 mA @ 300V			2 mA @ 300V				
Fuse Size (Not Supplied)	1/4 x 1-1/4 in.			5 x 20 mm				
Short-Circuit Current Rating	See page 12-42							

Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	
Color:	Black No-indication	1492-H6	25	1492-WFB4	50
	Black w/LED	1492-H5	25	1492-WFB424	50
	Black w/Neon	1492-H4	25	1492-WFB4250	50
Accessories					
	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	
Mounting Rails:					
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	
3 ft Scored A-B Rail	1492-N1	20	—	—	
3 ft Rigid A-B Rail	1492-N22	20	—	—	
3 ft High Rise A-B Rail	1492-N44	2	—	—	
Standoff Brackets (Use Every 12 in.)	1492-N25	2	—	—	
End Barrier	1492-N37	50	Not Required	—	
End Anchors and Retainers:					
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	
A-B Rail — Heavy Duty	1492-N23	10	—	—	
10-Pole Side Jumper *	1492-N49	10	1492-SJFB8-10	10	
Side Jumper Insulating Sleeve	1492-SJS	10	—	—	
Other Accessories:			1492-PPSL3	50	
Partition Plate	—	—			
Marking Systems:			1492-MS8X12 (56/card)	5	
Snap-In Marker Card — For Base Block	—	5	1492-MS8X9 (56/card)	5	
For Handle	1492-MS8X12 (56/card)	5	1492-MS8X9 (56/card)	5	
	1492-MS8X9 (56/card)	5			
Adhesive Labels	1492-ALHFB (50/sheet)	1	1492-ALHFB (50/card)	1	

* IEC standards for 5 x 20 mm fuses do not include ratings above 6.3 A.
 * Cat. No. 1492-N49 is uninsulated. Cat. No. 1492-SJFB8-10 is insulated.