

Product Details and Certifications

Cross Reference RA Part Number: 1492-N47 A

 **Product: 1492-N47**

Description: 1492 Terminal Block Accessories, End Anchor, A-B Rail-Normal Duty



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Terminal Blocks and Wiring System

Screw Connection Terminal Blocks

Isolation Blocks

	1492-JKD4TW			1492-JKD4Q			1492-H7		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	<i>Feed-through terminal block with knife disconnect; 3 connection points, 2 on one side</i>			<i>Feed-through terminal block with knife disconnect; 2 connection points on each side</i>			<i>Handle-style isolating terminal block</i>		
Certifications		CSA	IEC		CSA	IEC		CSA	IEC
Voltage Rating	600V AC/DC		500V AC/DC	600V AC/DC		500V AC/DC	300V AC/DC	300V AC/DC	500V AC/DC
Maximum Current	25 A		30 A	25 A		30 A	15 A	15 A	15 A
Wire Range (Rated Cross Section)	#30...10 AWG		0.5...4 mm ²	#30...10 AWG		0.5...4 mm ²	#30...10 AWG		0.5...4.0 mm ²
Fuse Size (Dummy Fuse Supplied)	—			—			1/4 x 1-1/4 in.		
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)			0.38 in. (9.7 mm)		
Recommended Tightening Torque	6.2 lb•in (0.7 N•m)			6.2 lb•in (0.7 N•m)			7.1 lb•in (0.8 N•m)		
Density	49 pcs/ft (163 pcs/m)			49 pcs/ft (163 pcs/m)			33 pcs/ft (109 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-40...+221 °F (-40...+105 °C)		
Short-Circuit Current Rating	See page 12-42								
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.			
Color:	Grey	1492-JKD4TW	50	1492-JKD4Q	50	—			
With Test Points	Grey	1492-JKD4TWTP	50	1492-JKD4QTP	50	—			
	Black	—	—	—	—	1492-H7			
						25			
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.			
Mounting Rails:									
3 ft Scored A-B Rail	—	—	—	—	1492-N1	20			
3 ft Rigid A-B Rail	—	—	—	—	1492-N22	20			
3 ft Rigid Rise A-B Rail	—	—	—	—	1492-N44	2			
Standoff Brackets (use every 12 in.) *	—	—	—	—	1492-N25	2			
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10			
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10			
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2			
End Barrier	Grey	1492-EBJ4TW	50	1492-EBJ4Q	50	1492-N37			
	Yellow	1492-EBJ4TW-Y	50	1492-EBJ4Q-Y	50	—			
End Anchors and Retainers:									
A-B Rail — Heavy Duty	—	—	—	—	1492-N23	10			
A-B Rail — Normal Duty	—	—	—	—	1492-N47	50			
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20			
DIN Rail - Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100			
DIN Rail - Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50			
Jumpers:									
Plug-in Center Jumper — 41-pole	1492-CJLJ6-41	10	1492-CJLJ6-41	10	—	—			
Plug-in Center Jumper — 10-pole	1492-CJLJ6-10	20	1492-CJLJ6-10	20	—	—			
Plug-in Center Jumper — 4-pole	1492-CJLJ6-4	60	1492-CJLJ6-4	60	—	—			
Plug-in Center Jumper — 3-pole	1492-CJLJ6-3	60	1492-CJLJ6-3	60	—	—			
Plug-in Center Jumper — 2-pole	1492-CJLJ6-2	60	1492-CJLJ6-2	60	—	—			
Uninsulated Side Jumper — 10-Pole	—	—	—	—	1492-N49	10			
Side Jumper — Insulating Sleeve	—	—	—	—	1492-SJS	10			
Other Accessories:									
Partition Plate	—	—	—	—	—	—			
Marking Systems:									
Snap-in marker cards	1492-MR6X12 (120/card)	5	1492-MR6X12 (120/card)	5	1492-MS8X12 (56/card)	5			
Snap-in marker cards	1492-M6X12 (120/card)	5	1492-M6X12 (120/card)	5	1492-MS8X9 (56/card)	5			
Adhesive Labels	—	—	—	—	1492-ALHFB (50/sheet)	1			

* For use with 1492-N22 DIN rail only.