

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-QP5-8 A**



**Product: 1492-QP5-8**

Description: 1492 Terminal Block Accessories, Socket Strips, 8 Poles, Black



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

|                     |                                 |
|---------------------|---------------------------------|
| Bulletin Number     | 1492 Terminal Block Accessories |
| Accessory Selection | Individual Accessory Selection  |


## ***SELECTION***

---

1492 Terminal Blocks and Wiring System


**Plug-In and Sensor Connection Blocks**

**Plug-In Connection Blocks \***



| Photo   | Wire Range                             | For Use With                    | Pkg Qty.  | Cat. No.          |
|---|--|---------------------------------|-----------|-------------------|
|  | #22...12 AWG<br>(2.5 mm <sup>2</sup> ) | 1492-JC3,<br>JDC3, LC3,<br>LDC3 | 100       | 1492-QP5-2        |
|   |  |                                 | 100       | 1492-QP5-3        |
|   |  |                                 | 100       | 1492-QP5-4        |
|   |  |                                 | 50        | 1492-QP5-5        |
|   |  |                                 | 50        | 1492-QP5-6        |
|   |  |                                 | 50        | 1492-QP5-7        |
|   |  |                                 | <b>50</b> | <b>1492-QP5-8</b> |
|   |  |                                 | 50        | 1492-QP5-9        |
|   |  |                                 | 50        | 1492-QP5-10       |
|   |  |                                 | 50        | 1492-QP5-11       |
| 50  | 1492-QP5-12                            |                                 |           |                   |

\* Tightening Torque: 3.5...4.4 lb•in. (0.4...0.5 N•m)




**Sensor Connection Blocks**

| Photo   | Wire Range                             | For Use With  | Color | Pkg. Qty. | Cat. No.    |
|---|--|---|-------|-----------|-------------|
|  | #26...14 AWG<br>(1.5 mm <sup>2</sup> ) | 1492-LS2-3,<br>LS2-3L,<br>LSG2-3,<br>LS2-4, LS2-4L,<br>LSG2-4 | Brown | 100       | 1492-LS2-BR |
|   |  |   | Blue  | 100       | 1492-LS2-B  |
|   |  |   | Green | 100       | 1492-LSG2   |

**Plug-In Connectors and Accessories for Flexible Configuration Blocks**



| Photo   | Description | Color | Pkg. Qty. | Cat. No.   |
|---|-------------|-------|-----------|------------|
| <b>Individual Plug-in Connectors</b>  |             |       |           |            |
|  | Standard    | Grey  | 50        | 1492-STP   |
|   | Grounded    | Green | 50        | 1492-STP-G |
| <b>Ganged Connectors</b>  |             |       |           |            |
|  | Start plug  | Grey  | 50        | 1492-SBSTP |
|   | Middle plug | Grey  | 50        | 1492-GSTP  |
|   | End plug    | Grey  | 50        | 1492-EBSTP |

**Accessories**

|   |   |        |    |            |
|---|---|--------|----|------------|
|  | Plug-in block locking element           | Yellow | 25 | 1492-STPLE |
|  | Coding Element for keyed configuration  | Yellow | 50 | 1492-STPCE |
|  | Strain Relief covering w plug-in blocks | Yellow | 25 | 1492-STPSR |

**DIN Rail Receptacle**

Convenient 15 A or 20 A power source designed to be installed in panels that will be used in North America and other locations that use the NEMA 5-15 socket (125V, 50/60 Hz).

| Photo   | Device Rating | Pkg Qty. | Cat. No.    |
|---|---------------|----------|-------------|
| <b>Standard Duplex</b>  |               |          |             |
|  | 15 A          | 1        | 1492-REC15  |
|   | 20 A          | 1        | 1492-REC20  |
| <b>Ground Fault Circuit Interrupter (GFCI)</b>                                    |               |          |             |
|  | 15 A          | 1        | 1492-REC15G |
|   | 20 A          | 1        | 1492-REC20G |



| Electrical Ratings          |                                 |   |
|-----------------------------|---------------------------------|---|
|                             | Standard Duplex                 | Ground Fault Circuit Interrupter (GFCI) |
| Certifications              | cUL <sub>US</sub> LISTED        |   |
|                             | UL 508A, NEMA WD-6, NEMA 5-15R  |   |
|                             | UL498                           | UL 498, UL 943                          |
| Device Rating               | 15 A                            | 15 Amp 125V                             |
|                             | 20 A                            | 20 Amp 125V                             |
| Operating Frequency         | 50/60 Hz                        |   |
| Dielectric Voltage          | Withstands 2000V per UL498      | Withstands 1500V per UL498              |
|                             | Short-Circuit Current Rating    | 10 kA                                   |
| Environmental Ratings       |                                 |   |
| Operating Temperature Range | -31...+140 °F (-35...+60 °C)    |   |
| Storage Temperature Range   | -13...+176 °F (-25...+80 °C)    |   |
| Mechanical Ratings          |                                 |   |
| Terminal Wire Sizes         | #20...#10 AWG solid or stranded |   |
| Terminal Torque             | 7 lb•in. (.79 N•m)              |   |
| Markers                     | 1492-MS10X17                    |   |