

# Product Details and Certifications

## Cross Reference RA Part Number: 150-C43NCD B

 Product: **150-C43NCD**

Description: SMC-3, 3-Wire, Open Type, 43A, 600V 3-Phase  
50/60 Hz Max, Control Voltage 100...240V AC



Representative Photo Only (actual product may vary based on configuration sections)

### **CONTROLLER DATA**

---

Bulletin Number	150-C Solid State Controller
Enclosure Type	Open
Input Line Voltage	200..600V AC 50/60Hz
Control Voltage	100...240V AC
Phase	3 PH
Amperage Rating	43 A

### **CERTIFICATIONS AND APPROVALS**

---

UL  
CSA  
EN/IEC  
CE

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

## SMC-3 Controllers


The compact design of the SMC-3 controller provides three-phase control, increased intelligence, and unmatched performance in a cost-effective package with overload protection, integrated bypass, and motor system diagnostics. DIP switches and a rotary dial make secure setup easy. This controller features an electronic overload with adjustable trip class.

Modes of operation include the following:

- Soft Start
- Current Limit Start
- Selectable Kickstart
- Coast-to-rest
- Soft Stop

## Catalog Number Explanation

Examples that are given in this section are not intended to be used for product selection. Use ProposalWorks to configure the SMC-Flex controller. ProposalWorks is available from <http://www.rockwellautomation.com/global/e-tools/overview.page>.


150 - C 43 N C D  
a      b      c      d      e      f

a		b		c		d	
Bulletin Number		Controller Type		Ampere Ratings		Enclosure Type	
Code	Description	Code	Description	Code	Description	Code	Description
150	Solid-state Controller	C	SMC-3	3	3 A	N	Open
				9	9 A		
				16	16 A		
				19	19 A		
				25	25 A		
				30	30 A		
				37	37 A		
				43	43 A		
				60	60 A		
				85	85 A		
				108	108 A		
				135	135 A		
				201	201 A		
				251	251 A		
				317	317 A		
				361	361 A		
				480	480 A		

e	
Input Line Voltage	
Code	Description
B	200...460V AC, 3-Phase, 50/60 Hz
C	200...600V AC, 3-Phase, 50/60 Hz

f	
Control Voltage	
Code	Description
D	100...240V AC
R	24V AC/DC