

Product Details and Certifications

Cross Reference RA Part Number: 1794-PS3 A

 **Product: 1794-PS3**

Description: 1794-P 120/230 VAC To 24VDC 3A Power Supply



Representative Photo Only (actual product may vary based on configuration sections)

POWER SUPPLY DATA

Bulletin Number	1794 I/O System
Indicators	1 Green Power Indicator
Nominal Supply Voltage	120V AC, 47...63 Hz, 1.4 A / 230V AC, 47...63 Hz, 0.8 A
Voltage Range	85...264V AC
Input Current, Max	1.9 A
Inrush Current	30A, 1AC Cycle @ Vin 264V AC, 55 °C
Interruption	Output will stay within specification when input drops out for 1/2 cycle @ 47 Hz, 85V AC with maximum load

CERTIFICATIONS AND APPROVALS

UL
CE
C-Tick
KCC

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

1794-PS13, 1794-PS3

FLEX I/O Power Supply Modules

Input Specifications

Attribute	1794-PS13	1794-PS3
Indicators	1 green power indicator	
Nominal supply voltage	120V AC, 47...63 Hz; 0.62 A 230V AC, 47...63 Hz; 0.42 A	120V AC, 47...63 Hz; 1.4 A 230V AC, 47...63 Hz; 0.8 A
Voltage range	85...264V AC	
Input current, max	0.7 A	1.9 A
Inrush current	30 A, 1 AC cycle @ Vin 264V AC, 55 °C	
Interruption	Output will stay within specification when input drops out for 1/2 cycle @ 47 Hz, 85V AC with maximum load	

Output Specifications

Attribute	1794-PS13	1794-PS3
Nominal output	+24V DC	
Output voltage regulation	20.4...27.6V DC ($\pm 15\%$, includes noise and 5% AC ripple)	
Output current, max	1.3 A	3 A horizontal mount, 2.8 A all other mounting
Output power	31.2 W	72 W
Output ripple	$\pm 5\%$ 1200mV peak-to-peak max	
Minimum load	0 mA	50 mA
Output surge	Sufficient to drive 4 adapters	Sufficient to drive 10 adapters
Overvoltage protection	Output internally limited to 40V DC. Cycle power to reenergize.	
Leakage current	0.5 mA rms max @ rated input and output	
Isolation voltage	Isolation will be required between the AC input terminals and the DC output terminals. Isolation voltage requirements: 2500V DC for 1 s	
Overcurrent protection	1.4 A	3.2 A
Thermal dissipation	23.9 BTU/hr	41.0 BTU/hr
Power dissipation	7 W	12 W
Terminal base screw torque	0.8 Nm (7 lb-in.)	
Conductors Wire size	0.33 mm ² ...3.31 mm ² (22...12 AWG) stranded copper wire rated @ 75 °C or higher 1.2mm (3/64 in.) insulation max	
Category ⁽¹⁾	2	
North American temperature code	T3C	T3
Enclosure	None (open-style)	
Dimensions (HxWxD)	87 x 69 x 69 mm (3.4 x 2.7 x 2.7 in.)	87 x 94 x 69 mm (3.4 x 3.7 x 2.7 in.)
Publication, installation instructions	1794-IN069	

(1) You use this category information for planning conductor routing as described in Allen-Bradley publication [1770-4.1](#), Industrial Automation Wiring and Grounding Guidelines



Environmental Specifications

Attribute	1794-PS13	1794-PS3
Temperature, operating	IEC 60068-2-1 (Test Ad, Operating Cold), IEC 60068-2-2 (Test Bd, Operating Dry Heat), IEC 60068-2-14 (Test Nb, Operating Thermal Shock): 0...55 °C (32...131 °F)	
Temperature, nonoperating	IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold), IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat), IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock): -40...85 °C (-40...185 °F)	
Relative humidity	IEC 60068-2-30 (Test Db, Unpackaged Nonoperating Damp Heat): 5...95% noncondensing	
Vibration	IEC 60068-2-6 (Test Fc, Operating): 5 g @ 10...500 Hz	
Shock, operating	IEC 60068-2-27 (Test Ea, Unpackaged Shock): 30 g	
Shock, nonoperating	IEC 60068-2-27 (Test Ea, Unpackaged Shock): 50 g	
Emissions	CISPR 11: Group 1, Class A	
ESD immunity	IEC 61000-4-2: 6 kV contact discharges 8 kV air discharges	
Radiated RF immunity	IEC 61000-4-3: 10V/m with 1 kHz sine-wave 80% AM from 30...1000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 10V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz	
EFT/B immunity	IEC 61000-4-4: ±2 kV @ 5 kHz on power ports	
Surge transient immunity	IEC 61000-4-5: ±1 kV line-line(DM) and ±2 kV line-earth(CM) on AC power ports	
Conducted RF immunity	IEC 61000-4-6: 10Vrms with 1kHz sine-wave 80%AM from 150 kHz...80 MHz	

Certifications

Certification ⁽¹⁾ (When marked on product)	1794-PS13	1794-PS3
c-UL-us	UL Listed for Class 1, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584.	
CE	European Union 2004/108/IEC EMC Directive, compliant with: EN 61326-1; Meas./Control/Lab., Industrial Requirements EN 61000-6-2; Industrial Immunity EN 61000-6-4; Industrial Emissions EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) European Union 2006/95/EC LVD, compliant with: EN 61131-2; Programmable Controllers (Clause 11)	
C-Tick	Australian Radiocommunications Act, compliant with: AS/NZS CISPR 11; Industrial Emissions	
KC	—	Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3

(1) See the Product Certification link at <http://www.rockwellautomation.com/products/certification/> for Declaration of Conformity, Certificates, and other certification details.