

Product Details and Certifications

Cross Reference RA Part Number: U-00820919060007

Product: **20BC3P5A0AYNANN0**

Description: PowerFlex700 AC Drive, 400 VAC, 3 PH, 3.5 Amps, 1.5 kW ND, 1.1 kW HD, IP20 / NEMA Type 1, with conformal coating, No HIM (Blank Plate), Brake IGBT Installed, without Drive Mounted Brake Resistor, Second Environment Filter per CE EMC directive (89/336/EEC), No Communication Module, Standard Control with No I/O, No Feedback



Representative Photo Only (actual product may vary based on configuration sections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 700 AC Drive
Input Voltage	400 VAC, 3 PH
Output Current	3.5 Amps
Enclosure	IP20 / Type 1, with conformal coating
Frame Size	Frame Size 0
I/O	Standard Control with No I/O
Output Current Information	Output Amps: 3.5A Cont. 4.5A 1 Min. 6A 3 Sec
Brake IGBT	Brake IGBT Installed
Brake Resistor	No Brake Resistor
EMC Filtering Options	Second Environment Filter per CE EMC directive (89/336/EEC)

OPTION INFORMATION

Base Plus Options	Base Plus Options Method
Internal Communication Module	No Communication Module

LIFECICLE STATUS NOTE

LifeCycle Status Note	PowerFlex 700 Frame 7 - 10 drives are now in End of Life status. They are still available for sale, but we recommend that you consider the new generation PowerFlex 755 drive family as an alternative.
-----------------------	---

Catalog Number Explanation



a

Drive	
Code	Type
20B	PowerFlex 700

b

Voltage Rating				
Code	Voltage	Ph.	Prechg.	Frames
B	240V AC	3	-	0...6
C	400V AC	3	-	0...10
D	480V AC	3	-	0...10
E	600V AC	3	-	0...6
F	690V AC	3	-	5...6
H	540V DC	-	N	5...6, 10
J	650V DC	-	N	5...6, 10
N	325V DC	-	Y	5...6
P	540V DC	-	Y	5...9
R	650V DC	-	Y	5...9
T	810V DC	-	Y	5...6
W	932V DC	-	Y	5...6

c1

ND Rating				
208/240V, 60 Hz Input				
Code	208V Amps	240V Amps	Hp	Frame
2P2	2.5	2.2	0.5	0
4P2	4.8	4.2	1.0	0
6P8	7.8	6.8	2.0	1
9P6	11	9.6	3.0	1
015	17.5	15.3	5.0	1
022	25.3	22	7.5	1
028	32.2	28	10	2
042	48.3	42	15	3
052	56	52	20	3
070	78.2	70	25	4
080	92	80	30	4
104	120	104	40	5
130	130	130	50	5
154	177	154	60	6
192	221	192	75	6
260	260	260	100	6

c2

ND Rating				
400V, 50 Hz Input				
Code	Amps	kW	Frame	
1P3	1.3	0.37	0	
2P1	2.1	0.75	0	
3P5	3.5	1.5	0	
5P0	5.0	2.2	0	
8P7	8.7	4.0	0	
011	11.5	5.5	0	
015	15.4	7.5	1	
022	22	11	1	
030	30	15	2	
037	37	18.5	2	
043	43	22	3	
056	56	30	3	
072	72	37	3	
085	85	45	4	
105	105	55	5	
125	125	55	5	
140	140	75	5	
170	170	90	6	
205	205	110	6	
260	260	132	6	
292	292	160	7	
325	325	180	7	
365	365	200	8	
415	415	240	8	
481	481	280	8	
535	535	300	8	
600	600	350	8	
730	730	400	9	
875	875	500	10	

c3

ND Rating				
480V, 60 Hz Input				
Code	Amps	Hp	Frame	
1P1	1.1	0.5	0	
2P1	2.1	1.0	0	
3P4	3.4	2.0	0	
5P0	5.0	3.0	0	
8P0	8.0	5.0	0	
011	11	7.5	0	
014	14	10	1	
022	22	15	1	
027	27	20	2	
034	34	25	2	
040	40	30	3	
052	52	40	3	
065	65	50	3	
077	77	60	4	
096	96	75	5	
125	125	100	5	
156	156	125	6	
180	180	150	6	
248	248	200	6	
292	292	250	7	
325	325	250	7	
365	365	300	8	
415	415	350	8	
481	481	400	8	
535	535	450	8	
600	600	500	8	
730	730	600	9	
875	875	700	10	

c4

ND Rating				
600V, 60 Hz Input				
Code	Amps	Hp	Frame	
1P7	1.7	1.0	0	
2P7	2.7	2.0	0	
3P9	3.9	3.0	0	
6P1	6.1	5.0	0	
9P0	9.0	7.5	0	
011	11	10	1	
017	17	15	1	
022	22	20	2	
027	27	25	2	
032	32	30	3	
041	41	40	3	
052	52	50	3	
062	62	60	4	
077	77	75	5	
099	99	100	5	
125	125	125	6	
144	144	150	6	

20B C 3P5 A 0 A Y N A N N 0

a b c1...c5 d e f g h i j k l m n

c5

ND Rating			
690V, 50 Hz Input			
Code	Amps	KW	Frame
052	52	45	5
060	60	55	5
082	82	75	5
098	98	90	6
119	119	110	6
142	142	132	6

d

Enclosure	
Code	Enclosure
A	IP20, NEMA/UL Type 1
F	Open/Flange Mount Front: IP00, NEMA/UL Type Open Back/Heatsink: IP54, NEMA Type 12
N	Open/Flange Mount Front: IP00, NEMA/UL Type Open Back/Heatsink: IP54, NEMA 12
G	Stand-Alone/Wall Mount IP54, NEMA/UL Type 12
U	Roll-In Front: IP00, NEMA/UL Type Open Back/Heatsink: IP54, NEMA 12 Frames 8 & 9 Only

♣ Only available for Frame 5 & Frame 6 drives, 400...690V.
 ♣ Only available for Frames 7...10.

e

HIM	
Code	Operator Interface
0	Blank Cover
3	LCD Display, Full Numeric Keypad
J	Remote (Panel Mount), IP66, NEMA/UL Type 12 Full Numeric LCD HIM
K	Remote (Panel Mount), IP66, NEMA/UL Type 12 Prog. Only LCD HIM

♣ Available with Frames 5...6 Stand-Alone IP54 drives (Enclosure Code "G").

f

Documentation	
Code	Type
A	Manual
N	No Manual
Q	No Shipping Package (Internal Use Only)

g

Brake	
Code	w/Brake IGBT ‡
Y	Yes
N	No

‡ Brake IGBT is standard on Frames 0-3, optional on Frames 4-6 and not available on Frames 7...10.

h

Internal Braking Resistor	
Code	w/Resistor
Y	Yes *
N	No

* Not available for Frame 3 drives or larger.

i

Emission		
Code	CE Filter §	CM Choke
A	Yes	Yes
B #	Yes	No
N	No	No

§ Note: 600V class drives below 77 Amps (Frames 0-4) are declared to meet the Low Voltage Directive. It is the responsibility of the user to determine compliance to the EMC directive. Frames 7...10, 400/480V AC drives (Voltage Rating codes "C" and "D") meet CE certification requirements when installed per recommendations.

Only available for 208...240V Frame 0-3 drives.

j

Comm Slot	
Code	Network Type
C	ControlNet (Coax)
D	DeviceNet
E	EtherNet/IP
N	None

k

Control & I/O		
Code	Control	I/O Volts
A	Standard ♣	24V DC/AC
B	Standard ♣	115V AC
C	Vector Δ	24V DC
D	Vector Δ	115V AC
N	Standard	None

Δ Vector Control Option utilizes DPI Only.
 ♣ Frame 0...6 drives only.

l

Feedback	
Code	Type
0	None
1	Encoder, 12V/5V

m

Future Use

n

Special Firmware (Frames 0...6 Only)	
Code	Type
AD ♣	60 Hz Maximum
AE ♣	Cascading Fan/Pump Control
AX ♣	82 Hz Maximum
BA ♣	Pump Off (for pump jack)

♣ Must be used with Vector Control option C or D (Position k). Positions m-n are only required when custom firmware is supplied.