

# Product Details and Certifications

## Cross Reference RA Part Number: U-00820919197550

### Product: **20BE6P1A0AYNANC0**

Description: PowerFlex700 AC Drive, 600 VAC, 3 PH, 6.4 Amps, 5 HP ND, 3 HP HD, IP20 / NEMA Type 1, with conformal coating, No HIM (Blank Plate), Brake IGBT Installed, without Drive Mounted Brake Resistor, Second Environment Filter per CE EMC directive (89/336/EEC), No Communication Module, Vector Control with 24V I/O, No Feedback



Representative Photo Only (actual product may vary based on configuration sections)

### **BASE DRIVE INFORMATION**

---

Bulletin Number	PowerFlex 700 AC Drive
Input Voltage	600 VAC, 3 PH
Output Current	6.1 Amps
Enclosure	IP20 / Type 1, with conformal coating
Frame Size	Frame Size 0
I/O	Vector Control with 24V I/O
Output Current Information	Output Amps: 6.1A Cont. 6.7A 1 Min.9.2A 3 Sec
Brake IGBT	Brake IGBT Installed
Brake Resistor	No Brake Resistor
EMC Filtering Options	Second Environment Filter per CE EMC directive (89/336/EEC)

### **OPTION INFORMATION**

---


Base Plus Options	Base Plus Options Method
Internal Communication Module	No Communication Module

### **LIFECICLE STATUS NOTE**

---

LifeCycle Status Note	PowerFlex 700 Frame 7 - 10 drives are now in End of Life status. They are still available for sale, but we recommend that you consider the new generation PowerFlex 755 drive family as an alternative.
-----------------------	---

### Catalog Number Explanation



*a*

Drive	
Code	Type
<b>20B</b>	<b>PowerFlex 700</b>

*b*

Voltage Rating				
Code	Voltage	Ph.	Prechg.	Frames
B	240V AC	3	-	0...6
C	400V AC	3	-	0...10
D	480V AC	3	-	0...10
<b>E</b>	<b>600V AC</b>	<b>3</b>	<b>-</b>	<b>0...6</b>
F	690V AC	3	-	5...6
H	540V DC	-	N	5...6, 10
J	650V DC	-	N	5...6, 10
N	325V DC	-	Y	5...6
P	540V DC	-	Y	5...9
R	650V DC	-	Y	5...9
T	810V DC	-	Y	5...6
W	932V DC	-	Y	5...6

*c1*

ND Rating				
208/240V, 60 Hz Input				
Code	208V Amps	240V Amps	Hp	Frame
2P2	2.5	2.2	0.5	0
4P2	4.8	4.2	1.0	0
6P8	7.8	6.8	2.0	1
9P6	11	9.6	3.0	1
015	17.5	15.3	5.0	1
022	25.3	22	7.5	1
028	32.2	28	10	2
042	48.3	42	15	3
052	56	52	20	3
070	78.2	70	25	4
080	92	80	30	4
104	120	104	40	5
130	130	130	50	5
154	177	154	60	6
192	221	192	75	6
260	260	260	100	6

*c2*

ND Rating			
400V, 50 Hz Input			
Code	Amps	kW	Frame
1P3	1.3	0.37	0
2P1	2.1	0.75	0
3P5	3.5	1.5	0
5P0	5.0	2.2	0
8P7	8.7	4.0	0
011	11.5	5.5	0
015	15.4	7.5	1
022	22	11	1
030	30	15	2
037	37	18.5	2
043	43	22	3
056	56	30	3
072	72	37	3
085	85	45	4
105	105	55	5
125	125	55	5
140	140	75	5
170	170	90	6
205	205	110	6
260	260	132	6
292	292	160	7
325	325	180	7
365	365	200	8
415	415	240	8
481	481	280	8
535	535	300	8
600	600	350	8
730	730	400	9
875	875	500	10

*c3*

ND Rating			
480V, 60 Hz Input			
Code	Amps	Hp	Frame
1P1	1.1	0.5	0
2P1	2.1	1.0	0
3P4	3.4	2.0	0
5P0	5.0	3.0	0
8P0	8.0	5.0	0
011	11	7.5	0
014	14	10	1
022	22	15	1
027	27	20	2
034	34	25	2
040	40	30	3
052	52	40	3
065	65	50	3
077	77	60	4
096	96	75	5
125	125	100	5
156	156	125	6
180	180	150	6
248	248	200	6
292	292	250	7
325	325	250	7
365	365	300	8
415	415	350	8
481	481	400	8
535	535	450	8
600	600	500	8
730	730	600	9
875	875	700	10

*c4*

ND Rating			
600V, 60 Hz Input			
Code	Amps	Hp	Frame
1P7	1.7	1.0	0
2P7	2.7	2.0	0
3P9	3.9	3.0	0
<b>6P1</b>	<b>6.1</b>	<b>5.0</b>	<b>0</b>
9P0	9.0	7.5	0
011	11	10	1
017	17	15	1
022	22	20	2
027	27	25	2
032	32	30	3
041	41	40	3
052	52	50	3
062	62	60	4
077	77	75	5
099	99	100	5
125	125	125	6
144	144	150	6

