

Product Details and Certifications

Cross Reference RA Part Number: U-00820919488627

Product: 20CE208A0ANNBNN0

Description: PowerFlex700H AC Drive, 600 VAC, 3 PH, 208 Amps, 200 HP Normal Duty, 150 HP Heavy Duty, IP21 / Type 1, with Conformal Coating, No HIM (Blank Plate), No Brake IGBT, Without Drive Mounted Brake Resistor, Common Mode Choke Removed, Second Environment Filter per CE EMC directive (89/336/EEC), No Communication Module, Standard Control with No I/O, No Feedback



Representative Photo Only (actual product may vary based on configuration selections)

NOTE

Lifecycle Status Note PowerFlex 700H drive family is now in End of Life status. It is still available for sale, but we recommend that you consider the new generation PowerFlex 755 drive family as an alternative.

BASE DRIVE INFORMATION

Input Voltage 600 VAC 60 Hz
Phases 3 Phases

INSTALLED OPTIONS

Normal Duty Output Current Rating 208 Amps
Heavy Duty Output Current Rating 170 Amps
Normal Duty HP 200 HP
Heavy Duty HP 150 HP
Enclosure IP21 / Type 1, with Conformal Coating
Frame Size Frame Size 9
Documentation User Manual
Brake IGBT No Brake IGBT
Brake Resistor Without Drive Mounted Brake Resistor
Filter Options Common Mode Choke Removed, Second Environment Filter per CE EMC directive (89/336/EEC)
I/O Options Standard Control with No I/O

USER INSTALLED OPTIONS

Base Plus Options Base Plus Options Method
Internal Communication Module No Communication Module

Standard Drives

Catalog Number Explanation

1-3			4	5-7			8	Position				13	14	15	16
20C			E	208			A	0	A	N	N	B	N	N	0
a			b	c			d	e	f	g	h	i	j	k	l

a

Drive	
Code	Type
20C	PowerFlex 700H

b

Voltage Rating		
Code	Voltage	Ph.
C	400V AC	3
D	480V AC	3
E	600V AC	3
F	690V AC	3

c1

Rating		
400V, 50Hz Input		
Code	Amps - ND (HD)	kW - ND (HD)
261	261 (205)	132 (110)
300	300 (245)	160 (132)
385	385 (300)	200 (160)
460	460 (385)	250 (200)
500	500 (420)	250 (250)
590	590 (520)	315 (250)
650	650 (590)	355 (315)
730	730 (650)	400 (355)
820	820 (730)	450 (400)
920	920 (820)	500 (450)
1K0	1030 (920)	560 (500)
1K1	1150 (1030)	630 (560)
1K3	1300 (1150)	710 (630)
1K4	1450 (1200)	800 (710)
1K7	1770 (1600)	1000 (900)
2K1	2150 (1940)	1200 (1100)

c2

Rating		
480V, 60Hz Input		
Code	Amps - ND (HD)	Hp - ND (HD)
261	261 (205)	200 (150)
300	300 (245)	250 (200)
385	385 (300)	300 (250)
460	460 (385)	350 (300)
500	500 (420)	450 (350)
590	590 (520)	500 (450)
650	650 (590)	500 (500)
730	730 (650)	600 (500)
820	820 (730)	700 (600)
920	920 (820)	800 (700)
1K0	1030 (920)	900 (800)
1K1	1150 (1030)	1000 (900)
1K3	1300 (1150)	1100 (1000)
1K4	1450 (1200)	1250 (1000)
1K7	1770 (1600)	1500 (1400)
2K1	2150 (1940)	1900 (1700)

c3

Rating		
600V, 60Hz Input		
Code	Amps - ND (HD)	Hp - ND (HD)
170	170 (144)	150 (150)
208	208 (170)	200 (150)
261	261 (208)	250 (200)
325	325 (261)	350 (250)
385	385 (325)	400 (350)
416	416 (325)	450 (350)
460	460 (385)	500 (400)
502	502 (460)	500 (500)
590	590 (502)	600 (500)
650	650 (590)	700 (650)
750	750 (650)	800 (700)
820	820 (750)	900 (700)
920	920 (820)	1000 (900)
1K0	1030 (920)	1100 (1000)
1K1	1180 (1030)	1300 (1100)
1K5	1500 (1300)	1600 (1400)
1K9	1900 (1500)	2000 (1600)
2K2	2250 (1900)	2400 (2000)

c4

Rating		
690V, 50Hz Input		
Code	Amps - ND (HD)	kW - ND (HD)
170	170 (144)	160 (132)
208	208 (170)	200 (160)
261	261 (208)	250 (200)
325	325 (261)	315 (250)
385	385 (325)	355 (315)
416	416 (325)	400 (315)
460	460 (385)	450 (355)
502	502 (460)	500 (450)
590	590 (502)	560 (500)
650	650 (590)	630 (560)
750	750 (650)	710 (630)
820	820 (750)	800 (630)
920	920 (820)	900 (800)
1K0	1030 (920)	1000 (900)
1K1	1180 (1030)	1100 (1000)
1K5	1500 (1300)	1500 (1300)
1K9	1900 (1500)	1900 (1500)
2K2	2250 (1900)	2300 (1900)

d

Enclosure	
Code	Enclosure
A	IP21, NEMA Type 1 (Frame 9) Rittal Enclosure (Frames 10 & Up)
B	IP20, NEMA Type 1, MCC §
H	IP54, NEMA Type 12, Rittal §
K	IP20, NEMA Type 1, MCC with Conformal Coat §
M	IP21, NEMA Type 1 (Frame 9) Rittal Enclosure (Frames 10 & Up) with Conformal Coat
W	IP54, NEMA Type 12, Rittal with Conformal Coat §

§ Frame 10 & up only.

e

HIM	
Code	Operator Interface
0	Blank Cover
3	Full Numeric LCD, Drive Mounted
C	Full Numeric LCD, Door Mount *

* IP21, NEMA Type 1 Frame 10 & up only.

Catalog Number Explanation, Continued

