


# Product Details and Certifications

Cross Reference RA Part Number: **PN-478090**

 **Product: 20G11NB9P6JA0NNNNN**

Description: PowerFlex 755 AC Drive, with Embedded Ethernet/IP, Air Cooled, AC Input with DC Terminals, Open Type, 9.6 Amps, 3 HP ND, 2 HP HD, 240 (208) VAC, 3 PH, Frame 2, Filtered, CM Jumper Installed, DB Transistor, Blank (No HIM)




## **BASE DRIVE INFORMATION**

Representative Photo Only (actual product may vary based on configuration selections)

---

Bulletin Number	PowerFlex 755 AC Drive, with Embedded Ethernet/IP
Input Voltage	240 (208) VAC, 3 PH
Phases	3 Phases
Current Power Rating	9.6 Amps, 3 HP ND, 2 HP HD
Enclosure Type	Open Type
Input Type	AC Input with DC Terminals
Frame Size	Frame 2
Filtering & CM Cap Config	Filtered, CM Jumper Installed
Dynamic Braking	DB Transistor
HIM	Blank (No HIM)

# Catalog Number Explanation



**a**

Drive		
Code	Type	Frames
20F	PowerFlex® 753	1...7
20G	PowerFlex 755	1...10
21G	PowerFlex 755 Drive with Options	8...10

**b**

Future Use		
------------	--	--

**c**

Input Type		
Code	Description	Frames
1	AC Input with Precharge, includes DC Terminals	1...5 8...10
4	DC Input with Precharge	5...10
A	AC Input with Precharge, no DC Terminals	6...8 <sup>(1)</sup>

The DC Bus Bar kit (20-750-DCBB1-Fx) is available for Frames 6...7 AC input drives that require DC bus terminals.

**d**

Enclosure		
Code	Description	Frames
R	IP20, NEMA/UL Type Open, Frame 1	1
F <sup>(1)</sup>	Flange (NEMA/UL Type 4X/12 back)	2...5
G	IP54, NEMA/UL Type 12	2...7
N <sup>(2)</sup>	IP20/IP00, NEMA/UL Type Open	2...7
B <sup>(3)</sup>	IP20, NEMA/UL Type 1, 600 mm (23.6 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
J <sup>(3)</sup>	IP54, UL Type 12, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
K <sup>(3)</sup>	IP54, NEMA 12, 2500 MCC Style Cabinet and Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
L <sup>(3)</sup>	IP20, NEMA/UL Type 1, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
P <sup>(3)</sup>	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet and Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
W <sup>(3)</sup>	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet and Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
Y <sup>(3)</sup>	IP54, NEMA 12, 2500 MCC Style Cabinet and Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
T	IP00, UL Open Type without Control POD	8...10

**e**

Voltage Rating	
Code	Voltage
B	240V AC (208V AC) <sup>(1)</sup> /325V DC (281V DC) <sup>(1)</sup>
C	400V AC/540V DC
D	480V AC/650V DC
E	600V AC/810V DC
F	690V AC/932V DC (not UL Listed)

(1) Drive must be programmed to obtain low (208V AC) voltage rating.

**f1**

ND Rating								
208V <sup>(1)</sup> , 60 Hz Input								
Code	Amps	kW	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R
2P2	2.5	0.37						1
4P2	4.8	0.75						
6P8	7.8	1.5						
9P6	11	2.2						
015	15.3	4						
2P2	2.5	0.37						
4P2	4.8	0.75						
6P8	7.8	1.5						
9P6	11	2.2		2	2	2		
015	17.5	4						
022	22	5.5						
028	32.2	7.5						
042	43	11		3	3	3		
054	60	15		4	4	4		
070	78.2	18.2		5	5	5		
080	92	22						
104	120	30						
130	150	37			6			
154	177	45		(2)		6		
192	221	55						
260	260	66						
312	359	90			7			
360	414	110		(2)		7		
477	477	132						

(1) Drive must be programmed to obtain low (208VAC) voltage rating.  
 (2) For Frames 6 and 7, a user-installed flange kit (20-750-FLNG4-Fx) is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.

**f2**

ND Rating									
240V, 60 Hz Input									
Code	Amps	Hp	Frame						
			Enclosure Code						
			B, J, L, T	F	G	N	K, P, W, Y	R	
2P2	2.2	0.5							
4P2	4.2	1							
6P8	6.8	2						1	
9P6	9.6	3							
015	15.3	5							
2P2	2.2	0.5							
4P2	4.2	1							
6P8	6.8	2							
9P6	9.6	3		2	2	2			
015	15.3	5							
022	22	7.5							
028	28	10							
042	42	15		3	3	3			
054	54	20		4	4	4			
070	70	25		5	5	5			
080	80	30							
104	104	40							
130	130	50							
154	154	60		(1)		6			
192	192	75							
260	260	100							
312	312	125							
360	360	150		(1)		7			
477	477	200							

(1) For Frames 6 and 7, a user-installed flange kit (20-750-FLNG4-Fx) is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.

(1) For Frames 6...7, a user installed flange kit (20-750-FLNG4-Fx) is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.  
 (2) Frames 2...5 are IP20, Frames 6...7 are IP00.  
 (3) Available as a drive with options (21G).

1...3 4 5 6 7 8...10 11 12 13 14 15 16 17 18  
**20G 1 1 N B 9P6 J A 0 N N N N N** LD - P3 - P11...  
*a b c d e f1...f6 g h i Positions 14...18 are not used.*

ND Rating			Frame						
690V, 50 Hz Input (not UL Listed)			Enclosure Code						
Code	Amps	kW	B, J, L, T	F	G	N	K, P, W, Y	R	
012	12	7.5							
015	15	11							
020	20	15							
023	23	18.5							
030	30	22							
034	34	30							
046	46	37			6	6			
050	50	45							
061	61	55							
082	82	75							
098	98	90		(1)					
119	119	110							
142	142	132							
171	171	160							
212	212	200			7	7			
263	263	250							
265	265	250							
330	330	315							
370	370	355							
415	415	400	8				g <sup>(2)</sup>		
460	460	450							
500	500	500							
590	590	560							
650	650	630							
710	710	710							
765	765	750							
795	795	800							
960	960	900							
1K0	1040	1000							
1K4	1400	1400	10				10 <sup>(2)</sup>		

- (1) For Frames 6...7, a user installed flange kit (20-750-FLNG4-Fx) is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
- (2) Available as a drive with options (21G).

Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

*PowerFlex 755 w/Options (21G)  
Required Selections*

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle <sup>(1)</sup>
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal-magnetic Circuit Breaker	8...10	Power Disconnect <sup>(1)</sup>
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

(1) Only one option of this type can be selected.

*PowerFlex 755 w/Options (21G)  
Additional Selections*

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors <sup>(1)(2)</sup>
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors <sup>(1)</sup>
L2	3% Output Reactor		
L3	5% Input Reactor	8 Only	
L4	5% Output Reactor		
P20	1200 A Bus	8...10	MCC Power Bus Capacity <sup>(1)</sup>
P22	2000 A Bus		
P24	3000 A Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only <sup>(3)</sup>	Auxiliary Power

- (1) Only one option of this type can be selected.
- (2) Contactor options are not available for systems with MCC power bus.
- (3) Standard on all other cabinet configurations.

*g*

Filtering and CM Cap Configuration		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

*h*

Dynamic Braking <sup>(1)</sup>		
Code	Internal Resistor <sup>(2)</sup>	Internal Transistor <sup>(3)</sup>
A	No	Yes
N	No	No

- (1) Not available on Frames 8...10, specify Code 'N'.
- (2) Frames 1...2 only. Internal Resistor kits (20-750-DB1-Dx) sold separately.
- (3) Standard on Frames 1...5, optional on 6...7.