

Catalog Number Explanation

1...3 4 5 6 7 8...10 11 12 13 14 15 16 17 18
20G 1 1 N E 017 A A 0 N N N N N Cabinet Options (21G)
a b c d e f1...f4 g h i



Drive		
Code	Type	Frames
20F	PowerFlex 753	1...7
20G	PowerFlex 755	1...10
21G	PowerFlex 755 Drive with Options	8...10

Voltage Rating	
Code	Voltage
C	400V AC/540V DC
D	480V AC/650V DC
E	600V AC/810V DC
F	690V AC/932V DC (not UL listed)

b		
Future Use		

c		
Input Type		
Code	Description	Frames
1	AC Input with Precharge, includes DC Terminals	1...4, 8...10
	AC Input without Precharge, includes DC Terminals	5
4	DC Input with Precharge	5...10
A	AC Input with Precharge, no DC Terminals	6...8 *

* The DC Bus Bar kit (20-750-DCBB1-Fx) is available for Frames 6...7 AC input drives requiring DC bus terminals.

f1								
ND Rating								
400V, 50 Hz Input								
Code	Amps	kW	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R

f2								
ND Rating								
480V, 60 Hz Input								
Code	Amps	Hp	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R

2P1	2.1	0.75							
3P5	3.5	1.5							
5P0	5.0	2.2							
8P7	8.7	4		2	2	2		1	
011	11.5	5.5							
015	15.4	7.5							
022	22	11							
030	30	15							
037	37	18.5		3	3	3			
043	43	22							
060	60	30			4	4			
072	72	37				4			
085	85	45				5			
104	104	55					5		
140	140	75						6	
170	170	90							6
205	205	110							
260	260	132							
302	302	160							
367	367	200							
456	456	250							
460	460	250							
540	540	315							
567	567	315							
650	650	355							
750	750	400							
770	770	400							
910	910	500							
1K0	1040	560							
1K1	1090	630							
1K2	1175	710							
1K4	1465	800							
1K5	1480	850							
1K6	1590	900							
2K1	2150	1250							

2P1	2.1	1							
3P4	3.4	2							
5P0	5.0	3							
8P0	8.0	5							
011	11	7.5							
014	14	10							
022	22	15							
027	27	20							
034	34	25							
040	40	30							
052	52	40							
065	65	50							
077	77	60							
096	96	75							
125	125	100							
156	156	125							
186	186	150							
248	248	200							
302	302	250							
361	361	300							
415	415	350							
430	430	350							
485	485	400							
545	545	450							
617	617	500							
710	710	600							
740	740	650							
800	800	700							
960	960	800							
1K0	1045	900							
1K2	1135	1000							
1K3	1365	1100							
1K4	1420	1250							
1K5	1525	1350							
2K0	2070	1750							

d		
Enclosure		
Code	Description	Frames
R	IP20, NEMA/UL Type Open, Frame 1	1
F §	Flange (NEMA/UL Type 4X/12 back)	2...5
G	IP54, NEMA/UL Type 12	2...7
N ‡	IP20/IP00, NEMA/UL Type Open	2...7
B Δ	IP20, NEMA/UL Type 1, 600 mm (23.6 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
J Δ	IP54, UL Type 12, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
K Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
L Δ	IP20, NEMA/UL Type 1, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
P Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
W Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
Y Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
T	IP00, UL Open Type without Control POD	8...10

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 ‡ Frames 2...5 are IP20, Frames 6...7 are IP00.
 Δ Available as a drive with options (21G).

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 Δ Available as a drive with options (21G).

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 Δ Available as a drive with options (21G).

f3

ND Rating				Frame					
600V, 60 Hz Input				Enclosure Code					
Code	Amps	Hp	Enclosure Code						
			B, J, L, T	F	G	N	K, P, W, Y	R	
1P7	1.7	1							
2P7	2.7	2							
3P9	3.9	3							
6P1	6.1	5							
9P0	9	7.5							
011	11	10							
012	12	10							
017	17	15							
018	18	15							
022	22	20							
023	23	20							
024	24	20							
027	27	25							
028	28	25							
032	32	30							
033	33	30							
041	41	40							
042	42	40							
052	52	50							
053	53	50							
063	63	60							
077	77	75							
099	99	100							
125	125	125							
144	144	150							
192	192	200							
242	242	250							
289	289	300							
295	295	300							
355	355	350							
395	395	400							
435	435	450							
460	460	500							
510	510	500							
595	595	600							
630	630	700							
760	760	800							
825	825	900							
900	900	950							
980	980	1000							
1K1	1110	1100							
1K4	1430	1400							

f4

ND Rating				Frame					
690V, 50 Hz Input (not UL listed)				Enclosure Code					
Code	Amps	kW	Enclosure Code						
			B, J, L, T	F	G	N	K, P, W, Y	R	
012	12	7.5							
015	15	11							
020	20	15							
023	23	18.5							
030	30	22							
034	34	30							
046	46	37							
050	50	45							
061	61	55							
082	82	75							
098	98	90							
119	119	110							
142	142	132							
171	171	160							
212	212	200							
263	263	250							
265	265	250							
330	330	315							
370	370	355							
415	415	400							
460	460	450							
500	500	500							
590	590	560							
650	650	630							
710	710	710							
765	765	750							
795	795	800							
960	960	900							
1K0	1040	1000							
1K4	1400	1400							

△ Available as a drive with options (21G).

g

Filtering and CM Cap Configuration ♦		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

♦ 480V drives must select code "A." Jumpers are included for field reconfiguration as desired.

h

Dynamic Braking &		
Code	Internal Resistor ▲	Internal Transistor ▽
A	No	Yes
N	No	No

▲ Frames 1...2 only.

▽ Standard on Frames 1...5, optional on 6...7.

& Not available on Frames 8...10, specify Code "N."

i

Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

PowerFlex 755 w/Options (21G) - Required Selections

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle ★
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal Magnetic Circuit Breaker	8...10	Power Disconnect ★
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

★ Only one option of this type may be selected.

PowerFlex 755 w/Options (21G) - Additional Selections

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors ★ §
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors ★
L2	3% Output Reactor		
L3	5% Input Reactor		
L4	5% Output Reactor		
P20	1200 Amp Bus	8...10	MCC Power Bus Capacity ★
P22	2000 Amp Bus		
P24	3000 Amp Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only	Auxiliary Power

★ Only one option of this type may be selected.

§ Contactor options are not available for systems with MCC power bus.

△ Available as a drive with options (21G).