


Product Details and Certifications

Cross Reference RA Part Number: DB!%+- +&'

 **Product: &\$; %B9\$(%5 \$BBBBB**

Description: PowerFlex 755 AC Drive, with Embedded Ethernet/IP, Air Cooled, AC Input with DC Terminals, Open Type, 41 Amps, 40HP ND, 30HP HD, 600 VAC, 3HP, Frame 5, Filtered, CM Jumper Removed, DB Transistor, Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 755 AC Drive, with Embedded Ethernet/IP
Input Voltage	600 VAC 60Hz
Phases	3 Phases
Current Power Rating	41 Amps, 40HP ND, 30HP HD
Enclosure Type	Open Type
Input Type	AC Input with DC Terminals
Frame Size	Frame 5
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	DB Transistor
HIM	Blank (No HIM)

f3							
ND Rating							
600V, 60 Hz Input							
Code	Amps	Hp	Frame				R
			Enclosure Code				
			B, J, L, T	F	G	N	
1P7	1.7	1					
2P7	2.7	2					
3P9	3.9	3					
6P1	6.1	5					
9P0	9	7.5					
011	11	10					
012	12	10					
017	17	15					
018	18	15					
022	22	20					
023	23	20					
024	24	20					
027	27	25					
028	28	25					
032	32	30					
033	33	30					
041	41	40					
042	42	40					
052	52	50					
053	53	50					
063	63	60					
077	77	75					
099	99	100					
125	125	125					
144	144	150					
192	192	200					
242	242	250					
289	289	300					
295	295	300					
355	355	350					
395	395	400					
435	435	450					
460	460	500					
510	510	500					
595	595	600					
630	630	700					
760	760	800					
825	825	900					
900	900	950					
980	980	1000					
1K1	1110	1100					
1K4	1430	1400					

f4							
ND Rating							
690V, 50 Hz Input (not UL listed)							
Code	Amps	kW	Frame				R
			Enclosure Code				
			B, J, L, T	F	G	N	
012	12	7.5					
015	15	11					
020	20	15					
023	23	18.5					
030	30	22					
034	34	30					
046	46	37					
050	50	45					
061	61	55					
082	82	75					
098	98	90					
119	119	110					
142	142	132					
171	171	160					
212	212	200					
263	263	250					
265	265	250					
330	330	315					
370	370	355					
415	415	400					
460	460	450					
500	500	500					
590	590	560					
650	650	630					
710	710	710					
765	765	750					
795	795	800					
960	960	900					
1K0	1040	1000					
1K4	1400	1400					

△ Available as a drive with options (21G).

g		
Filtering and CM Cap Configuration ♦		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

♦ 480V drives must select code "A." Jumpers are included for field reconfiguration as desired.

h		
Dynamic Braking &		
Code	Internal Resistor ▲	Internal Transistor ▽
A	No	Yes
N	No	No

▲ Frames 1...2 only.

▽ Standard on Frames 1...5, optional on 6...7.

& Not available on Frames 8...10, specify Code "N."

i	
Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

PowerFlex 755 w/Options (21G) - Required Selections

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle *
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal Magnetic Circuit Breaker	8...10	Power Disconnect *
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

* Only one option of this type may be selected.

PowerFlex 755 w/Options (21G) - Additional Selections

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors * §
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors *
L2	3% Output Reactor		
L3	5% Input Reactor		
L4	5% Output Reactor		
P20	1200 Amp Bus	8...10	MCC Power Bus Capacity *
P22	2000 Amp Bus		
P24	3000 Amp Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only	Auxiliary Power

* Only one option of this type may be selected.

§ Contactor options are not available for systems with MCC power bus.

△ Available as a drive with options (21G).