

Product Details and Certifications

Cross Reference RA Part Number: PN-~~04~~ +0%

 Product: **20G11NE D-AA0NNNNN**

Description: PowerFlex 755 AC Drive, with Embedded Ethernet/IP, Air Cooled, AC Input with DC Terminals, Open Type, ~~H~~ Amps, ~~H~~HP ND, 2HP HD, 600V/AC, 3HP, Frame ~~AAAAAAAAAAAAAAAAAAAA~~, Filtered, CM Jumper Removed, DB Transistor, Blank (No HIM)




Representative Photo Only (actual product may vary based on configuration selections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 755 AC Drive, with Embedded Ethernet/IP
Input Voltage	600 VAC 60Hz
Phases	3 Phases
Current Power Rating	H Amps, H HP ND, 2HP HD
Enclosure Type	Open Type
Input Type	AC Input with A DC Terminals
Frame Size	Frame H
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	DB Transistor
HIM	Blank (No HIM)

Catalog Number Explanation



a

Drive		
Code	Type	Frames
20F	PowerFlex 753	1...7
20G	PowerFlex 755	1...10
21G	PowerFlex 755 Drive with Options	8...10

e

Voltage Rating	
Code	Voltage
C	400V AC/540V DC
D	480V AC/650V DC
E	600V AC/810V DC
F	690V AC/932V DC (not UL listed)

b

Future Use

f1

ND Rating	
400V, 50 Hz Input	

f2

ND Rating	
480V, 60 Hz Input	

c

Input Type		
Code	Description	Frames
1	AC Input with Precharge, includes DC Terminals	1...4, 8...10
	AC Input without Precharge, includes DC Terminals	5
4	DC Input with Precharge	5...10
A	AC Input with Precharge, no DC Terminals	6...8 *

* The DC Bus Bar kit (20-750-DCBB1-Fx) is available for Frames 6...7 AC input drives requiring DC bus terminals.

Code	Amps	kW	Frame							
			Enclosure Code							
			B, J, L, T	F	G	N	K, P, W, Y	R		
2P1	2.1	0.75								
3P5	3.5	1.5								
5P0	5.0	2.2								
8P7	8.7	4		2	2	2			1	
011	11.5	5.5								
015	15.4	7.5								
022	22	11								
030	30	15								
037	37	18.5		3	3	3				
043	43	22								
060	60	30			4	4				
072	72	37				5				
085	85	45				5				
104	104	55					5			
140	140	75						6		
170	170	90							6	
205	205	110								6
260	260	132								5
302	302	160								
367	367	200								7
456	456	250								
460	460	250								
540	540	315								
567	567	315								
650	650	355					8			8 Δ
750	750	400								
770	770	400								
910	910	500								
1K0	1040	560								
1K1	1090	630								
1K2	1175	710								
1K4	1465	800								
1K5	1480	850								
1K6	1590	900								
2K1	2150	1250								

Code	Amps	Hp	Frame							
			Enclosure Code							
			B, J, L, T	F	G	N	K, P, W, Y	R		
2P1	2.1	1								
3P4	3.4	2								
5P0	5.0	3								
8P0	8.0	5								
011	11	7.5								
014	14	10								
022	22	15								
027	27	20								
034	34	25								
040	40	30								
052	52	40								
065	65	50								
077	77	60								
096	96	75								
125	125	100								
156	156	125								
186	186	150								
248	248	200								
302	302	250								
361	361	300								
415	415	350								
430	430	350								
485	485	400								
545	545	450								
617	617	500								
710	710	600								
740	740	650								
800	800	700								
960	960	800								
1K0	1045	900								
1K2	1135	1000								
1K3	1365	1100								
1K4	1420	1250								
1K5	1525	1350								
2K0	2070	1750								

d

Enclosure		
Code	Description	Frames
R	IP20, NEMA/UL Type Open, Frame 1	1
F §	Flange (NEMA/UL Type 4X/12 back)	2...5
G	IP54, NEMA/UL Type 12	2...7
N ‡	IP20/IP00, NEMA/UL Type Open	2...7
B Δ	IP20, NEMA/UL Type 1, 600 mm (23.6 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
J Δ	IP54, UL Type 12, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
K Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
L Δ	IP20, NEMA/UL Type 1, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
P Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
W Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
Y Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
T	IP00, UL Open Type without Control POD	8...10

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 ‡ Frames 2...5 are IP20, Frames 6...7 are IP00.
 Δ Available as a drive with options (21G).

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 Δ Available as a drive with options (21G).

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 Δ Available as a drive with options (21G).

f3

ND Rating			600V, 60 Hz Input								
Code	Amps	Hp	Frame								
			Enclosure Code								
			B, J, L, T	F	G	N	K, P, W, Y	R			
1P7	1.7	1									
2P7	2.7	2									
3P9	3.9	3		3	3	3					
6P1	6.1	5									
9P0	9	7.5									
011	11	10									
012	12	10		-	6	6					
017	17	15		3	3	3					
018	18	15		-	6	6					
022	22	20		3	3	3					
023	23	20									
024	24	20		-	6	6					
027	27	25		4	4	4					
028	28	25		-	6	6					
032	32	30		4	4	4					
033	33	30		-	6	6					
041	41	40		5	5	5					
042	42	40		-	6	6					
052	52	50		5	-	5					
053	53	50									
063	63	60									
077	77	75									
099	99	100			6	6					
125	125	125									
144	144	150									
192	192	200									
242	242	250			7	7					
289	289	300									
295	295	300									
355	355	350									
395	395	400									
435	435	450									
460	460	500									
510	510	500									
595	595	600									
630	630	700									
760	760	800									
825	825	900									
900	900	950									
980	980	1000									
1K1	1110	1100									
1K4	1430	1400									

Δ Available as a drive with options (21G).

f4

ND Rating			690V, 50 Hz Input (not UL listed)								
Code	Amps	kW	Frame								
			Enclosure Code								
			B, J, L, T	F	G	N	K, P, W, Y	R			
012	12	7.5									
015	15	11									
020	20	15									
023	23	18.5									
030	30	22									
034	34	30									
046	46	37						6	6		
050	50	45									
061	61	55									
082	82	75									
098	98	90									
119	119	110									
142	142	132									
171	171	160									
212	212	200						7	7		
263	263	250									
265	265	250									
330	330	315									
370	370	355									
415	415	400								8 Δ	
460	460	450									
500	500	500									
590	590	560									
650	650	630									
710	710	710									
765	765	750								9 Δ	
795	795	800									
960	960	900									
1K0	1040	1000									
1K4	1400	1400									10 Δ

Δ Available as a drive with options (21G).

g

Filtering and CM Cap Configuration ♦		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

♦ 480V drives must select code "A." Jumpers are included for field reconfiguration as desired.

h

Dynamic Braking &		
Code	Internal Resistor ▲	Internal Transistor ▽
A	No	Yes
N	No	No

▲ Frames 1...2 only.
 ▽ Standard on Frames 1...5, optional on 6...7.
 & Not available on Frames 8...10, specify Code "N."

i

Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

PowerFlex 755 w/Options (21G) - Required Selections

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle ★
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal Magnetic Circuit Breaker	8...10	Power Disconnect ★
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

★ Only one option of this type may be selected.

PowerFlex 755 w/Options (21G) - Additional Selections

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors ★ §
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors ★
L2	3% Output Reactor		
L3	5% Input Reactor		
L4	5% Output Reactor		
P20	1200 Amp Bus	8...10	MCC Power Bus Capacity ★
P22	2000 Amp Bus		
P24	3000 Amp Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only	Auxiliary Power

★ Only one option of this type may be selected.
 § Contactor options are not available for systems with MCC power bus.