

 **Cross Reference RA Part Number: PN-135244**

 **Product: 20G11RD011AA0NNNNN**

Description: PowerFlex 755 AC Drive, with Embedded Ethernet/IP, Air Cooled, AC Input with DC Terminals, Open Type/Frame 1, 11 Amps, (Fr1 7.5HP ND, 5HP HD/Fr2 7.5HP ND, 7.5HP HD), 480 VAC, 3 PH, Frame 1, Filtered, CM Jumper Removed, DB Transistor, Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration sections)

BASE DRIVE INFORMATION

PowerFlex 755 AC Drive, with Embedded Ethernet/IP

BULLETIN NUMBER

PowerFlex 755 AC Drive, with Embedded Ethernet/IP

VOLTAGE CLASS

480 VAC, 3 PH

OUTPUT CURRENT

11 Amps, (Fr1 7.5HP ND, 5HP HD/Fr2 7.5HP ND, 7.5HP HD)

ENCLOSURE TYPE

Open Type/Frame 1

INPUT TYPE

AC Input with DC Terminals

FRAME SIZE

Frame 1

EMC FILTERING OPTIONS

Filtered, CM Jumper Removed

DYNAMIC BRAKING

DB Transistor

HIM

Blank (No HIM)

Catalog Number Explanation

1...3 4 5 6 7 8...10 11 12 13 14 15 16 17 18
20G 1 1 R D 011 A A 0 N N N N N Cabinet Options (21G)
a b c d e f1...f4 g h i

a

Drive		
Code	Type	Frames
20F	PowerFlex 753	1...7
20G	PowerFlex 755	1...10
21G	PowerFlex 755 Drive with Options	8...10

e

Voltage Rating	
Code	Voltage
C	400V AC/540V DC
D	480V AC/650V DC
E	600V AC/810V DC
F	690V AC/932V DC (not UL listed)

b

Future Use

f1

ND Rating								
400V, 50 Hz Input								
Code	Amps	kW	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R

f2

ND Rating								
480V, 60 Hz Input								
Code	Amps	Hp	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R

c

Input Type		
Code	Description	Frames
1	AC Input with Precharge, includes DC Terminals	1...4, 8...10
	AC Input without Precharge, includes DC Terminals	5
4	DC Input with Precharge	5...10
A	AC Input with Precharge, no DC Terminals	6...8 *

* The DC Bus Bar kit (20-750-DCBB1-Fx) is available for Frames 6...7 AC input drives requiring DC bus terminals.

2P1	2.1	0.75																	
3P5	3.5	1.5																	
5P0	5.0	2.2																	
8P7	8.7	4																	
011	11.5	5.5																	
015	15.4	7.5																	
022	22	11																	
030	30	15																	
037	37	18.5																	
043	43	22																	
060	60	30																	
072	72	37																	
085	85	45																	
104	104	55																	
140	140	75																	
170	170	90																	
205	205	110																	
260	260	132																	
302	302	160																	
367	367	200																	
456	456	250																	
460	460	250																	
540	540	315																	
567	567	315																	
650	650	355																	
750	750	400																	
770	770	400																	
910	910	500																	
1K0	1040	560																	
1K1	1090	630																	
1K2	1175	710																	
1K4	1465	800																	
1K5	1480	850																	
1K6	1590	900																	
2K1	2150	1250																	

2P1	2.1	1																	
3P4	3.4	2																	
5P0	5.0	3																	
8P0	8.0	5																	
011	11	7.5																	
014	14	10																	
022	22	15																	
027	27	20																	
034	34	25																	
040	40	30																	
052	52	40																	
065	65	50																	
077	77	60																	
096	96	75																	
125	125	100																	
156	156	125																	
186	186	150																	
248	248	200																	
302	302	250																	
361	361	300																	
415	415	350																	
430	430	350																	
485	485	400																	
545	545	450																	
617	617	500																	
710	710	600																	
740	740	650																	
800	800	700																	
960	960	800																	
1K0	1045	900																	
1K2	1135	1000																	
1K3	1365	1100																	
1K4	1420	1250																	
1K5	1525	1350																	
2K0	2070	1750																	

d

Enclosure		
Code	Description	Frames
R	IP20, NEMA/UL Type Open, Frame 1	1
F §	Flange (NEMA/UL Type 4X/12 back)	2...5
G	IP54, NEMA/UL Type 12	2...7
N ‡	IP20/IP00, NEMA/UL Type Open	2...7
B Δ	IP20, NEMA/UL Type 1, 600 mm (23.6 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
J Δ	IP54, UL Type 12, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
K Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
L Δ	IP20, NEMA/UL Type 1, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
P Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, Standard Cabinet Color (RAL 7032)	8...10
W Δ	IP20, NEMA/UL Type 1, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
Y Δ	IP54, NEMA 12, 2500 MCC Style Cabinet & Options w/MCC Power Bus, 800 mm (31.5 in.) Deep, CenterLine 2100 Gray (ASA49)	8...10
T	IP00, UL Open Type without Control POD	8...10

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 ‡ Frames 2...5 are IP20, Frames 6...7 are IP00.
 Δ Available as a drive with options (21G).

§ For Frames 6...7 a User Installed Flange Kit is available to convert a Code N drive that provides a NEMA/UL Type 4X/12 back.
 Δ Available as a drive with options (21G).

f3

ND Rating			600V, 60 Hz Input					
Code	Amps	Hp	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R
1P7	1.7	1						
2P7	2.7	2						
3P9	3.9	3						
6P1	6.1	5						
9P0	9	7.5						
011	11	10						
012	12	10						
017	17	15						
018	18	15						
022	22	20						
023	23	20						
024	24	20						
027	27	25						
028	28	25						
032	32	30						
033	33	30						
041	41	40						
042	42	40						
052	52	50						
053	53	50						
063	63	60						
077	77	75						
099	99	100						
125	125	125						
144	144	150						
192	192	200						
242	242	250						
289	289	300						
295	295	300						
355	355	350						
395	395	400						
435	435	450						
460	460	500						
510	510	500						
595	595	600						
630	630	700						
760	760	800						
825	825	900						
900	900	950						
980	980	1000						
1K1	1110	1100						
1K4	1430	1400						

△ Available as a drive with options (21G).

f4

ND Rating			690V, 50 Hz Input (not UL listed)					
Code	Amps	kW	Frame					
			Enclosure Code					
			B, J, L, T	F	G	N	K, P, W, Y	R
012	12	7.5						
015	15	11						
020	20	15						
023	23	18.5						
030	30	22						
034	34	30						
046	46	37						
050	50	45						
061	61	55						
082	82	75						
098	98	90						
119	119	110						
142	142	132						
171	171	160						
212	212	200						
263	263	250						
265	265	250						
330	330	315						
370	370	355						
415	415	400						
460	460	450						
500	500	500						
590	590	560						
650	650	630						
710	710	710						
765	765	750						
795	795	800						
960	960	900						
1K0	1040	1000						
1K4	1400	1400						

△ Available as a drive with options (21G).

g

Filtering and CM Cap Configuration ♦		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

♦ 480V drives must select code "A." Jumpers are included for field reconfiguration as desired.

h

Dynamic Braking &		
Code	Internal Resistor ▲	Internal Transistor ▽
A	No	Yes
N	No	No

▲ Frames 1...2 only.
 ▽ Standard on Frames 1...5, optional on 6...7.
 & Not available on Frames 8...10, specify Code "N."

i

Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

PowerFlex 755 w/Options (21G) - Required Selections

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle ★
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal Magnetic Circuit Breaker	8...10	Power Disconnect ★
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

★ Only one option of this type may be selected.

PowerFlex 755 w/Options (21G) - Additional Selections

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors ★ §
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors ★
L2	3% Output Reactor		
L3	5% Input Reactor		
L4	5% Output Reactor		
P20	1200 Amp Bus	8...10	MCC Power Bus Capacity ★
P22	2000 Amp Bus		
P24	3000 Amp Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only	Auxiliary Power

★ Only one option of this type may be selected.
 § Contactor options are not available for systems with MCC power bus.