

# Product Details and Certifications

7 fcgg'F YZYfYbW'F 5 'DUfhBi a VYf. 'i !\$\$, &\$- &\$\$' , \$+%

**Product: 20; 1AN8% \* AB0NNNNN**

Description: PowerFlex 751 AC Drive, with Embedded  $\text{O}@\{ \} \wedge \sigma \text{U}$ , Air Cooled, AC Input with  $\text{U}!\wedge \& \text{e}^* \wedge \text{E} \text{P}$  DC Terminals, Open Type,  $\text{A} \hat{I} \hat{I}$  Amps,  $\text{A} \hat{I} \hat{I} \in \text{A} \text{P ND}$ ,  $\text{A} \hat{G} \hat{A} \text{P HD}$ ,  $\text{A} \hat{I} \hat{I} \in \text{XO} \hat{E} \text{A} \text{P} \hat{U} \hat{Z} \alpha \hat{A}$ , Filtered, CM Jumper Removed,  $\text{P}[\ ] \wedge$ , Blank (No HIM)



Representative Photo Only (actual product may vary based on configuration selections)

## BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 751 AC Drive, with Embedded $\text{O}@\{ \} \wedge \sigma \text{U}$
Input Voltage	$\text{I} \hat{I} \in \text{VAC} \hat{I} \text{E} \text{P}$ :
Phases	3 Phases
Current $\text{U}[\ ] \wedge \text{A}$ Rating	$\text{F} \hat{I} \hat{I}$ Amps $\text{A} \hat{I} \hat{I} \in \text{A} \text{P} \hat{U} \hat{Z} \alpha \hat{A} \text{G} \hat{A} \text{P} \hat{U} \hat{Z} \alpha \hat{A}$
Enclosure Type	$\text{U}[\ ] \wedge \text{A}$ type
Input Type	AC Input with Precharge, no DC Terminals
Frame Size	Frame $\hat{I}$
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	$\text{P}[\ ] \wedge$
HIM	Blank (No HIM)



*f3*

ND Rating		600V, 60 Hz Input		Frame					
Code	Amps	Hp	Enclosure Code						
			B, J, L, T	F	G	N	K, P, W, Y	R	
1P7	1.7	1							
2P7	2.7	2							
3P9	3.9	3							
6P1	6.1	5							
9P0	9	7.5							
011	11	10							
012	12	10							
017	17	15							
018	18	15							
022	22	20							
023	23	20							
024	24	20							
027	27	25							
028	28	25							
032	32	30							
033	33	30							
041	41	40							
042	42	40							
052	52	50							
053	53	50							
063	63	60							
077	77	75							
099	99	100							
125	125	125							
144	144	150							
192	192	200							
242	242	250							
289	289	300							
295	295	300							
355	355	350							
395	395	400							
435	435	450							
460	460	500							
510	510	500							
595	595	600							
630	630	700							
760	760	800							
825	825	900							
900	900	950							
980	980	1000							
1K1	1110	1100							
1K4	1430	1400							

△ Available as a drive with options (21G).

*f4*

ND Rating		690V, 50 Hz Input (not UL listed)		Frame					
Code	Amps	kW	Enclosure Code						
			B, J, L, T	F	G	N	K, P, W, Y	R	
012	12	7.5							
015	15	11							
020	20	15							
023	23	18.5							
030	30	22							
034	34	30							
046	46	37							
050	50	45							
061	61	55							
082	82	75							
098	98	90							
119	119	110							
142	142	132							
171	171	160							
212	212	200							
263	263	250							
265	265	250							
330	330	315							
370	370	355							
415	415	400							
460	460	450							
500	500	500							
590	590	560							
650	650	630							
710	710	710							
765	765	750							
795	795	800							
960	960	900							
1K0	1040	1000							
1K4	1400	1400							

△ Available as a drive with options (21G).

*g*

Filtering and CM Cap Configuration ♦		
Code	Filtering	Default CM Cap Connection
A	Yes	Jumper Removed
J	Yes	Jumper Installed

♦ 480V drives must select code "A." Jumpers are included for field reconfiguration as desired.

*h*

Dynamic Braking &		
Code	Internal Resistor ▲	Internal Transistor ▽
A	No	Yes
N	No	No

▲ Frames 1...2 only.  
 ▽ Standard on Frames 1...5, optional on 6...7.  
 & Not available on Frames 8...10, specify Code "N."

*i*

Door Mounted HIM (Frames 8...10)	
Code	Operator Interface
0	No Door Mounted HIM
2	Enhanced LCD, Full Numeric, IP20
4	Enhanced LCD, Full Numeric, IP66 NEMA Type 4X/12

PowerFlex 755 w/Options (21G) - Required Selections

Code	Option	Frames	Type
LD	Light Duty	8...10	System Overload Duty Cycle *
ND	Normal Duty		
HD	Heavy Duty		
P3	Input Thermal Magnetic Circuit Breaker	8...10	Power Disconnect *
P5	Input Non-Fused Molded Case Disconnect Switch	8 Only	
P14	Wiring Only Bay	8...10	Wiring Only Bay

\* Only one option of this type may be selected.

PowerFlex 755 w/Options (21G) - Additional Selections

Code	Option	Frames	Type
P11	Input Contactor	8 Only	Contactors * §
P12	Output Contactor		
L1	3% Input Reactor	8...9	Reactors *
L2	3% Output Reactor		
L3	5% Input Reactor		
L4	5% Output Reactor		
P20	1200 Amp Bus	8...10	MCC Power Bus Capacity *
P22	2000 Amp Bus		
P24	3000 Amp Bus		
P30	UPS Control Bus, DC Input w/Precharge only	8...10	UPS Control Bus
X1	Auxiliary Transformer (500VA available), IP20 Cabinet Only	8 Only	Auxiliary Power

\* Only one option of this type may be selected.  
 § Contactor options are not available for systems with MCC power bus.