

Product Details and Certifications

Cross Reference RA Part Number: 700-ADR B

 **Product: 700-ADR**

Description: 700-A Diode Surge Suppressor Module, 6...220V DC (Pkg. Qty. 20)



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number










700-H General Purpose Accessories

Accessory Selection

Individual Accessory Selection

SELECTION

Bulletin 700-H Accessories

| | Description | Pkg. Qty. | Cat. No. | |
|--|---|--|----------------|-----------|
|  | Diode Surge Suppressor Voltage Range: 6...220V DC used with 700-HN153 socket | 10 | 700-ADR | |
| | Diode with LED Surge Suppressor Voltage Range: 6...24V DC used with 700-HN153 socket | 10 | 700-ADL1R | |
| | Diode with LED Surge Suppressor Voltage Range: 28...60V DC used with 700-HN153 socket | 10 | 700-ADL2R | |
| | Diode with LED Surge Suppressor Voltage Range: 110...220V DC used with 700-HN153 socket | 10 | 700-ADL3R | |
| | Varistor with LED Surge Suppressor Voltage Range: 6...24V AC used with 700-HN153 socket | 10 | 700-AV1R | |
| | Varistor with LED Surge Suppressor Voltage Range: 110...240V AC used with 700-HN153 socket | 10 | 700-AV3R | |
| | RC Surge Suppressor Voltage Range: 6...24V AC/DC used with 700-HN153 socket | 10 | 700-AR1 | |
| | RC Surge Suppressor Voltage Range: 110...240V AC/DC used with 700-HN153 socket | 10 | 700-AR2 | |
|  | Timing Module On-Delay or One-Shot selectable voltage range: 12...24V AC/DC used with sockets that accept plug-in accessory modules. |  | 700-AT3 | |
| | Timing Module On-Delay or One-Shot selectable voltage range: 110...125V AC used with sockets that accept plug-in accessory modules. | | 1 | 700-AT3A1 |
| | Timing Module On-Delay or One-Shot selectable voltage range: 230...240V AC used with sockets that accept plug-in accessory modules. | | | 700-AT3A2 |
|  <p>Cat. No. 700-HT3</p> | Multi-Function Multi-Range Time Module Voltage range 12...240V AC 50/60 Hz and 12...240V DC, with a voltage variation of 85...110%. Repeat accuracy of ±1%. Reset time <50 ms. For use with 700-HN153 socket. Refer to page 9-23 for Specifications. Eight Timing Modes Seven Timing Ranges: |  | 1 | 700-HT3 |
| | 1. 1 s 2. 10 s 3. 100 s 4. 10 min. 5. 100 min. 6. 10 hours 7. 100 hours 8. LED Indicator | | | |
|  <p>Cat. No. 700-HN153</p> | Screw Terminal Socket — Panel or DIN Rail Mounting. Guarded Terminal Construction 11-blade socket for use with Bulletin 700-HB relays. This socket has coil and contact separation as well as the ability to use optional plug-in modules (700-A__ accessories, LED, surge suppression, timing modules). | 10 | 700-HN153 | |
|  <p>Cat. No. 700-HN154</p> | Screw Terminal Base Socket — Panel or DIN Rail Mounting. Open Style Construction 11-blade for use with Bulletin 700-HB relays. | 10 | 700-HN154 | |
|  <p>Cat. No. 199-DR1</p> | DIN (#3) symmetrical hat rail 35 x 7.5 x 1 m | 10 | 199-DR1 | |
|  <p>Sample Retainer Clips</p> | Retainer Clip for Cat. No. -HN154 open terminal socket with 700-HB relays* Secures relay in socket. Order must be for 10 clips or multiples of 10. | 10 | 700-HN156 | |
| | Retainer Clip for Cat. No. 700-HN153 Sockets with 700-HB Relays* . Secures relay in socket. Order must be for 10 clips or multiples of 10. | 10 | 700-HN158 | |



* See Bulletin 700-HB square base relay socket and retainer clip reference chart (see page 9-22).