


Features

- » Dust and water jet protected to IP55 (NEMA4 IEC529)
- » Withstands high levels of shock, vibration, dirt and humidity
- » The contoured window gives an exceptionally wide viewing angle
- » Complies with ANSI-C39 (IEC 51)
- » UL approval for short scale Ammeters, Voltmeters, Frequency Meters and Elapsed Time meters on selected ranges. File Number E87815
- » Instruments comply with BSEN61010-1 meets IEC414 (BS5458) Dielectric Test (2600V for 1 min)

Options

On request the following are available:

- » Supplementary Pointer
- » Non Reflecting Window
- » Heavily Damped Movement
- » Panel Gasket
- » Clamp Band Fixing long scale
- » Coloured Internal Gasket



A range of shortscale and longscale panel meters. Their rugged design will suit demanding environmental applications.

Elapsed Time Meter and Frequency Meter

Voltage:	100/125V, 200/250V or 480V A.C.	Temperature:	
Frequency:	50Hz or 60Hz	Range:	-20°C to 65°C (-4°F to 149°F)
Burden:	4VA Maximum	Storage:	-30°C to 70°C (-22°F to 158°F)

Iron Vane A.C. Ammeter & Voltmeter


Accuracy:	Shortscale: ammeters 2.5%; Longscale: 1.5 %	Burden:	
Ratings:		Ammeters:	shortscale 0.5VA; long scale 1.5VA
Ammeters:	Shortscale 1 to 80A Longscale 1 to 20A	Voltmeters:	4.5VA maximum
Voltmeters:	10V to 600V	Temperature:	
Overload:		Range:	-20°C to 65°C (-4°F to 149°F)
Ammeters:	x1.2 for 2 hours 10 x for 5 seconds	Storage:	-30°C to 70°C (-22°F to 158°F)
Voltmeters:	x1.2 for 2 hours 2 x for 5 seconds		

Moving Coil D.C. Ammeter & Voltmeter


Accuracy Class:	Shortscale 1.5; longscale 1.5	Impedance:	Voltmeters 1000 ohms per Volt nominal
Ratings:		Temperature:	
Ammeters:	200µA to 30A (100µA shortscale)	Range:	-20°C to 65°C (-4°F to 149°F)
Voltmeters:	50mV to 600V	Storage:	-30°C to 70°C (-22°F to 158°F)
Overload:			
Ammeters:	x1.2 for 2 hours 10 x for 5 seconds		
Voltmeters:	x1.2 for 2 hours 2 x for 5 seconds		

Dimensions


x = Terminals
1/4 - 28 UNF up to 59.9A 0.72" long.
5/16 - 24UNF over 60A 0.94" long.




016 Series Fiesta Indicators



A.C. Ammeter



A.C. Voltmeter



D.C. Voltmeter

Rating	Scaling*	Short Scale Catalogue No.	Long Scale Catalogue No.
--------	----------	---------------------------	--------------------------

A.C. Ammeter True RMS Reading - Self Contained 40/70Hz

5A	0-5a	•016-02A*-LSLS	016-03A*-.LSLS
10A	0-10a	016-02A*-MTMT	016-03A*-.MTMT
15A	0-15a	016-02A*-NDND	016-03A*-.NDND
20A	0-20a	016-02A*-NGNG	016-03A*-.NGNG
30A	0-30a	016-02A*-NLNL	016-03A*-.NLNL
5A	Transformer Rated	•016-02A*-LS**	016-03A*-.LS**

A.C. Ammeters - Moving Coil Rectified

100µA to 1A	To Suit	016-01B*-	016-05B*-
-------------	---------	-----------	-----------

A.C. Voltmeter True RMS Reading

150v	0-150V	•016-02V*-PZPZ	016-03V*-PZPZ
300v	0-300V	•016-02V*-RXRX	016-03V*-RXRX
600v	0-600V	•016-02V*-SJSJ	016-03V*-SJSJ
150V	Transformer Rated	•016-02V*-PZ**	016-03V*-PZ**

A.C. Voltmeters - Moving Coil Rectified

15V to 600V	To suit	016-01W*-	016-05W*-
-------------	---------	-----------	-----------

D.C. Ammeters

0-50mV	To Suit Requirements	016-01A*-EC**	016-05A*-.EC**
0-1mA	To Suit Requirements	•016-01A*-FA**	016-05A*-.FA**
0-5mA	To Suit Requirements	016-01A*-FX**	016-05A*-.FX**
0-10mA	To Suit Requirements	016-01A*-HA**	016-05A*-.HA**
0-20mA	To Suit Requirements	•016-01A*-HF**	016-05A*-.HF**

Milliammeters Suppressed Zero - No zero set unless specified

4/20mA	To Suit Requirements	•016-01RA*-HG**	016-05RA-HG**
--------	----------------------	-----------------	---------------

Voltage Suppressed Zero - No zero set unless specified

1-5V	To Suit	016-01S*-LM	016-05S*-LM
------	---------	-------------	-------------

D.C. Voltmeters Sensitivity 1000Ω/Volt

0-15V	0-15V	016-01V*-NDND	016-05V*-NDND
0-30V	0-30V	016-01V*-NLNL	016-05V*-NLNL
0-50V	0-50V	•016-01V*-NTNT	016-05V*-NTNT
0-150V	0-150V	•016-01V*-PZPZ	016-05V*-PZPZ
0-300V	0-300V	•016-01V*-RXRX	016-05V*-RXRX
0-600V	0-600V	016-01V*-SJSJ	016-05V*-SJSJ

* Please state A or B at time of ordering. A = ANSI B = BS89

** Customer to state required scaling at time of ordering

• UL recognised

0-80A Scale