

➔ Cross Reference RA Part Number: **PN-115234**

➔ Mfr Part Number: **143-500**

## GE Energy Connections



# Model 143

## Current Transformer Window Diameter 7.31"

### Application

Relaying and metering.

### Frequency

50-400 Hz.

### Insulation Level

600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Order mounting bracket kit 0221B00775 separately.

Multi-ratios available on request.

Approximate weight 60 lbs.

REGULATORY AGENCY APPROVALS  
 E93779  LR89403  
Manufactured to meet the requirements of ANSI/IEEE C57.13.  
Classified by U.L. in accordance with IEC 44-1

### Model 143




Catalog Number	Current Ratio	Relay Class	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (Ω @ 75 °C)	Continuous Thermal Rating Factor	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30 °C	@ 55 °C
➔ 143-500	50:5	C20	4.8	4.8	—	—	—	0.014	2.0	2.0
143-750	75:5	C20	2.4	2.4	—	—	—	0.042	2.0	2.0
143-101	100:5	C20	1.2	2.4	4.8	4.8	—	0.056	2.0	2.0
143-151	150:5*	C50	0.6	0.6	1.2	2.4	4.8	0.121	2.0	2.0
143-201	200:5*	C50	0.3	0.3	0.6	1.2	2.4	0.161	2.0	2.0
143-251	250:5*	C50	0.3	0.3	0.6	1.2	2.4	0.175	2.0	2.0
143-301	300:5*	C100	0.3	0.3	0.3	0.6	1.2	0.241	2.0	2.0
143-401	400:5*	C100	0.3	0.3	0.3	0.3	0.6	0.322	2.0	2.0
143-501	500:5*	C100	0.3	0.3	0.3	0.6	0.6	0.441	2.0	2.0
143-601	600:5*	C200	0.3	0.3	0.3	0.3	0.3	0.530	2.0	1.5
143-751	750:5*	C200	0.3	0.3	0.3	0.3	0.3	0.662	2.0	1.5
143-801	800:5*	C200	0.3	0.3	0.3	0.3	0.3	0.706	2.0	1.5
143-102	1,000:5*	C200	0.3	0.3	0.3	0.3	0.3	0.883	1.5	1.33
143-122	1,200:5*	C400	0.3	0.3	0.3	0.3	0.3	1.059	1.5	1.0
143-152	1,500:5*	C400	0.3	0.3	0.3	0.3	0.3	1.324	1.5	1.0
143-162	1,600:5*	C400	0.3	0.3	0.3	0.3	0.3	1.413	1.33	1.0
143-202	2,000:5*	C400	0.3	0.3	0.3	0.3	0.3	1.678	1.33	1.0
143-252	2,500:5*	C400	0.3	0.3	0.3	0.3	0.3	2.097	1.0	0.8
143-302	3,000:5*	C800	0.3	0.3	0.3	0.3	0.3	2.516	1.0	0.8
143-322	3,200:5*	C800	0.3	0.3	0.3	0.3	0.3	2.684	1.0	0.8
143-352	3,500:5*	C800	0.3	0.3	0.3	0.3	0.3	2.936	1.0	0.8
143-402	4,000:5*	C800	0.3	0.3	0.3	0.3	0.3	3.355	1.0	0.6
143-502	5,000:5*	C800	0.3	0.3	0.3	0.3	0.3	3.983	1.0	0.6
143-602	6,000:5*	C800	0.3	0.3	0.3	0.3	0.3	4.780	0.8	0.6

Approved for revenue metering by Industry Canada No. AE-0642



# Model 143

EXCITATION CURVE



Grid-AIS-L4-ITL\_Model\_143-1256-2017\_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

