

VEEDER-ROOT brand
Electronic Time Indicators/Controllers

7999 Mite Elapsed Timers



A family of low cost, high performance LCD indicators and accessories



5 ELECTRONIC

The MITE Series 7999 time indicators offer unmatched ease-of-use, simplicity, performance and value. Two models provide four timing ranges to cover applications such as coating/rinsing, baking and engine usage.

- Timers include models for second or minutes and seconds; or hours and minutes or hours and hundredths
- Compact, solid state design
- Front panel and remote reset
- NEMA-4/IP65 environmental sealing
- Easy-to-read, high contrast Liquid Crystal Display (LCD)
- UL recognized, CSA Certified
- Supplied with prewired plug-in connector
- Fast, easy mounting - minimal 1.2" (30mm) depth behind panel
- Very low priced - without sacrifice of performance or reliability

Power Requirements: None; permanent internal lithium battery with 10-year typical life

Operating Temperature: +14° to +144 °F (-10° to +60°C)

Storage Temperature: +4° to +144 °F (-20° to +60°C)

Model No.	Description
079998D-510	LCD Time Indicator, Sec or Min-Sec, Din Size
079998D-610	LCD Time Indicator, Hr-Min or Hrs- ¹ / ₁₀₀ ths, Din Size

SPECIFICATIONS

Accuracy: Timer: ±20 ppm @ 20°C

Inputs: Contact closure or open collector

Display: 7 digit, 7mm LCD

Reset: Front panel (selectable), remote by contact closure or NPN transistor.


ACCESSORIES

AC/DC Input Module: Allows use of high voltage input signal of 5 to 240 VAC/DC. Connections are via screw terminations. Part Number 108940-0001

Screw Terminal Adaptor: Provides the convenience of screw terminal connection of input signal and remote reset. Part Number 108937-0001

For 12mm Display, see Series A103
For Electrical Hour Meters, see Series 7795

Typical Applications:



Dimensions:

